

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P518588

Luminaire Tested: **SQ4-BB-0U-050D-830-1D-UNV-STD-W-4**

Issue Date: 4/29/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P518588  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2009-966-12)  
Test Lab: INNOVATION CENTER  
Issue Date: 4/29/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-BB-0U-050D-830-1D-UNV-STD-W-4  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH BLACK BAFFLE  
DOWNLIGHT 500 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: 3000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1183.1 lumens  
Efficiency: N/A  
Efficacy: 73.0 lumens/watt  
Spacing Criteria (0/90/45): 0.85 / 0.97 / 0.97  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 16.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P518588  
CATALOG NUMBER: SQ4-BB-0U-050D-830-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P518588

CATALOG NUMBER: SQ4-BB-0U-050D-830-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91				91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82				82
3	99	91	85	81	97	90	84	80	87	82	79	85	81	77	82	79	76	74				74
4	93	84	77	72	91	83	76	72	80	75	71	78	74	70	76	72	69	67				67
5	87	77	70	65	85	76	70	65	74	68	64	72	67	64	71	66	63	61				61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56				56
7	77	66	59	54	75	65	59	54	64	58	53	62	57	53	61	56	53	51				51
8	72	61	54	50	71	61	54	49	59	53	49	58	53	49	57	52	49	47				47
9	68	57	50	46	67	57	50	46	56	50	46	55	49	45	54	49	45	44				44
10	65	54	47	42	63	53	47	42	52	46	42	51	46	42	51	46	42	41				41

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	9151	9151	9151
5°	9003	8981	9048
10°	8424	8537	8775
15°	7659	7901	8341
20°	6798	7152	7778
25°	5920	6389	7146
30°	5071	5628	6548
35°	4205	4778	5825
40°	3230	3820	4965
45°	2336	2893	3994
50°	1590	2156	3168
55°	1034	1559	2463
60°	592	1098	1779
65°	157	670	902
70°	78	208	259
75°	36	18	0
80°	27	0	0
85°	0	0	0



TEST NUMBER: P518588

CATALOG NUMBER: SQ4-BB-0U-050D-830-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	90.5	7.7
10°-20°	231.5	19.6
20°-30°	289.8	24.5
30°-40°	267.7	22.6
40°-50°	179.8	15.2
50°-60°	92.9	7.9
60°-70°	29.1	2.5
70°-80°	1.8	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	611.8	51.7
0°-40°	879.4	74.3
0°-60°	1152.1	97.4
0°-90°	1183.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1183.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	992	992	992	992	992	
5°	972	962	970	973	977	90
15°	802	799	827	855	873	223
25°	582	586	628	670	702	267
35°	373	383	424	474	517	231
45°	179	190	222	265	306	141
55°	64	75	97	124	153	60
65°	7	14	31	37	41	12
75°	1	1	0	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P518588

CATALOG NUMBER: SQ4-BB-0U-050D-830-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	991.8	991.8	991.8	991.8	991.8
2.5°	994.1	984.7	987.2	987.1	984.5
5°	972.1	962.3	969.7	973.2	976.9
7.5°	931.0	923.3	937.7	948.4	956.2
10°	899.2	892.6	911.2	925.8	936.6
12.5°	862.3	857.3	879.7	899.8	913.6
15°	801.8	799.0	827.2	855.0	873.3
17.5°	736.9	736.8	769.1	803.5	825.6
20°	692.4	693.8	728.4	766.4	792.2
22.5°	647.8	651.1	688.1	727.7	757.2
25°	581.5	586.2	627.6	670.5	702.0
27.5°	517.8	524.7	568.2	612.8	651.1
30°	476.0	484.0	528.3	575.2	614.6
32.5°	434.9	444.4	487.6	537.3	577.4
35°	373.3	382.7	424.2	474.1	517.2
37.5°	309.7	318.9	359.4	408.5	455.2
40°	268.2	278.5	317.2	364.8	412.2
42.5°	230.6	240.9	277.2	324.0	368.8
45°	179.0	189.8	221.7	264.8	306.1
47.5°	136.2	147.9	175.9	214.9	252.6
50°	110.8	122.6	150.2	184.6	220.7
52.5°	90.5	101.8	126.8	159.2	192.3
55°	64.3	75.1	96.9	124.4	153.1
57.5°	44.4	53.7	73.3	96.3	118.7
60°	32.1	41.1	59.5	78.1	96.4
62.5°	21.4	29.6	47.6	61.9	74.2
65°	7.2	13.8	30.7	37.0	41.3
67.5°	3.6	4.4	16.1	17.0	18.4
70°	2.9	2.9	7.7	8.2	9.6
72.5°	2.1	2.1	3.1	3.9	4.2
75°	1.0	1.0	0.5	0.0	0.0
77.5°	0.5	0.5	0.4	0.0	0.0
80°	0.5	0.5	0.0	0.0	0.0
82.5°	0.1	0.1	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)