

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562818

Luminaire Tested: **SQ4-PC3-0U-075D-830-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562818
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-0U-075D-830-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2737.8 lumens
Efficiency: N/A
Efficacy: 114.1 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 24
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562818
CATALOG NUMBER: SQ4-PC3-0U-075D-830-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P562818

CATALOG NUMBER: SQ4-PC3-0U-075D-830-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	88	87	85
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73	71
3	91	80	72	66	88	79	71	65	76	70	64	73	68	63	71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	53	51
5	77	64	55	48	74	63	54	48	61	53	48	59	52	47	57	51	47	44
6	71	58	49	42	69	57	48	42	55	47	42	53	46	41	52	46	41	39
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	34
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	31
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	29	28
10	54	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	27	25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9256	9256	9256
5°	9325	9265	9231
10°	9302	9259	9233
15°	9254	9254	9245
20°	9193	9220	9220
25°	9106	9172	9144
30°	8995	9103	9064
35°	8861	8997	8934
40°	8715	8838	8749
45°	8557	8617	8484
50°	8332	8332	8199
55°	8068	7964	7843
60°	7678	7525	7405
65°	7097	6955	6894
70°	6215	6264	6239
75°	5001	5529	5561
80°	3555	4686	4739
85°	2160	3938	3938



TEST NUMBER: P562818

CATALOG NUMBER: SQ4-PC3-0U-075D-830-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.9	3.5
10°-20°	272.4	10.0
20°-30°	412.6	15.1
30°-40°	494.6	18.1
40°-50°	504.4	18.4
50°-60°	440.3	16.1
60°-70°	315.2	11.5
70°-80°	162.3	5.9
80°-90°	41.1	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	780.0	28.5
0°-40°	1274.6	46.6
0°-60°	2219.2	81.1
0°-90°	2737.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2737.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1003	1003	1003	1003	1003	
5°	1007	997	1000	998	997	96
15°	969	961	969	969	968	273
25°	894	888	901	898	898	412
35°	787	785	799	793	793	492
45°	656	654	660	652	650	505
55°	502	495	495	488	488	447
65°	325	318	319	316	316	322
75°	140	147	155	156	156	152
85°	20	31	37	38	37	29
90°	0	0	0	0	0	



TEST NUMBER: P562818

CATALOG NUMBER: SQ4-PC3-0U-075D-830-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1003.2	1003.2	1003.2	1003.2	1003.2
2.5°	1009.1	1000.4	1003.2	1000.8	997.2
5°	1006.9	996.9	1000.4	997.6	996.7
7.5°	999.6	989.6	994.2	992.4	991.5
10°	992.9	982.9	988.3	986.4	985.5
12.5°	984.0	974.8	980.9	979.0	978.8
15°	968.8	960.6	968.8	968.8	967.9
17.5°	949.7	942.2	951.0	951.5	951.0
20°	936.3	928.1	939.1	938.2	939.1
22.5°	919.9	913.2	924.9	922.6	923.5
25°	894.5	888.1	901.0	898.2	898.2
27.5°	864.4	859.8	873.9	870.9	870.9
30°	844.3	839.8	854.5	850.8	850.8
32.5°	822.0	818.9	833.0	828.5	828.5
35°	786.7	784.9	798.8	793.2	793.2
37.5°	750.3	748.7	761.3	754.5	752.4
40°	723.6	722.7	733.8	726.4	726.4
42.5°	696.8	695.9	705.6	696.6	696.6
45°	655.8	654.0	660.4	652.0	650.2
47.5°	611.0	609.2	613.2	604.1	603.2
50°	580.5	578.7	580.5	572.2	571.2
52.5°	549.3	546.1	546.3	538.0	537.8
55°	501.6	495.2	495.1	487.6	487.6
57.5°	451.0	442.7	443.4	437.1	436.2
60°	416.1	407.0	407.8	402.2	401.3
62.5°	381.9	371.4	373.6	367.3	367.1
65°	325.1	317.8	318.6	315.8	315.8
67.5°	270.5	263.8	268.6	266.4	266.2
70°	230.4	225.8	232.2	232.2	231.3
72.5°	193.2	193.0	201.0	201.0	201.6
75°	140.3	146.6	155.1	156.0	156.0
77.5°	93.6	104.9	114.2	114.6	114.4
80°	66.9	79.6	88.2	90.1	89.2
82.5°	45.3	58.8	65.9	67.8	66.9
85°	20.4	31.3	37.2	38.1	37.2
87.5°	5.9	12.5	14.9	14.8	13.4
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)