

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562842

Luminaire Tested: **SQ4-PC3-0U-100D-830-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562842
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-0U-100D-830-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3637.7 lumens
Efficiency: N/A
Efficacy: 110.9 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562842
CATALOG NUMBER: SQ4-PC3-0U-100D-830-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P562842

CATALOG NUMBER: SQ4-PC3-0U-100D-830-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	88	87	85
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73	71
3	91	80	72	66	88	79	71	65	76	70	64	73	68	63	71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	53	51
5	77	64	55	48	74	63	54	48	61	53	48	59	52	47	57	51	47	44
6	71	58	49	42	69	57	48	42	55	47	42	53	46	41	52	46	41	39
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	34
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	31
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	29	28
10	54	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	27	25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12298	12298	12298
5°	12390	12310	12265
10°	12360	12303	12267
15°	12295	12295	12283
20°	12214	12250	12250
25°	12099	12186	12149
30°	11952	12096	12044
35°	11773	11955	11871
40°	11579	11743	11624
45°	11369	11449	11272
50°	11072	11072	10894
55°	10719	10581	10422
60°	10202	9998	9839
65°	9431	9241	9160
70°	8257	8322	8290
75°	6645	7347	7390
80°	4723	6227	6296
85°	2879	5229	5229



TEST NUMBER: P562842

CATALOG NUMBER: SQ4-PC3-0U-100D-830-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.1	3.5
10°-20°	362.0	10.0
20°-30°	548.2	15.1
30°-40°	657.2	18.1
40°-50°	670.1	18.4
50°-60°	585.0	16.1
60°-70°	418.8	11.5
70°-80°	215.7	5.9
80°-90°	54.6	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1036.3	28.5
0°-40°	1693.6	46.6
0°-60°	2948.7	81.1
0°-90°	3637.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3637.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1333	1333	1333	1333	1333	
5°	1338	1325	1329	1326	1324	127
15°	1287	1276	1287	1287	1286	363
25°	1188	1180	1197	1193	1193	547
35°	1045	1043	1061	1054	1054	654
45°	871	869	878	866	864	671
55°	666	658	658	648	648	594
65°	432	422	423	420	420	427
75°	186	195	206	207	207	201
85°	27	42	49	51	49	38
90°	0	0	0	0	0	



TEST NUMBER: P562842

CATALOG NUMBER: SQ4-PC3-0U-100D-830-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1332.9	1332.9	1332.9	1332.9	1332.9
2.5°	1340.8	1329.2	1332.9	1329.8	1325.0
5°	1337.8	1324.6	1329.2	1325.5	1324.3
7.5°	1328.2	1314.9	1321.0	1318.6	1317.3
10°	1319.3	1306.0	1313.2	1310.7	1309.4
12.5°	1307.5	1295.2	1303.3	1300.8	1300.6
15°	1287.2	1276.4	1287.2	1287.2	1286.0
17.5°	1261.8	1251.9	1263.5	1264.3	1263.5
20°	1244.0	1233.2	1247.7	1246.5	1247.7
22.5°	1222.3	1213.4	1229.0	1225.8	1227.0
25°	1188.5	1180.1	1197.1	1193.4	1193.4
27.5°	1148.5	1142.5	1161.1	1157.2	1157.2
30°	1121.9	1115.8	1135.4	1130.5	1130.5
32.5°	1092.2	1088.1	1106.8	1100.9	1100.9
35°	1045.3	1042.9	1061.4	1054.0	1054.0
37.5°	997.0	994.8	1011.5	1002.6	999.7
40°	961.4	960.2	975.0	965.1	965.1
42.5°	925.9	924.7	937.5	925.6	925.6
45°	871.3	868.9	877.5	866.3	863.9
47.5°	811.8	809.4	814.8	802.7	801.5
50°	771.4	768.9	771.4	760.2	759.0
52.5°	729.9	725.5	725.9	714.8	714.6
55°	666.4	658.0	657.8	647.9	647.9
57.5°	599.3	588.2	589.2	580.8	579.6
60°	552.9	540.8	541.8	534.4	533.2
62.5°	507.5	493.5	496.4	488.0	487.7
65°	432.0	422.3	423.3	419.6	419.6
67.5°	359.4	350.5	356.9	354.0	353.7
70°	306.1	300.0	308.5	308.5	307.3
72.5°	256.7	256.5	267.1	267.1	267.8
75°	186.4	194.8	206.1	207.3	207.3
77.5°	124.4	139.4	151.8	152.3	152.0
80°	88.9	105.8	117.2	119.7	118.5
82.5°	60.2	78.1	87.6	90.1	88.9
85°	27.2	41.6	49.4	50.6	49.4
87.5°	7.9	16.6	19.7	19.7	17.8
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)