

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562890

Luminaire Tested: **SQ4-PC3-100U-050D-830-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562890
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-100U-050D-830-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5649.7 lumens
Efficiency: N/A
Efficacy: 136.8 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 41.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562890
CATALOG NUMBER: SQ4-PC3-100U-050D-830-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P562890

CATALOG NUMBER: SQ4-PC3-100U-050D-830-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	33				
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34	28				
2	86	78	72	67	77	71	66	62	57	53	50	44	41	39	31	30	29	23				
3	78	69	62	56	70	62	56	51	50	46	42	38	36	33	28	26	24	20				
4	71	61	53	47	64	55	48	43	44	39	36	34	31	28	25	23	21	17				
5	65	54	46	40	59	49	42	37	39	34	31	31	27	24	22	20	18	15				
6	60	48	40	35	54	44	37	32	35	30	27	28	24	21	20	18	16	13				
7	55	43	36	30	50	40	33	28	32	27	23	25	21	19	18	16	14	11				
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	14	13	10				
9	48	36	29	24	43	33	26	22	27	22	18	21	17	15	16	13	11	9				
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10	8				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6279	6279	6279
5°	6326	6286	6263
10°	6312	6282	6264
15°	6278	6278	6273
20°	6237	6255	6255
25°	6178	6223	6204
30°	6103	6177	6150
35°	6012	6105	6062
40°	5912	5997	5935
45°	5805	5847	5755
50°	5654	5654	5563
55°	5474	5403	5323
60°	5209	5106	5023
65°	4816	4720	4678
70°	4216	4251	4232
75°	3394	3750	3775
80°	2412	3183	3214
85°	1471	2668	2668



TEST NUMBER: P562890

CATALOG NUMBER: SQ4-PC3-100U-050D-830-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.4	1.1
10°-20°	184.8	3.3
20°-30°	279.9	5.0
30°-40°	335.6	5.9
40°-50°	342.2	6.1
50°-60°	298.7	5.3
60°-70°	213.9	3.8
70°-80°	110.2	1.9
80°-90°	29.1	0.5
90°-100°	273.2	4.8
100°-110°	754.3	13.4
110°-120°	777.9	13.8
120°-130°	625.1	11.1
130°-140°	491.3	8.7
140°-150°	376.8	6.7
150°-160°	270.8	4.8
160°-170°	165.6	2.9
170°-180°	55.8	1.0
0°-30°	529.2	9.4
0°-40°	864.8	15.3
0°-60°	1505.7	26.7
0°-90°	1858.8	32.9
90°-120°	1805.5	32.0
90°-150°	3298.7	58.4
90°-180°	3791.0	67.1
0°-180°	5649.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	681	681	681	681	681	
5°	683	676	679	677	676	65
15°	657	652	657	657	657	185
25°	607	603	611	609	609	279
35°	534	533	542	538	538	334
45°	445	444	448	442	441	342
55°	340	336	336	331	331	303
65°	221	216	216	214	214	218
75°	95	100	105	106	106	103
85°	14	21	25	26	25	19
90°	2	4	8	8	9	3
95°	40	148	496	204	133	43
105°	134	207	830	1267	1193	143
115°	241	291	668	1323	1505	237
125°	330	376	606	1025	1203	294
135°	398	441	589	830	936	308
145°	461	493	582	707	761	289
155°	520	537	577	634	654	240
165°	563	570	580	602	607	159
175°	584	584	581	589	587	55
180°	584	584	584	584	584	

TEST NUMBER: P562890

CATALOG NUMBER: SQ4-PC3-100U-050D-830-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	680.6	680.6	680.6	680.6	680.6
2.5°	684.7	678.7	680.6	679.1	676.6
5°	683.1	676.4	678.7	676.8	676.2
7.5°	678.2	671.4	674.6	673.3	672.7
10°	673.7	666.9	670.5	669.3	668.6
12.5°	667.6	661.4	665.5	664.2	664.1
15°	657.3	651.8	657.3	657.3	656.7
17.5°	644.3	639.3	645.2	645.6	645.2
20°	635.2	629.7	637.1	636.5	637.1
22.5°	624.2	619.6	627.6	625.9	626.5
25°	606.9	602.6	611.3	609.4	609.4
27.5°	586.5	583.4	592.9	590.9	590.9
30°	572.9	569.8	579.8	577.3	577.3
32.5°	557.7	555.6	565.2	562.1	562.1
35°	533.8	532.6	542.0	538.2	538.2
37.5°	509.1	508.0	516.5	511.9	510.5
40°	490.9	490.3	497.9	492.8	492.8
42.5°	472.8	472.2	478.7	472.7	472.7
45°	444.9	443.7	448.1	442.4	441.1
47.5°	414.5	413.3	416.1	409.9	409.3
50°	393.9	392.6	393.9	388.2	387.6
52.5°	372.7	370.5	370.7	365.0	364.9
55°	340.3	336.0	335.9	330.9	330.9
57.5°	306.0	300.4	300.9	296.6	295.9
60°	282.3	276.2	276.7	272.9	272.2
62.5°	259.1	252.0	253.5	249.2	249.1
65°	220.6	215.6	216.2	214.3	214.3
67.5°	183.5	179.0	182.3	180.7	180.6
70°	156.3	153.2	157.6	157.5	156.9
72.5°	131.1	131.0	136.4	136.4	136.8
75°	95.2	99.5	105.2	105.9	105.9
77.5°	63.5	71.2	77.5	77.8	77.6
80°	45.4	54.0	59.9	61.1	60.5
82.5°	30.8	39.9	44.7	46.0	45.4
85°	13.9	21.3	25.2	25.8	25.2
87.5°	4.4	9.2	11.6	11.7	10.9
90°	1.9	3.7	7.5	8.4	9.3
92.5°	16.8	69.7	124.7	45.5	35.5
95°	40.1	147.8	495.7	203.8	132.6
97.5°	66.5	165.6	734.3	565.3	409.4
100°	85.9	176.2	822.4	828.2	673.1
102.5°	104.6	188.3	839.6	1023.3	876.2
105°	134.4	207.4	829.9	1267.0	1193.0
107.5°	166.2	231.2	783.6	1384.5	1411.5
110°	188.6	247.0	747.8	1409.7	1497.4



TEST NUMBER: P562890

CATALOG NUMBER: SQ4-PC3-100U-050D-830-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	208.7	265.0	714.1	1389.8	1519.0
115°	240.8	291.1	668.4	1323.2	1504.8
117.5°	268.9	318.9	638.3	1229.5	1436.1
120°	287.5	336.8	626.4	1166.0	1374.1
122.5°	305.4	352.5	616.7	1106.8	1303.9
125°	330.5	376.1	605.9	1025.3	1203.3
127.5°	351.8	397.4	599.5	956.4	1110.0
130°	365.9	411.6	596.5	914.3	1053.9
132.5°	379.4	422.8	593.5	878.9	1005.4
135°	397.7	440.6	589.1	830.4	936.3
137.5°	418.2	457.3	586.8	789.8	880.1
140°	429.4	467.8	585.3	762.6	842.0
142.5°	442.1	477.5	583.8	738.5	808.4
145°	461.2	493.1	581.6	707.0	760.8
147.5°	479.5	507.4	579.5	680.4	722.2
150°	492.9	515.7	578.8	664.5	698.3
152.5°	503.4	524.7	578.0	650.9	678.9
155°	520.0	537.3	576.9	634.3	654.4
157.5°	535.3	548.6	577.1	622.2	635.9
160°	544.2	556.1	577.9	615.4	625.5
162.5°	551.7	562.1	578.6	609.4	617.2
165°	562.9	570.2	579.7	602.2	606.8
167.5°	571.5	575.9	580.7	597.9	599.3
170°	576.0	579.6	580.7	595.6	595.6
172.5°	579.7	581.9	580.7	592.6	591.9
175°	583.5	584.4	580.7	589.0	587.2
177.5°	584.9	584.2	580.5	585.7	584.2
180°	583.5	583.5	583.5	583.5	583.5

(END OF REPORT)