

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P563082

Luminaire Tested: **SQ4-PC3-150U-050D-830-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563082
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-150U-050D-830-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7545.4 lumens
Efficiency: N/A
Efficacy: 135.5 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 55.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563082
CATALOG NUMBER: SQ4-PC3-150U-050D-830-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P563082

CATALOG NUMBER: SQ4-PC3-150U-050D-830-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33	25				25
1	92	88	84	81	82	78	75	73	61	59	57	44	43	42	29	28	28	21				21
2	84	77	71	66	74	69	64	59	53	50	47	39	37	35	26	24	23	17				17
3	76	67	60	55	68	60	54	50	47	43	39	34	32	29	23	21	20	15				15
4	70	59	52	46	62	53	47	42	41	37	33	30	27	25	20	18	17	13				13
5	64	53	45	39	57	47	41	36	37	32	29	27	24	22	18	16	15	11				11
6	59	47	39	34	52	42	36	31	33	28	25	24	21	19	16	14	13	10				10
7	54	42	35	29	48	38	31	27	30	25	22	22	19	16	15	13	11	8				8
8	50	38	31	26	44	34	28	24	27	22	19	20	17	15	14	12	10	8				8
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	13	11	9	7				7
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	8	6				6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6279	6279	6279
5°	6326	6286	6263
10°	6312	6282	6264
15°	6278	6278	6273
20°	6237	6255	6255
25°	6178	6223	6204
30°	6103	6177	6150
35°	6012	6105	6062
40°	5912	5997	5935
45°	5805	5847	5755
50°	5654	5654	5563
55°	5474	5403	5323
60°	5209	5106	5023
65°	4816	4720	4678
70°	4216	4251	4232
75°	3394	3750	3775
80°	2412	3183	3214
85°	1471	2668	2668



TEST NUMBER: P563082

CATALOG NUMBER: SQ4-PC3-150U-050D-830-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.4	0.9
10°-20°	184.8	2.4
20°-30°	279.9	3.7
30°-40°	335.6	4.4
40°-50°	342.2	4.5
50°-60°	298.7	4.0
60°-70°	213.9	2.8
70°-80°	110.2	1.5
80°-90°	29.7	0.4
90°-100°	409.8	5.4
100°-110°	1108.2	14.7
110°-120°	1165.1	15.4
120°-130°	946.4	12.5
130°-140°	742.3	9.8
140°-150°	569.7	7.6
150°-160°	409.7	5.4
160°-170°	250.3	3.3
170°-180°	84.4	1.1
0°-30°	529.2	7.0
0°-40°	864.8	11.5
0°-60°	1505.7	20.0
0°-90°	1859.4	24.6
90°-120°	2683.1	35.6
90°-150°	4941.5	65.5
90°-180°	5686.0	75.4
0°-180°	7545.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	681	681	681	681	681	
5°	683	676	679	677	676	65
15°	657	652	657	657	657	185
25°	607	603	611	609	609	279
35°	534	533	542	538	538	334
45°	445	444	448	442	441	342
55°	340	336	336	331	331	303
65°	221	216	216	214	214	218
75°	95	100	105	106	106	103
85°	14	21	25	26	25	19
90°	2	6	12	13	12	5
95°	64	223	682	353	210	67
105°	206	318	1229	1813	1739	217
115°	363	443	1020	1974	2228	358
125°	496	569	919	1551	1822	443
135°	595	666	894	1252	1417	460
145°	692	744	882	1072	1153	433
155°	781	812	874	961	993	360
165°	851	859	878	912	917	240
175°	883	882	879	890	888	84
180°	882	882	882	882	882	



TEST NUMBER: P563082

CATALOG NUMBER: SQ4-PC3-150U-050D-830-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	680.6	680.6	680.6	680.6	680.6
2.5°	684.7	678.7	680.6	679.1	676.6
5°	683.1	676.4	678.7	676.8	676.2
7.5°	678.2	671.4	674.6	673.3	672.7
10°	673.7	666.9	670.5	669.3	668.6
12.5°	667.6	661.4	665.5	664.2	664.1
15°	657.3	651.8	657.3	657.3	656.7
17.5°	644.3	639.3	645.2	645.6	645.2
20°	635.2	629.7	637.1	636.5	637.1
22.5°	624.2	619.6	627.6	625.9	626.5
25°	606.9	602.6	611.3	609.4	609.4
27.5°	586.5	583.4	592.9	590.9	590.9
30°	572.9	569.8	579.8	577.3	577.3
32.5°	557.7	555.6	565.2	562.1	562.1
35°	533.8	532.6	542.0	538.2	538.2
37.5°	509.1	508.0	516.5	511.9	510.5
40°	490.9	490.3	497.9	492.8	492.8
42.5°	472.8	472.2	478.7	472.7	472.7
45°	444.9	443.7	448.1	442.4	441.1
47.5°	414.5	413.3	416.1	409.9	409.3
50°	393.9	392.6	393.9	388.2	387.6
52.5°	372.7	370.5	370.7	365.0	364.9
55°	340.3	336.0	335.9	330.9	330.9
57.5°	306.0	300.4	300.9	296.6	295.9
60°	282.3	276.2	276.7	272.9	272.2
62.5°	259.1	252.0	253.5	249.2	249.1
65°	220.6	215.6	216.2	214.3	214.3
67.5°	183.5	179.0	182.3	180.7	180.6
70°	156.3	153.2	157.6	157.5	156.9
72.5°	131.1	131.0	136.4	136.4	136.8
75°	95.2	99.5	105.2	105.9	105.9
77.5°	63.5	71.2	77.5	77.8	77.6
80°	45.4	54.0	59.9	61.1	60.5
82.5°	30.8	39.9	44.7	46.0	45.4
85°	13.9	21.3	25.2	25.8	25.2
87.5°	4.4	9.6	12.6	12.7	11.5
90°	1.9	5.6	12.3	13.3	12.3
92.5°	27.0	98.2	193.8	84.2	60.9
95°	63.6	223.3	681.6	352.7	209.8
97.5°	102.1	256.0	1062.5	879.3	645.7
100°	131.0	269.3	1180.9	1231.6	995.8
102.5°	157.6	287.7	1222.7	1498.7	1322.4
105°	206.0	318.3	1229.3	1813.4	1739.1
107.5°	250.8	353.3	1175.6	2009.7	2034.4
110°	285.7	378.6	1127.8	2062.4	2167.3



TEST NUMBER: P563082

CATALOG NUMBER: SQ4-PC3-150U-050D-830-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	316.9	403.8	1083.7	2051.8	2228.0
115°	362.6	443.4	1019.6	1973.7	2228.0
117.5°	407.4	483.2	977.2	1854.3	2142.6
120°	434.8	509.0	952.2	1768.6	2062.8
122.5°	460.6	533.4	937.0	1676.8	1973.2
125°	496.5	568.9	918.9	1550.7	1821.7
127.5°	529.5	600.6	908.3	1447.8	1686.2
130°	547.7	621.1	903.7	1384.2	1599.6
132.5°	566.7	639.3	899.2	1326.9	1525.2
135°	595.2	665.8	894.2	1252.1	1417.3
137.5°	623.9	690.5	890.1	1191.4	1326.0
140°	643.6	705.8	888.5	1152.3	1272.1
142.5°	662.6	721.1	885.5	1117.1	1221.9
145°	692.0	744.0	881.9	1071.7	1153.4
147.5°	718.8	764.9	877.7	1030.7	1093.4
150°	738.6	779.4	876.2	1008.4	1058.5
152.5°	756.8	792.4	875.4	987.6	1028.9
155°	781.3	811.9	874.3	961.4	993.0
157.5°	806.7	828.1	874.5	943.1	963.9
160°	821.1	838.8	875.3	931.6	946.5
162.5°	832.5	847.2	876.0	922.4	933.5
165°	850.6	858.9	878.1	912.4	917.0
167.5°	862.9	868.7	878.3	903.8	906.0
170°	870.5	873.3	879.1	899.9	899.9
172.5°	876.6	877.1	879.1	895.4	894.6
175°	882.9	881.9	879.1	890.4	888.5
177.5°	884.9	882.7	878.9	886.4	884.2
180°	881.9	881.9	881.9	881.9	881.9

(END OF REPORT)