

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563106

Luminaire Tested: **SQ4-PC3-150U-075D-830-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563106  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2106-289-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PC3-150U-075D-830-1D-UNV-STD-W-4  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 1500 LUMENS PER FOOT  
Light Source: 3000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8425.6 lumens  
Efficiency: N/A  
Efficacy: 132.7 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 63.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563106  
CATALOG NUMBER: SQ4-PC3-150U-075D-830-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P563106

CATALOG NUMBER: SQ4-PC3-150U-075D-830-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	33
1	94	90	86	83	84	81	78	75	64	62	60	49	48	47	35	35	34	27
2	85	78	72	67	77	71	66	61	56	53	50	43	41	39	31	30	29	23
3	78	69	62	56	70	62	56	51	50	45	42	38	35	33	28	26	24	19
4	71	61	53	47	64	55	48	43	44	39	36	34	31	28	25	23	21	17
5	65	54	46	40	58	49	42	37	39	34	31	30	27	24	22	20	18	14
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	18	16	13
7	55	43	36	30	50	39	33	28	32	27	23	25	21	19	18	16	14	11
8	51	39	32	27	46	36	29	25	29	24	20	23	19	16	17	14	13	10
9	48	36	28	24	43	33	26	22	26	22	18	21	17	15	15	13	11	9
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	9256	9256	9256
5°	9325	9265	9231
10°	9302	9259	9233
15°	9254	9254	9245
20°	9193	9220	9220
25°	9106	9172	9144
30°	8995	9103	9064
35°	8861	8997	8934
40°	8715	8838	8749
45°	8557	8617	8484
50°	8332	8332	8199
55°	8068	7964	7843
60°	7678	7525	7405
65°	7097	6955	6894
70°	6215	6264	6239
75°	5001	5529	5561
80°	3555	4686	4739
85°	2160	3938	3938



TEST NUMBER: P563106

CATALOG NUMBER: SQ4-PC3-150U-075D-830-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	94.9	1.1
10°-20°	272.4	3.2
20°-30°	412.6	4.9
30°-40°	494.6	5.9
40°-50°	504.4	6.0
50°-60°	440.3	5.2
60°-70°	315.2	3.7
70°-80°	162.3	1.9
80°-90°	42.9	0.5
90°-100°	409.8	4.9
100°-110°	1108.2	13.2
110°-120°	1165.1	13.8
120°-130°	946.4	11.2
130°-140°	742.3	8.8
140°-150°	569.7	6.8
150°-160°	409.7	4.9
160°-170°	250.3	3.0
170°-180°	84.4	1.0
0°-30°	780.0	9.3
0°-40°	1274.6	15.1
0°-60°	2219.2	26.3
0°-90°	2739.6	32.5
90°-120°	2683.1	31.8
90°-150°	4941.5	58.6
90°-180°	5686.0	67.5
0°-180°	8425.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1003	1003	1003	1003	1003	
5°	1007	997	1000	998	997	96
15°	969	961	969	969	968	273
25°	894	888	901	898	898	412
35°	787	785	799	793	793	492
45°	656	654	660	652	650	505
55°	502	495	495	488	488	447
65°	325	318	319	316	316	322
75°	140	147	155	156	156	152
85°	20	31	37	38	37	28
90°	2	6	12	13	12	5
95°	64	223	682	353	210	67
105°	206	318	1229	1813	1739	217
115°	363	443	1020	1974	2228	358
125°	496	569	919	1551	1822	443
135°	595	666	894	1252	1417	460
145°	692	744	882	1072	1153	433
155°	781	812	874	961	993	360
165°	851	859	878	912	917	240
175°	883	882	879	890	888	84
180°	882	882	882	882	882	

TEST NUMBER: P563106

CATALOG NUMBER: SQ4-PC3-150U-075D-830-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1003.2	1003.2	1003.2	1003.2	1003.2
2.5°	1009.1	1000.4	1003.2	1000.8	997.2
5°	1006.9	996.9	1000.4	997.6	996.7
7.5°	999.6	989.6	994.2	992.4	991.5
10°	992.9	982.9	988.3	986.4	985.5
12.5°	984.0	974.8	980.9	979.0	978.8
15°	968.8	960.6	968.8	968.8	967.9
17.5°	949.7	942.2	951.0	951.5	951.0
20°	936.3	928.1	939.1	938.2	939.1
22.5°	919.9	913.2	924.9	922.6	923.5
25°	894.5	888.1	901.0	898.2	898.2
27.5°	864.4	859.8	873.9	870.9	870.9
30°	844.3	839.8	854.5	850.8	850.8
32.5°	822.0	818.9	833.0	828.5	828.5
35°	786.7	784.9	798.8	793.2	793.2
37.5°	750.3	748.7	761.3	754.5	752.4
40°	723.6	722.7	733.8	726.4	726.4
42.5°	696.8	695.9	705.6	696.6	696.6
45°	655.8	654.0	660.4	652.0	650.2
47.5°	611.0	609.2	613.2	604.1	603.2
50°	580.5	578.7	580.5	572.2	571.2
52.5°	549.3	546.1	546.3	538.0	537.8
55°	501.6	495.2	495.1	487.6	487.6
57.5°	451.0	442.7	443.4	437.1	436.2
60°	416.1	407.0	407.8	402.2	401.3
62.5°	381.9	371.4	373.6	367.3	367.1
65°	325.1	317.8	318.6	315.8	315.8
67.5°	270.5	263.8	268.6	266.4	266.2
70°	230.4	225.8	232.2	232.2	231.3
72.5°	193.2	193.0	201.0	201.0	201.6
75°	140.3	146.6	155.1	156.0	156.0
77.5°	93.6	104.9	114.2	114.6	114.4
80°	66.9	79.6	88.2	90.1	89.2
82.5°	45.3	58.8	65.9	67.8	66.9
85°	20.4	31.3	37.2	38.1	37.2
87.5°	6.3	13.6	17.3	17.5	15.8
90°	1.9	5.6	12.3	13.3	12.3
92.5°	27.0	98.2	193.8	84.2	60.9
95°	63.6	223.3	681.6	352.7	209.8
97.5°	102.1	256.0	1062.5	879.3	645.7
100°	131.0	269.3	1180.9	1231.6	995.8
102.5°	157.6	287.7	1222.7	1498.7	1322.4
105°	206.0	318.3	1229.3	1813.4	1739.1
107.5°	250.8	353.3	1175.6	2009.7	2034.4
110°	285.7	378.6	1127.8	2062.4	2167.3



TEST NUMBER: P563106

CATALOG NUMBER: SQ4-PC3-150U-075D-830-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	316.9	403.8	1083.7	2051.8	2228.0
115°	362.6	443.4	1019.6	1973.7	2228.0
117.5°	407.4	483.2	977.2	1854.3	2142.6
120°	434.8	509.0	952.2	1768.6	2062.8
122.5°	460.6	533.4	937.0	1676.8	1973.2
125°	496.5	568.9	918.9	1550.7	1821.7
127.5°	529.5	600.6	908.3	1447.8	1686.2
130°	547.7	621.1	903.7	1384.2	1599.6
132.5°	566.7	639.3	899.2	1326.9	1525.2
135°	595.2	665.8	894.2	1252.1	1417.3
137.5°	623.9	690.5	890.1	1191.4	1326.0
140°	643.6	705.8	888.5	1152.3	1272.1
142.5°	662.6	721.1	885.5	1117.1	1221.9
145°	692.0	744.0	881.9	1071.7	1153.4
147.5°	718.8	764.9	877.7	1030.7	1093.4
150°	738.6	779.4	876.2	1008.4	1058.5
152.5°	756.8	792.4	875.4	987.6	1028.9
155°	781.3	811.9	874.3	961.4	993.0
157.5°	806.7	828.1	874.5	943.1	963.9
160°	821.1	838.8	875.3	931.6	946.5
162.5°	832.5	847.2	876.0	922.4	933.5
165°	850.6	858.9	878.1	912.4	917.0
167.5°	862.9	868.7	878.3	903.8	906.0
170°	870.5	873.3	879.1	899.9	899.9
172.5°	876.6	877.1	879.1	895.4	894.6
175°	882.9	881.9	879.1	890.4	888.5
177.5°	884.9	882.7	878.9	886.4	884.2
180°	881.9	881.9	881.9	881.9	881.9

(END OF REPORT)