

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P853706

Luminaire Tested: SQ2-F-100U-050D-940-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P853706
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-12, G2-2308-131-13)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-F-100U-050D-940-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6373.1 lumens
Efficiency: N/A
Efficacy: 126.4 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.25 / 1.36
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 50.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P853706
CATALOG NUMBER: SQ2-F-100U-050D-940-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P853706

CATALOG NUMBER: SQ2-F-100U-050D-940-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	75	75	75	57	57	57	42	42	42	34
1	94	90	86	83	85	81	78	75	65	63	61	50	49	47	37	36	35	29
2	86	78	72	67	77	71	66	61	57	53	50	44	42	39	32	31	29	24
3	78	69	62	56	70	62	56	51	50	46	42	39	36	33	28	26	25	20
4	71	61	53	47	64	55	48	43	44	39	36	34	31	28	25	23	21	17
5	65	54	46	40	59	49	42	37	40	34	31	31	27	24	23	20	18	15
6	60	48	40	35	54	44	37	32	35	30	26	28	24	21	20	18	16	13
7	55	43	36	30	50	39	33	28	32	27	23	25	21	19	19	16	14	11
8	51	39	32	26	46	36	29	24	29	24	20	23	19	17	17	15	13	10
9	48	36	28	23	43	33	26	22	27	22	18	21	17	15	16	13	11	9
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	15	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12536	12536	12536
5°	12446	12481	12584
10°	12418	12452	12539
15°	12341	12376	12500
20°	12268	12287	12395
25°	12155	12155	12230
30°	12029	12029	12070
35°	11883	11842	11925
40°	11727	11683	11727
45°	11545	11497	11545
50°	11371	11266	11293
55°	11105	11077	11018
60°	10827	10760	10692
65°	10506	10384	10265
70°	9885	9838	9635
75°	9301	9108	8840
80°	8266	8061	7773
85°	6669	6076	5687

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 11615 cd/sqm



TEST NUMBER: P853706

CATALOG NUMBER: SQ2-F-100U-050D-940-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.4	1.2
10°-20°	209.7	3.3
20°-30°	315.5	5.0
30°-40°	377.5	5.9
40°-50°	389.5	6.1
50°-60°	351.4	5.5
60°-70°	268.1	4.2
70°-80°	154.2	2.4
80°-90°	41.4	0.6
90°-100°	281.3	4.4
100°-110°	850.9	13.4
110°-120°	830.6	13.0
120°-130°	678.7	10.7
130°-140°	554.0	8.7
140°-150°	431.3	6.8
150°-160°	310.9	4.9
160°-170°	190.3	3.0
170°-180°	64.3	1.0
0°-30°	598.6	9.4
0°-40°	976.1	15.3
0°-60°	1717.0	26.9
0°-90°	2180.7	34.2
90°-120°	1962.8	30.8
90°-150°	3626.9	56.9
90°-180°	4192.0	65.8
0°-180°	6373.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	776	776	776	776	776	
5°	768	778	770	771	776	73
15°	738	748	740	744	748	208
25°	682	690	682	683	686	314
35°	603	607	601	603	605	377
45°	506	509	504	505	506	390
55°	394	397	394	391	391	353
65°	275	274	272	270	269	270
75°	149	148	146	143	142	157
85°	36	34	33	30	31	42
90°	0	2	13	7	6	3
95°	35	110	531	196	124	41
105°	148	208	835	1587	1508	155
115°	263	314	676	1398	1642	260
125°	368	408	666	1104	1300	327
135°	441	488	662	952	1071	341
145°	515	553	662	819	896	323
155°	587	606	666	734	762	270
165°	642	649	669	695	703	181
175°	672	672	673	678	676	64
180°	674	674	674	674	674	



TEST NUMBER: P853706

CATALOG NUMBER: SQ2-F-100U-050D-940-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	776.4	776.4	776.4	776.4	776.4
2.5°	771.3	780.4	773.0	774.7	775.6
5°	767.9	778.3	770.1	771.2	776.4
7.5°	761.6	772.8	763.7	765.7	771.5
10°	757.4	767.7	759.5	760.6	764.8
12.5°	750.6	760.9	752.7	754.7	758.8
15°	738.3	747.6	740.4	743.7	747.8
17.5°	724.1	734.1	726.1	728.9	732.4
20°	714.0	722.3	715.1	716.2	721.4
22.5°	701.3	709.6	703.2	703.5	707.9
25°	682.3	689.5	682.3	683.4	686.5
27.5°	660.5	666.7	660.5	661.6	664.3
30°	645.2	651.4	645.2	646.3	647.4
32.5°	628.3	633.7	627.5	628.6	631.3
35°	602.9	607.1	600.8	603.0	605.0
37.5°	575.8	579.0	573.7	574.8	576.7
40°	556.4	559.5	554.3	555.4	556.4
42.5°	536.9	539.2	534.0	535.1	536.9
45°	505.6	508.7	503.5	504.6	505.6
47.5°	473.9	475.7	471.3	470.5	472.4
50°	452.7	453.8	448.5	448.5	449.6
52.5°	429.9	430.9	427.3	425.7	426.7
55°	394.5	396.6	393.5	391.4	391.4
57.5°	359.0	360.9	356.9	355.8	355.6
60°	335.3	336.3	333.2	332.1	331.1
62.5°	311.6	311.8	308.7	307.6	306.5
65°	275.0	274.0	271.8	269.7	268.7
67.5°	234.0	235.0	232.9	229.5	229.5
70°	209.4	210.5	208.4	204.1	204.1
72.5°	185.7	185.1	183.8	180.4	178.8
75°	149.1	148.1	146.0	142.8	141.7
77.5°	112.5	111.5	110.4	106.4	107.3
80°	88.9	87.8	86.7	83.6	83.6
82.5°	67.7	65.8	64.7	61.6	61.6
85°	36.0	33.9	32.8	29.6	30.7
87.5°	10.2	9.7	11.0	8.2	8.0
90°	0.0	2.1	12.7	7.4	6.3
92.5°	11.8	47.8	171.7	57.0	41.0
95°	34.9	110.4	530.9	196.1	123.7
97.5°	67.5	140.5	836.7	553.6	337.1
100°	87.8	159.1	934.8	903.8	607.0
102.5°	110.6	179.5	914.5	1267.6	1010.5
105°	148.0	208.0	835.4	1586.6	1508.0
107.5°	183.6	240.9	759.3	1618.1	1709.1
110°	207.3	262.1	721.2	1578.4	1743.8



TEST NUMBER: P853706

CATALOG NUMBER: SQ2-F-100U-050D-940-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	230.1	283.3	698.4	1511.7	1721.0
115°	263.3	314.0	675.7	1398.3	1642.3
117.5°	296.3	344.3	667.7	1292.0	1541.8
120°	318.3	363.8	665.2	1230.0	1469.9
122.5°	338.6	381.6	665.2	1175.5	1397.1
125°	368.0	408.3	666.2	1104.2	1299.6
127.5°	391.9	433.7	665.2	1050.5	1217.2
130°	407.1	450.6	665.2	1019.7	1170.6
132.5°	420.7	464.9	664.3	991.5	1130.9
135°	441.0	487.5	662.0	952.3	1071.2
137.5°	463.6	507.9	662.0	910.5	1020.7
140°	478.0	521.4	662.0	883.3	987.7
142.5°	492.4	534.1	661.1	858.4	949.6
145°	515.0	553.3	662.0	819.2	895.7
147.5°	537.6	570.1	663.3	786.8	845.6
150°	552.0	582.0	664.1	768.9	818.5
152.5°	565.5	592.2	664.9	753.4	794.0
155°	586.9	606.5	666.2	734.5	762.4
157.5°	605.5	621.4	667.5	720.6	740.0
160°	616.5	630.0	668.3	712.0	726.5
162.5°	627.5	637.6	669.2	704.3	716.3
165°	641.9	649.1	669.4	695.0	703.2
167.5°	654.2	657.9	670.7	687.7	691.2
170°	660.9	663.0	671.5	684.2	685.3
172.5°	665.2	666.4	671.5	680.8	681.0
175°	671.5	671.5	672.6	677.8	675.7
177.5°	674.5	673.6	672.8	675.3	673.6
180°	673.6	673.6	673.6	673.6	673.6



TEST NUMBER: P853706

CATALOG NUMBER: SQ2-F-100U-050D-940-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.09	15.83	16.17	16.91	18.39	15.01	15.75	16.09	16.84	18.32
	3H	16.86	17.53	17.95	18.62	20.11	16.74	17.41	17.83	18.50	19.99
	4H	17.51	18.15	18.61	19.24	20.74	17.36	17.99	18.46	19.09	20.59
	6H	17.98	18.56	19.09	19.65	21.17	17.79	18.37	18.90	19.47	20.98
	8H	18.11	18.67	19.23	19.78	21.28	17.91	18.46	19.02	19.57	21.08
	12H	18.18	18.71	19.30	19.81	21.34	17.96	18.49	19.08	19.59	21.12
4H	2H	15.63	16.26	16.73	17.35	18.85	15.57	16.20	16.67	17.29	18.79
	3H	17.60	18.13	18.72	19.25	20.76	17.49	18.02	18.61	19.14	20.66
	4H	18.39	18.87	19.51	19.98	21.52	18.24	18.73	19.36	19.84	21.37
	6H	18.97	19.39	20.10	20.52	22.04	18.79	19.21	19.92	20.34	21.86
	8H	19.16	19.54	20.28	20.67	22.21	18.95	19.34	20.08	20.46	22.01
	12H	19.25	19.60	20.39	20.74	22.29	19.02	19.38	20.17	20.51	22.06
8H	4H	18.63	19.01	19.75	20.14	21.68	18.50	18.89	19.62	20.01	21.55
	6H	19.34	19.66	20.48	20.82	22.36	19.17	19.49	20.32	20.66	22.20
	8H	19.60	19.88	20.76	21.03	22.59	19.41	19.69	20.56	20.84	22.40
	12H	19.77	20.01	20.92	21.15	22.75	19.54	19.79	20.70	20.93	22.52
12H	4H	18.61	18.96	19.75	20.10	21.65	18.49	18.84	19.63	19.98	21.53
	6H	19.38	19.66	20.53	20.80	22.37	19.22	19.50	20.37	20.65	22.21
	8H	19.67	19.91	20.82	21.05	22.65	19.48	19.73	20.64	20.87	22.47