

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P563802

Luminaire Tested: **SQ4-PP3-150U-100D-830-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563802
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-150U-100D-830-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9291.1 lumens
Efficiency: N/A
Efficacy: 128.5 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 72.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563802
CATALOG NUMBER: SQ4-PP3-150U-100D-830-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P563802

CATALOG NUMBER: SQ4-PP3-150U-100D-830-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	95	91	87	84	87	83	80	77	68	66	64	54	52	51	41	40	39	33
2	87	80	74	69	79	73	68	63	60	56	53	47	45	43	36	34	33	28
3	79	70	63	57	72	64	58	53	53	48	44	42	39	36	32	30	28	24
4	73	62	54	49	66	57	50	45	47	42	38	37	34	31	29	26	24	20
5	67	55	47	42	60	51	44	39	42	37	33	33	30	27	26	23	21	18
6	61	50	42	36	56	45	38	33	38	32	28	30	26	24	23	21	19	16
7	57	45	37	31	51	41	34	29	34	29	25	27	24	21	21	19	17	14
8	52	40	33	28	48	37	30	26	31	26	22	25	21	18	20	17	15	12
9	49	37	30	25	44	34	27	23	28	23	20	23	19	17	18	15	13	11
10	46	34	27	22	41	31	25	21	26	21	18	21	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12989	12989	12989
5°	13085	13004	12959
10°	13063	12970	12912
15°	12976	12905	12835
20°	12889	12817	12721
25°	12736	12649	12523
30°	12501	12435	12277
35°	12174	12091	11938
40°	11785	11710	11577
45°	11463	11382	11269
50°	11051	10980	10874
55°	10480	10340	10261
60°	9540	9267	9221
65°	8405	8053	8027
70°	7256	6957	6957
75°	6245	6156	6071
80°	5504	5574	5441
85°	4308	4700	4700



TEST NUMBER: P563802

CATALOG NUMBER: SQ4-PP3-150U-100D-830-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.1	1.4
10°-20°	380.1	4.1
20°-30°	569.4	6.1
30°-40°	667.8	7.2
40°-50°	669.9	7.2
50°-60°	571.5	6.2
60°-70°	372.7	4.0
70°-80°	187.0	2.0
80°-90°	53.6	0.6
90°-100°	409.8	4.4
100°-110°	1108.2	11.9
110°-120°	1165.1	12.5
120°-130°	946.4	10.2
130°-140°	742.3	8.0
140°-150°	569.7	6.1
150°-160°	409.7	4.4
160°-170°	250.3	2.7
170°-180°	84.4	0.9
0°-30°	1082.6	11.7
0°-40°	1750.4	18.8
0°-60°	2991.8	32.2
0°-90°	3605.1	38.8
90°-120°	2683.1	28.9
90°-150°	4941.5	53.2
90°-180°	5686.0	61.2
0°-180°	9291.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1408	1408	1408	1408	1408	
5°	1413	1400	1404	1399	1399	134
15°	1358	1345	1351	1346	1344	383
25°	1251	1237	1242	1231	1230	575
35°	1081	1070	1074	1061	1060	675
45°	878	872	872	864	864	676
55°	652	649	643	639	638	579
65°	385	378	369	366	368	384
75°	175	175	173	172	170	190
85°	41	44	44	44	44	48
90°	2	6	12	13	12	6
95°	64	223	682	353	210	67
105°	206	318	1229	1813	1739	217
115°	363	443	1020	1974	2228	358
125°	496	569	919	1551	1822	443
135°	595	666	894	1252	1417	460
145°	692	744	882	1072	1153	433
155°	781	812	874	961	993	360
165°	851	859	878	912	917	240
175°	883	882	879	890	888	84
180°	882	882	882	882	882	

TEST NUMBER: P563802

CATALOG NUMBER: SQ4-PP3-150U-100D-830-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1407.8	1407.8	1407.8	1407.8	1407.8
2.5°	1416.7	1405.1	1407.8	1405.7	1400.0
5°	1412.8	1399.5	1404.1	1399.2	1399.2
7.5°	1403.2	1388.7	1393.3	1388.3	1388.1
10°	1394.3	1379.8	1384.4	1379.4	1378.2
12.5°	1381.4	1367.0	1372.6	1366.6	1366.4
15°	1358.5	1345.2	1351.1	1346.1	1343.7
17.5°	1332.6	1318.1	1325.2	1318.2	1317.3
20°	1312.8	1298.4	1305.4	1295.6	1295.6
22.5°	1289.1	1274.7	1282.7	1269.9	1269.9
25°	1251.1	1236.7	1242.5	1231.4	1230.2
27.5°	1206.0	1191.7	1197.8	1185.3	1185.0
30°	1173.4	1160.1	1167.2	1153.6	1152.4
32.5°	1137.9	1125.6	1130.7	1117.1	1115.9
35°	1080.9	1070.0	1073.5	1061.1	1059.9
37.5°	1020.9	1009.8	1013.7	1003.1	1002.6
40°	978.5	971.2	972.3	963.6	961.2
42.5°	939.0	930.8	931.8	923.2	922.7
45°	878.5	872.5	872.3	863.7	863.7
47.5°	814.4	809.8	808.4	801.3	801.0
50°	769.9	766.3	765.0	758.8	757.6
52.5°	723.5	721.9	717.6	712.4	712.2
55°	651.5	649.1	642.8	639.1	637.9
57.5°	573.3	568.4	561.4	556.0	557.0
60°	517.0	512.2	502.2	499.7	499.7
62.5°	462.7	456.9	446.9	443.5	445.4
65°	385.0	377.7	368.9	366.5	367.7
67.5°	314.4	307.9	298.4	298.3	297.4
70°	269.0	265.4	257.9	257.9	257.9
72.5°	228.5	226.8	221.4	221.3	220.4
75°	175.2	175.2	172.7	171.5	170.3
77.5°	131.3	131.8	130.5	129.3	127.1
80°	103.6	106.1	104.9	103.6	102.4
82.5°	78.0	80.4	80.2	78.0	77.7
85°	40.7	44.3	44.4	44.4	44.4
87.5°	11.2	15.8	18.3	18.5	19.2
90°	1.9	5.6	12.3	13.3	12.3
92.5°	27.0	98.2	193.8	84.2	60.9
95°	63.6	223.3	681.6	352.7	209.8
97.5°	102.1	256.0	1062.5	879.3	645.7
100°	131.0	269.3	1180.9	1231.6	995.8
102.5°	157.6	287.7	1222.7	1498.7	1322.4
105°	206.0	318.3	1229.3	1813.4	1739.1
107.5°	250.8	353.3	1175.6	2009.7	2034.4
110°	285.7	378.6	1127.8	2062.4	2167.3



TEST NUMBER: P563802

CATALOG NUMBER: SQ4-PP3-150U-100D-830-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	316.9	403.8	1083.7	2051.8	2228.0
115°	362.6	443.4	1019.6	1973.7	2228.0
117.5°	407.4	483.2	977.2	1854.3	2142.6
120°	434.8	509.0	952.2	1768.6	2062.8
122.5°	460.6	533.4	937.0	1676.8	1973.2
125°	496.5	568.9	918.9	1550.7	1821.7
127.5°	529.5	600.6	908.3	1447.8	1686.2
130°	547.7	621.1	903.7	1384.2	1599.6
132.5°	566.7	639.3	899.2	1326.9	1525.2
135°	595.2	665.8	894.2	1252.1	1417.3
137.5°	623.9	690.5	890.1	1191.4	1326.0
140°	643.6	705.8	888.5	1152.3	1272.1
142.5°	662.6	721.1	885.5	1117.1	1221.9
145°	692.0	744.0	881.9	1071.7	1153.4
147.5°	718.8	764.9	877.7	1030.7	1093.4
150°	738.6	779.4	876.2	1008.4	1058.5
152.5°	756.8	792.4	875.4	987.6	1028.9
155°	781.3	811.9	874.3	961.4	993.0
157.5°	806.7	828.1	874.5	943.1	963.9
160°	821.1	838.8	875.3	931.6	946.5
162.5°	832.5	847.2	876.0	922.4	933.5
165°	850.6	858.9	878.1	912.4	917.0
167.5°	862.9	868.7	878.3	903.8	906.0
170°	870.5	873.3	879.1	899.9	899.9
172.5°	876.6	877.1	879.1	895.4	894.6
175°	882.9	881.9	879.1	890.4	888.5
177.5°	884.9	882.7	878.9	886.4	884.2
180°	881.9	881.9	881.9	881.9	881.9

(END OF REPORT)