

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563898

Luminaire Tested: **SQ4-PR1-025U-100D-830-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563898
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-025U-100D-830-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4494.5 lumens
Efficiency: N/A
Efficacy: 116.1 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 38.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563898
CATALOG NUMBER: SQ4-PR1-025U-100D-830-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P563898

CATALOG NUMBER: SQ4-PR1-025U-100D-830-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	109	109	109	109	100	100	100	91	91	91	83	83	83	80
1	105	101	97	93	100	96	93	90	88	86	83	81	79	77	74	73	71	68
2	96	88	82	77	92	85	79	74	78	74	70	72	68	65	66	63	61	58
3	88	78	71	65	84	75	68	63	69	64	59	64	59	56	59	55	52	49
4	81	70	61	55	77	67	60	54	62	56	51	57	52	48	53	49	45	43
5	74	62	54	48	71	60	52	47	56	49	44	52	46	42	48	43	40	37
6	69	56	48	42	66	54	47	41	50	44	39	47	41	37	44	39	35	33
7	64	51	43	37	61	49	42	36	46	39	35	43	37	33	40	35	31	29
8	59	47	39	33	57	45	38	32	42	36	31	39	34	30	37	32	28	26
9	55	43	35	30	53	41	34	29	39	32	28	36	31	27	34	29	26	24
10	52	39	32	27	50	38	31	26	36	30	25	34	28	24	31	27	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13220	13220	13220
5°	13339	13236	13168
10°	13297	13204	13135
15°	13239	13156	13085
20°	13171	13087	12990
25°	13079	12991	12840
30°	12938	12846	12662
35°	12746	12636	12455
40°	12456	12322	12099
45°	11948	11739	11498
50°	11054	10788	10576
55°	9648	9429	9231
60°	8130	8062	7903
65°	7032	7060	7006
70°	6458	6493	6493
75°	6203	6203	6249
80°	5834	5903	5834
85°	4700	5229	5229



TEST NUMBER: P563898

CATALOG NUMBER: SQ4-PR1-025U-100D-830-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.5	3.0
10°-20°	387.7	8.6
20°-30°	584.7	13.0
30°-40°	696.7	15.5
40°-50°	686.9	15.3
50°-60°	525.0	11.7
60°-70°	324.9	7.2
70°-80°	184.5	4.1
80°-90°	56.9	1.3
90°-100°	68.6	1.5
100°-110°	180.2	4.0
110°-120°	186.9	4.2
120°-130°	149.9	3.3
130°-140°	117.6	2.6
140°-150°	90.3	2.0
150°-160°	65.0	1.4
160°-170°	39.8	0.9
170°-180°	13.4	0.3
0°-30°	1107.9	24.7
0°-40°	1804.6	40.2
0°-60°	3016.5	67.1
0°-90°	3582.8	79.7
90°-120°	435.7	9.7
90°-150°	793.5	17.7
90°-180°	912.0	20.3
0°-180°	4494.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1433	1433	1433	1433	1433	
5°	1440	1425	1429	1424	1422	137
15°	1386	1372	1377	1372	1370	391
25°	1285	1269	1276	1262	1261	591
35°	1132	1118	1122	1107	1106	706
45°	916	904	900	884	881	702
55°	600	590	586	576	574	537
65°	322	320	323	321	321	326
75°	174	174	174	175	175	184
85°	44	47	49	49	49	52
90°	1	3	7	4	4	3
95°	9	36	118	61	42	10
105°	32	49	199	302	282	34
115°	58	70	160	318	363	57
125°	80	90	145	245	289	71
135°	96	105	141	198	224	74
145°	111	118	139	169	182	69
155°	125	129	139	152	157	58
165°	135	137	139	144	146	38
175°	141	141	140	142	142	13
180°	141	141	141	141	141	

TEST NUMBER: P563898

CATALOG NUMBER: SQ4-PR1-025U-100D-830-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1432.9	1432.9	1432.9	1432.9	1432.9
2.5°	1441.7	1429.2	1432.9	1429.7	1423.0
5°	1440.3	1424.6	1429.2	1424.2	1421.8
7.5°	1429.2	1413.7	1418.3	1413.3	1411.9
10°	1419.3	1404.8	1409.4	1404.4	1402.0
12.5°	1408.4	1393.0	1398.6	1392.6	1390.2
15°	1386.0	1371.5	1377.3	1372.3	1369.9
17.5°	1361.3	1345.8	1351.7	1345.9	1342.8
20°	1341.5	1327.1	1332.9	1324.2	1323.0
22.5°	1319.8	1305.3	1311.2	1299.6	1299.3
25°	1284.8	1269.1	1276.1	1262.5	1261.3
27.5°	1243.0	1228.6	1234.4	1220.6	1219.1
30°	1214.4	1199.9	1205.8	1190.9	1188.5
32.5°	1181.8	1168.3	1173.2	1158.4	1156.9
35°	1131.7	1118.5	1121.9	1107.0	1105.8
37.5°	1074.7	1062.6	1064.6	1048.3	1047.1
40°	1034.2	1022.2	1023.1	1005.8	1004.6
42.5°	989.8	977.7	976.7	959.4	958.2
45°	915.7	903.7	899.7	883.6	881.2
47.5°	831.3	819.3	811.8	798.7	797.0
50°	770.1	758.0	751.6	740.4	736.8
52.5°	704.0	691.9	686.4	676.2	672.6
55°	599.8	590.1	586.2	576.3	573.9
57.5°	500.8	494.3	493.2	483.5	482.6
60°	440.6	437.0	436.9	428.3	428.3
62.5°	389.3	386.6	388.5	382.8	381.8
65°	322.1	319.7	323.4	320.9	320.9
67.5°	269.0	269.0	271.3	270.3	270.3
70°	239.4	239.4	240.7	240.7	240.7
72.5°	212.8	211.8	215.0	215.0	214.0
75°	174.0	174.0	174.0	175.3	175.3
77.5°	135.5	135.8	136.7	136.5	135.5
80°	109.8	111.0	111.1	109.8	109.8
82.5°	84.2	85.4	85.4	85.1	84.2
85°	44.4	46.8	49.4	49.4	49.4
87.5°	13.0	17.2	21.2	20.4	19.5
90°	0.9	2.7	7.2	3.6	3.6
92.5°	3.8	18.2	40.4	17.9	11.5
95°	9.0	35.5	118.1	60.9	41.5
97.5°	15.7	39.0	176.7	140.5	103.5
100°	20.7	41.9	194.8	197.4	153.3
102.5°	25.1	44.8	199.8	245.8	208.1
105°	32.5	49.2	199.3	302.5	282.2
107.5°	40.0	55.6	187.9	331.9	336.9
110°	45.1	59.2	178.5	339.5	360.7

TEST NUMBER: P563898

CATALOG NUMBER: SQ4-PR1-025U-100D-830-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	50.1	63.5	169.9	334.7	367.2
115°	57.7	70.1	159.6	318.4	363.4
117.5°	65.1	76.4	152.6	295.8	345.7
120°	69.4	80.0	149.7	280.6	329.1
122.5°	73.8	84.3	147.5	265.5	313.2
125°	80.3	89.9	145.2	245.4	289.4
127.5°	85.5	95.4	143.2	229.2	266.4
130°	88.4	98.9	142.5	219.0	253.4
132.5°	91.3	101.8	141.7	210.3	241.1
135°	95.6	105.3	140.7	198.1	224.5
137.5°	100.1	109.6	140.5	188.9	210.6
140°	103.7	112.5	139.8	181.7	202.0
142.5°	106.6	114.7	139.8	176.6	194.0
145°	110.9	118.0	138.9	168.9	182.1
147.5°	115.2	122.1	138.9	162.6	173.5
150°	118.1	124.3	138.9	158.9	167.7
152.5°	121.0	125.8	138.9	156.0	162.7
155°	125.3	128.9	138.9	152.5	156.9
157.5°	128.6	131.9	138.9	149.4	152.6
160°	130.7	133.4	138.9	147.9	149.7
162.5°	132.9	134.8	138.9	146.5	148.2
165°	135.3	137.0	138.9	144.3	146.1
167.5°	137.4	138.3	139.8	143.4	144.1
170°	138.9	139.7	139.8	143.4	143.4
172.5°	139.6	139.8	139.8	142.6	141.9
175°	140.7	140.7	139.8	141.6	141.6
177.5°	140.7	140.7	139.9	141.4	140.7
180°	140.7	140.7	140.7	140.7	140.7

(END OF REPORT)