

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P853868

Luminaire Tested: SQ2-FB-0U-100D-940-UNV-STD-W-4

Issue Date: 7/12/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P853868  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2308-131-12)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/12/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2-FB-0U-100D-940-UNV-STD-W-4  
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4216.8 lumens  
Efficiency: N/A  
Efficacy: 112.1 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 2.98 / 2.56  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 37.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P853868

CATALOG NUMBER: SQ2-FB-0U-100D-940-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P853868

CATALOG NUMBER: SQ2-FB-0U-100D-940-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	109	104	100	96	106	102	98	94	97	94	91	93	91	88	90	88	86	84				
2	98	90	83	77	96	88	82	76	84	79	74	81	77	73	78	74	71	69				
3	89	78	70	63	87	77	69	63	74	67	61	71	65	60	68	63	59	57				
4	81	69	60	53	79	67	59	52	65	57	52	63	56	51	60	55	50	48				
5	74	61	52	45	72	60	51	45	58	50	44	56	49	43	54	48	43	41				
6	68	54	45	39	66	53	45	38	52	44	38	50	43	38	48	42	37	35				
7	63	49	40	34	61	48	40	33	47	39	33	45	38	33	44	37	33	31				
8	58	44	36	30	57	44	35	29	42	35	29	41	34	29	40	34	29	27				
9	54	40	32	26	53	40	32	26	39	31	26	38	31	26	37	30	26	24				
10	51	37	29	23	49	37	29	23	36	28	23	35	28	23	34	28	23	21				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6889	6889	6889
5°	6716	9310	12203
10°	6291	18029	23746
15°	5693	23457	27331
20°	5041	25804	28624
25°	4459	27595	29094
30°	3939	28418	29451
35°	3518	28913	31663
40°	3199	29187	33641
45°	2952	29325	35228
50°	2783	29888	35867
55°	2714	30666	36152
60°	2784	31071	35973
65°	2900	30647	34957
70°	3002	29637	26441
75°	3325	26619	14591
80°	3431	13733	13547
85°	3427	9503	5706

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 52.5°  
 Luminance: 36479 cd/sqm



TEST NUMBER: P853868

CATALOG NUMBER: SQ2-FB-0U-100D-940-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	71.5	1.7
10°-20°	326.3	7.7
20°-30°	574.2	13.6
30°-40°	743.2	17.6
40°-50°	819.7	19.4
50°-60°	765.3	18.1
60°-70°	591.5	14.0
70°-80°	272.9	6.5
80°-90°	52.1	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	972.0	23.1
0°-40°	1715.2	40.7
0°-60°	3300.3	78.3
0°-90°	4216.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4216.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	427	427	427	427	427	
5°	414	475	574	701	753	38
15°	341	672	1403	1571	1635	95
25°	250	902	1549	1617	1633	115
35°	178	871	1467	1518	1606	112
45°	129	667	1284	1475	1543	100
55°	96	397	1089	1252	1284	87
65°	76	224	802	899	915	74
75°	53	138	427	230	234	55
85°	18	40	51	35	31	20
90°	0	0	0	0	0	



TEST NUMBER: P853868

CATALOG NUMBER: SQ2-FB-0U-100D-940-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	426.7	426.7	426.7	426.7	426.7
2.5°	423.5	441.1	461.2	484.4	494.0
5°	414.4	474.6	574.4	700.8	752.9
7.5°	398.4	520.8	835.4	1173.4	1277.7
10°	383.7	554.2	1099.7	1392.3	1448.4
12.5°	367.2	598.7	1265.4	1471.1	1528.9
15°	340.6	671.6	1403.3	1570.9	1635.1
17.5°	313.1	753.6	1467.3	1632.6	1667.5
20°	293.4	810.9	1501.8	1643.8	1665.9
22.5°	275.3	853.9	1526.4	1634.0	1657.7
25°	250.3	902.3	1549.0	1617.0	1633.1
27.5°	226.1	915.0	1539.1	1583.8	1599.4
30°	211.3	911.4	1524.3	1557.7	1579.7
32.5°	198.2	901.5	1503.0	1535.3	1583.0
35°	178.5	870.6	1466.9	1518.1	1606.4
37.5°	161.7	820.8	1419.3	1524.2	1609.3
40°	151.8	783.7	1384.8	1523.9	1596.1
42.5°	142.0	740.2	1345.4	1507.5	1579.7
45°	129.3	666.9	1284.3	1474.6	1542.8
47.5°	117.4	584.4	1227.7	1429.0	1478.8
50°	110.8	528.0	1189.9	1387.8	1427.9
52.5°	104.2	473.3	1152.2	1338.5	1375.4
55°	96.4	397.3	1089.4	1252.2	1284.3
57.5°	89.5	332.2	1018.0	1156.9	1183.0
60°	86.2	296.8	962.2	1087.9	1114.0
62.5°	81.2	264.6	899.8	1015.7	1040.2
65°	75.9	224.4	802.2	899.0	915.0
67.5°	68.5	194.5	698.4	757.6	727.5
70°	63.6	179.9	627.8	646.3	560.1
72.5°	60.3	163.8	550.7	501.8	338.5
75°	53.3	137.6	426.7	229.9	233.9
77.5°	43.5	106.5	280.7	176.5	180.1
80°	36.9	87.1	147.7	143.7	145.7
82.5°	30.4	67.7	101.8	105.8	103.0
85°	18.5	40.5	51.3	34.8	30.8
87.5°	6.6	14.6	8.2	8.2	8.2
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P853868

CATALOG NUMBER: SQ2-FB-0U-100D-940-UNV-STD-W-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.53	19.21	17.89	19.53	19.84	26.26	27.95	26.63	28.26	28.58
	3H	18.32	19.84	18.69	20.17	20.53	27.95	29.47	28.32	29.80	30.16
	4H	18.65	20.09	19.05	20.44	20.81	28.16	29.60	28.56	29.95	30.32
	6H	18.91	20.24	19.32	20.61	21.00	28.29	29.62	28.70	29.98	30.37
	8H	18.99	20.27	19.42	20.65	21.05	28.32	29.59	28.74	29.98	30.38
	12H	19.05	20.27	19.48	20.65	21.08	28.32	29.54	28.75	29.92	30.35
4H	2H	22.02	23.46	22.42	23.81	24.18	26.80	28.24	27.20	28.59	28.96
	3H	23.03	24.23	23.44	24.63	25.03	28.70	29.91	29.11	30.30	30.70
	4H	23.35	24.43	23.78	24.85	25.28	28.98	30.06	29.41	30.48	30.91
	6H	23.53	24.48	23.98	24.92	25.37	29.17	30.12	29.63	30.56	31.01
	8H	23.57	24.46	24.03	24.90	25.36	29.22	30.10	29.68	30.54	31.01
	12H	23.60	24.40	24.08	24.87	25.34	29.23	30.03	29.71	30.50	30.97
8H	4H	24.59	25.48	25.05	25.92	26.39	29.17	30.05	29.62	30.49	30.96
	6H	24.87	25.60	25.36	26.09	26.56	29.41	30.14	29.90	30.63	31.10
	8H	24.95	25.61	25.46	26.11	26.60	29.48	30.14	29.99	30.64	31.13
	12H	25.02	25.60	25.52	26.09	26.65	29.51	30.09	30.02	30.58	31.14
12H	4H	24.65	25.45	25.13	25.92	26.39	29.16	29.95	29.64	30.43	30.90
	6H	24.97	25.63	25.48	26.14	26.62	29.40	30.06	29.91	30.56	31.05
	8H	25.12	25.70	25.62	26.19	26.75	29.51	30.09	30.02	30.58	31.14