

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P853892

Luminaire Tested: SQ2-FB-125U-100D-940-UNV-STD-W-4

Issue Date: 7/12/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P853892  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-13, G2-2308-131-12)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/12/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2-FB-125U-100D-940-UNV-STD-W-4  
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9475.0 lumens  
Efficiency: N/A  
Efficacy: 116.3 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 2.98 / 2.56  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 81.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P853892

CATALOG NUMBER: SQ2-FB-125U-100D-940-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P853892

CATALOG NUMBER: SQ2-FB-125U-100D-940-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45
1	96	92	88	85	88	84	81	78	70	68	66	57	55	54	45	44	43	37
2	87	80	74	69	80	73	68	63	61	57	54	50	47	44	39	37	36	31
3	80	70	62	57	72	64	58	52	53	49	45	43	40	37	34	32	30	25
4	72	61	53	47	66	57	49	44	47	42	38	38	34	31	30	27	25	21
5	66	54	46	40	60	50	43	37	42	36	32	34	30	27	27	24	22	18
6	61	49	40	34	55	45	37	32	37	32	28	31	26	23	24	21	19	16
7	56	44	35	30	51	40	33	28	34	28	24	28	23	20	22	19	16	14
8	52	39	31	26	47	36	29	24	30	25	21	25	21	18	20	17	14	12
9	48	36	28	23	44	33	26	22	28	22	19	23	19	16	18	15	13	11
10	45	33	25	20	41	30	24	19	25	20	17	21	17	14	17	14	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6889	6889	6889
5°	6716	9310	12203
10°	6291	18029	23746
15°	5693	23457	27331
20°	5041	25804	28624
25°	4459	27595	29094
30°	3939	28418	29451
35°	3518	28913	31663
40°	3199	29187	33641
45°	2952	29325	35228
50°	2783	29888	35867
55°	2714	30666	36152
60°	2784	31071	35973
65°	2900	30647	34957
70°	3002	29637	26441
75°	3325	26619	14591
80°	3431	13733	13547
85°	3427	9503	5706

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 52.5°  
 Luminance: 36479 cd/sqm



TEST NUMBER: P853892

CATALOG NUMBER: SQ2-FB-125U-100D-940-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	71.5	0.8
10°-20°	326.3	3.4
20°-30°	574.2	6.1
30°-40°	743.2	7.8
40°-50°	819.7	8.7
50°-60°	765.3	8.1
60°-70°	591.5	6.2
70°-80°	272.9	2.9
80°-90°	53.1	0.6
90°-100°	325.9	3.4
100°-110°	1061.2	11.2
110°-120°	1049.7	11.1
120°-130°	857.8	9.1
130°-140°	701.1	7.4
140°-150°	546.1	5.8
150°-160°	393.6	4.2
160°-170°	240.6	2.5
170°-180°	81.2	0.9
0°-30°	972.0	10.3
0°-40°	1715.2	18.1
0°-60°	3300.3	34.8
0°-90°	4217.7	44.5
90°-120°	2436.8	25.7
90°-150°	4541.8	47.9
90°-180°	5257.0	55.5
0°-180°	9475.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	427	427	427	427	427	
5°	414	475	574	701	753	38
15°	341	672	1403	1571	1635	95
25°	250	902	1549	1617	1633	115
35°	178	871	1467	1518	1606	112
45°	129	667	1284	1475	1543	100
55°	96	397	1089	1252	1284	87
65°	76	224	802	899	915	74
75°	53	138	427	230	234	55
85°	18	40	51	35	31	19
90°	0	3	7	6	6	3
95°	44	134	597	213	131	51
105°	180	260	1051	2008	1901	192
115°	333	398	856	1765	2076	330
125°	463	516	845	1393	1642	412
135°	560	618	841	1202	1356	432
145°	654	702	838	1036	1134	409
155°	746	771	844	927	962	344
165°	814	822	846	878	888	229
175°	849	849	849	855	853	81
180°	852	852	852	852	852	

TEST NUMBER: P853892

CATALOG NUMBER: SQ2-FB-125U-100D-940-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	426.7	426.7	426.7	426.7	426.7
2.5°	423.5	441.1	461.2	484.4	494.0
5°	414.4	474.6	574.4	700.8	752.9
7.5°	398.4	520.8	835.4	1173.4	1277.7
10°	383.7	554.2	1099.7	1392.3	1448.4
12.5°	367.2	598.7	1265.4	1471.1	1528.9
15°	340.6	671.6	1403.3	1570.9	1635.1
17.5°	313.1	753.6	1467.3	1632.6	1667.5
20°	293.4	810.9	1501.8	1643.8	1665.9
22.5°	275.3	853.9	1526.4	1634.0	1657.7
25°	250.3	902.3	1549.0	1617.0	1633.1
27.5°	226.1	915.0	1539.1	1583.8	1599.4
30°	211.3	911.4	1524.3	1557.7	1579.7
32.5°	198.2	901.5	1503.0	1535.3	1583.0
35°	178.5	870.6	1466.9	1518.1	1606.4
37.5°	161.7	820.8	1419.3	1524.2	1609.3
40°	151.8	783.7	1384.8	1523.9	1596.1
42.5°	142.0	740.2	1345.4	1507.5	1579.7
45°	129.3	666.9	1284.3	1474.6	1542.8
47.5°	117.4	584.4	1227.7	1429.0	1478.8
50°	110.8	528.0	1189.9	1387.8	1427.9
52.5°	104.2	473.3	1152.2	1338.5	1375.4
55°	96.4	397.3	1089.4	1252.2	1284.3
57.5°	89.5	332.2	1018.0	1156.9	1183.0
60°	86.2	296.8	962.2	1087.9	1114.0
62.5°	81.2	264.6	899.8	1015.7	1040.2
65°	75.9	224.4	802.2	899.0	915.0
67.5°	68.5	194.5	698.4	757.6	727.5
70°	63.6	179.9	627.8	646.3	560.1
72.5°	60.3	163.8	550.7	501.8	338.5
75°	53.3	137.6	426.7	229.9	233.9
77.5°	43.5	106.5	280.7	176.5	180.1
80°	36.9	87.1	147.7	143.7	145.7
82.5°	30.4	67.7	101.8	105.8	103.0
85°	18.5	40.5	51.3	34.8	30.8
87.5°	6.6	15.2	9.7	9.5	9.5
90°	0.0	3.1	7.3	6.3	6.3
92.5°	15.1	54.2	173.4	57.1	44.0
95°	44.0	134.2	597.4	213.0	131.0
97.5°	82.8	174.6	1013.9	617.5	376.9
100°	108.0	198.1	1170.7	1043.9	677.1
102.5°	136.5	223.4	1151.4	1544.4	1174.3
105°	180.3	260.2	1051.2	2007.8	1901.2
107.5°	227.6	302.9	956.1	2048.0	2160.9
110°	262.0	330.7	910.8	1998.1	2202.0



TEST NUMBER: P853892

CATALOG NUMBER: SQ2-FB-125U-100D-940-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	290.5	358.4	882.3	1908.0	2171.0
115°	333.3	397.9	856.3	1764.7	2076.3
117.5°	377.3	435.5	846.2	1633.5	1943.6
120°	402.5	459.9	843.7	1552.7	1853.0
122.5°	426.8	483.3	844.5	1482.7	1762.5
125°	463.3	516.5	844.8	1393.3	1642.3
127.5°	494.5	549.0	844.5	1326.4	1534.0
130°	514.6	569.9	843.7	1288.1	1473.6
132.5°	532.2	590.0	842.9	1252.6	1426.7
135°	559.7	618.1	840.6	1202.5	1356.2
137.5°	586.5	645.3	838.3	1151.6	1288.1
140°	605.8	662.2	837.4	1117.0	1246.2
142.5°	624.2	678.1	837.4	1084.0	1199.2
145°	654.0	702.2	838.5	1035.6	1134.0
147.5°	682.9	724.7	839.9	994.5	1070.5
150°	702.2	739.1	841.6	969.9	1034.5
152.5°	721.5	751.8	842.5	951.2	1002.6
155°	746.2	770.8	843.7	927.3	962.1
157.5°	769.7	787.3	845.0	909.7	934.1
160°	784.0	798.3	845.8	898.7	918.1
162.5°	796.5	807.6	845.8	889.3	903.9
165°	814.4	821.5	845.8	877.5	887.7
167.5°	826.9	831.4	846.0	868.6	873.9
170°	835.3	837.4	846.9	862.6	864.7
172.5°	841.2	842.4	848.5	859.2	858.8
175°	848.9	848.9	848.9	855.2	853.1
177.5°	852.1	851.3	850.4	854.5	851.3
180°	852.1	852.1	852.1	852.1	852.1



TEST NUMBER: P853892

CATALOG NUMBER: SQ2-FB-125U-100D-940-UNV-STD-W-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.24	14.08	14.24	15.09	16.44	21.98	22.82	22.98	23.83	25.18
	3H	13.97	14.72	14.98	15.74	17.11	23.60	24.35	24.61	25.37	26.74
	4H	14.27	14.98	15.29	16.01	17.38	23.78	24.49	24.80	25.52	26.89
	6H	14.49	15.14	15.52	16.17	17.56	23.87	24.52	24.90	25.55	26.93
	8H	14.54	15.17	15.58	16.21	17.60	23.87	24.49	24.91	25.54	26.92
	12H	14.57	15.16	15.61	16.20	17.61	23.84	24.43	24.88	25.47	26.88
4H	2H	17.64	18.35	18.67	19.38	20.75	22.42	23.13	23.45	24.16	25.53
	3H	18.57	19.16	19.61	20.22	21.60	24.24	24.84	25.28	25.89	27.28
	4H	18.85	19.40	19.90	20.44	21.85	24.48	25.02	25.53	26.07	27.48
	6H	18.98	19.45	20.04	20.52	21.92	24.63	25.09	25.68	26.16	27.56
	8H	19.00	19.44	20.06	20.50	21.92	24.65	25.08	25.71	26.14	27.57
	12H	18.99	19.39	20.07	20.46	21.89	24.62	25.01	25.70	26.09	27.52
8H	4H	20.03	20.46	21.08	21.52	22.94	24.60	25.03	25.65	26.09	27.51
	6H	20.26	20.62	21.34	21.72	23.14	24.80	25.16	25.88	26.26	27.68
	8H	20.33	20.65	21.42	21.73	23.17	24.86	25.18	25.95	26.26	27.70
	12H	20.36	20.63	21.45	21.72	23.19	24.85	25.13	25.95	26.21	27.69
12H	4H	20.04	20.44	21.12	21.51	22.94	24.55	24.94	25.62	26.02	27.44
	6H	20.36	20.67	21.44	21.76	23.19	24.78	25.10	25.87	26.18	27.62
	8H	20.46	20.74	21.55	21.82	23.29	24.85	25.13	25.94	26.21	27.69