

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564546

Luminaire Tested: **SQ4-PW1-025U-075D-830-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P564546  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2106-289-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PW1-025U-075D-830-1D-UNV-STD-W-4  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 250 LUMENS PER FOOT  
Light Source: 3000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3594.8 lumens  
Efficiency: N/A  
Efficacy: 120.2 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 29.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P564546  
CATALOG NUMBER: SQ4-PW1-025U-075D-830-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P564546

CATALOG NUMBER: SQ4-PW1-025U-075D-830-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	97	97	97	87	87	87	79	79	79	75
1	103	99	95	91	98	94	91	88	86	83	80	77	75	73	70	68	67	63
2	94	87	80	75	89	83	77	72	75	71	67	68	65	62	62	59	57	53
3	86	76	69	63	82	73	66	60	66	61	56	60	56	52	55	51	48	45
4	79	68	59	53	75	65	57	51	59	53	48	54	49	45	49	45	42	39
5	73	61	52	46	69	58	50	44	53	47	42	48	43	39	44	40	36	34
6	67	54	46	40	64	52	44	39	48	41	37	44	38	34	40	36	32	30
7	62	49	41	35	59	47	40	34	44	37	32	40	35	30	37	32	29	26
8	58	45	37	31	55	43	36	31	40	33	29	37	31	27	34	29	26	23
9	54	41	33	28	51	40	32	27	37	30	26	34	28	25	31	27	23	21
10	50	38	30	25	48	37	30	25	34	28	24	31	26	22	29	24	21	19

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	9726	9726	9726
5°	9789	9712	9669
10°	9711	9633	9581
15°	9608	9502	9467
20°	9493	9348	9329
25°	9362	9190	9163
30°	9163	9025	8965
35°	8903	8777	8726
40°	8625	8491	8457
45°	8289	8181	8144
50°	7946	7879	7825
55°	7575	7575	7456
60°	7113	7250	6993
65°	6510	6833	6346
70°	5738	6288	5587
75°	4902	5629	4770
80°	3799	4739	3852
85°	2456	3642	3250



TEST NUMBER: P564546

CATALOG NUMBER: SQ4-PW1-025U-075D-830-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	99.3	2.8
10°-20°	280.3	7.8
20°-30°	415.7	11.6
30°-40°	486.5	13.5
40°-50°	484.3	13.5
50°-60°	418.2	11.6
60°-70°	301.0	8.4
70°-80°	157.9	4.4
80°-90°	39.9	1.1
90°-100°	68.6	1.9
100°-110°	180.2	5.0
110°-120°	186.9	5.2
120°-130°	149.9	4.2
130°-140°	117.6	3.3
140°-150°	90.3	2.5
150°-160°	65.0	1.8
160°-170°	39.8	1.1
170°-180°	13.4	0.4
0°-30°	795.3	22.1
0°-40°	1281.7	35.7
0°-60°	2184.2	60.8
0°-90°	2683.0	74.6
90°-120°	435.7	12.1
90°-150°	793.5	22.1
90°-180°	912.0	25.4
0°-180°	3594.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1054	1054	1054	1054	1054	
5°	1057	1045	1049	1046	1044	100
15°	1006	993	995	993	991	284
25°	920	904	903	897	900	423
35°	790	780	779	772	775	494
45°	635	630	627	625	624	490
55°	471	470	471	464	464	420
65°	298	307	313	301	291	295
75°	138	150	158	147	134	147
85°	23	30	34	32	31	31
90°	1	3	7	4	4	2
95°	9	36	118	61	42	10
105°	32	49	199	302	282	34
115°	58	70	160	318	363	57
125°	80	90	145	245	289	71
135°	96	105	141	198	224	74
145°	111	118	139	169	182	69
155°	125	129	139	152	157	58
165°	135	137	139	144	146	38
175°	141	141	140	142	142	13
180°	141	141	141	141	141	

TEST NUMBER: P564546

CATALOG NUMBER: SQ4-PW1-025U-075D-830-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1054.2	1054.2	1054.2	1054.2	1054.2
2.5°	1060.2	1051.5	1054.2	1051.9	1046.8
5°	1057.0	1045.2	1048.7	1045.8	1044.0
7.5°	1046.3	1035.4	1037.9	1034.9	1033.8
10°	1036.6	1025.7	1028.2	1024.5	1022.7
12.5°	1025.4	1013.8	1016.3	1012.6	1011.5
15°	1005.9	993.2	994.8	992.9	991.1
17.5°	983.3	970.4	970.6	967.7	967.3
20°	966.9	953.3	952.1	948.4	950.2
22.5°	949.1	934.7	933.5	928.3	930.9
25°	919.6	904.1	902.8	897.3	900.1
27.5°	885.4	870.1	870.1	862.4	865.3
30°	860.1	845.6	847.1	837.9	841.5
32.5°	833.4	820.3	821.1	811.9	815.5
35°	790.5	779.6	779.3	771.9	774.7
37.5°	746.6	737.0	735.5	731.2	731.9
40°	716.1	708.0	705.0	702.2	702.2
42.5°	684.2	676.7	673.8	671.7	671.0
45°	635.3	629.9	627.0	625.1	624.2
47.5°	587.0	581.9	579.4	578.1	577.2
50°	553.6	550.0	548.9	546.1	545.2
52.5°	520.2	518.0	517.0	513.4	512.5
55°	470.9	470.0	470.9	464.4	463.5
57.5°	419.7	421.1	424.1	415.3	413.2
60°	385.5	389.1	392.9	382.6	379.0
62.5°	350.5	356.4	361.7	349.9	344.8
65°	298.2	307.2	313.0	300.7	290.7
67.5°	247.6	258.9	265.8	252.6	241.3
70°	212.7	225.4	233.1	219.8	207.1
72.5°	182.2	196.4	202.7	190.1	177.4
75°	137.5	150.2	157.9	147.4	133.8
77.5°	97.5	109.5	115.9	106.7	95.5
80°	71.5	84.2	89.2	81.5	72.5
82.5°	50.7	61.3	64.6	60.0	53.9
85°	23.2	30.5	34.4	32.5	30.7
87.5°	6.1	11.6	15.6	14.9	15.6
90°	0.9	2.7	7.2	3.6	3.6
92.5°	3.8	18.2	40.4	17.9	11.5
95°	9.0	35.5	118.1	60.9	41.5
97.5°	15.7	39.0	176.7	140.5	103.5
100°	20.7	41.9	194.8	197.4	153.3
102.5°	25.1	44.8	199.8	245.8	208.1
105°	32.5	49.2	199.3	302.5	282.2
107.5°	40.0	55.6	187.9	331.9	336.9
110°	45.1	59.2	178.5	339.5	360.7



TEST NUMBER: P564546

CATALOG NUMBER: SQ4-PW1-025U-075D-830-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	50.1	63.5	169.9	334.7	367.2
115°	57.7	70.1	159.6	318.4	363.4
117.5°	65.1	76.4	152.6	295.8	345.7
120°	69.4	80.0	149.7	280.6	329.1
122.5°	73.8	84.3	147.5	265.5	313.2
125°	80.3	89.9	145.2	245.4	289.4
127.5°	85.5	95.4	143.2	229.2	266.4
130°	88.4	98.9	142.5	219.0	253.4
132.5°	91.3	101.8	141.7	210.3	241.1
135°	95.6	105.3	140.7	198.1	224.5
137.5°	100.1	109.6	140.5	188.9	210.6
140°	103.7	112.5	139.8	181.7	202.0
142.5°	106.6	114.7	139.8	176.6	194.0
145°	110.9	118.0	138.9	168.9	182.1
147.5°	115.2	122.1	138.9	162.6	173.5
150°	118.1	124.3	138.9	158.9	167.7
152.5°	121.0	125.8	138.9	156.0	162.7
155°	125.3	128.9	138.9	152.5	156.9
157.5°	128.6	131.9	138.9	149.4	152.6
160°	130.7	133.4	138.9	147.9	149.7
162.5°	132.9	134.8	138.9	146.5	148.2
165°	135.3	137.0	138.9	144.3	146.1
167.5°	137.4	138.3	139.8	143.4	144.1
170°	138.9	139.7	139.8	143.4	143.4
172.5°	139.6	139.8	139.8	142.6	141.9
175°	140.7	140.7	139.8	141.6	141.6
177.5°	140.7	140.7	139.9	141.4	140.7
180°	140.7	140.7	140.7	140.7	140.7

(END OF REPORT)