

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P519645

Luminaire Tested: **SQ4-025U-0D-830-1D-UNV-STD-W-6**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519645
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-025U-0D-830-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1367.6 lumens
Efficiency: N/A
Efficacy: 166.8 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Indirect

Input Watts (W): 8.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519645
CATALOG NUMBER: SQ4-025U-0D-830-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P519645

CATALOG NUMBER: SQ4-025U-0D-830-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20								20				20				20	
RC	80								50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	953	12505	4390
100°	1102	10346	8143
105°	1157	7103	10060
110°	1216	4816	9729
115°	1260	3484	7933
120°	1281	2762	6073
125°	1291	2336	4656
130°	1268	2045	3637
135°	1247	1835	2930
140°	1249	1683	2433
145°	1249	1564	2051
150°	1259	1479	1787
155°	1276	1414	1597
160°	1284	1363	1469
165°	1292	1326	1395
170°	1301	1309	1343
175°	1303	1294	1311



TEST NUMBER: P519645

CATALOG NUMBER: SQ4-025U-0D-830-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	102.8	7.5
100°-110°	270.3	19.8
110°-120°	280.3	20.5
120°-130°	224.9	16.4
130°-140°	176.4	12.9
140°-150°	135.4	9.9
150°-160°	97.5	7.1
160°-170°	59.7	4.4
170°-180°	20.2	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	653.5	47.8
90°-150°	1190.2	87.0
90°-180°	1368.0	100.0
0°-180°	1367.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	1	4	11	5	5	
95°	14	53	177	91	62	16
105°	49	74	299	454	423	52
115°	87	105	239	478	545	85
125°	120	135	218	368	434	107
135°	143	158	211	297	337	111
145°	166	177	208	253	273	104
155°	188	193	208	229	235	86
165°	203	206	208	216	219	57
175°	211	211	210	212	212	20
180°	211	211	211	211	211	



TEST NUMBER: P519645

CATALOG NUMBER: SQ4-025U-0D-830-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	1.4	4.0	10.8	5.4	5.4
92.5°	5.7	27.4	60.6	26.8	17.3
95°	13.5	53.2	177.2	91.3	62.2
97.5°	23.5	58.4	265.1	210.8	155.3
100°	31.1	62.8	292.1	296.1	229.9
102.5°	37.6	67.2	299.7	368.8	312.2
105°	48.7	73.8	298.9	453.8	423.3
107.5°	60.1	83.3	281.9	497.9	505.3
110°	67.6	88.8	267.8	509.3	541.0
112.5°	75.2	95.3	254.8	502.1	550.8
115°	86.6	105.1	239.4	477.6	545.1
117.5°	97.7	114.6	228.8	443.7	518.6
120°	104.1	120.0	224.5	420.9	493.7
122.5°	110.6	126.5	221.3	398.2	469.9
125°	120.4	134.9	217.8	368.0	434.2
127.5°	128.2	143.0	214.8	343.7	399.5
130°	132.5	148.4	213.7	328.5	380.1
132.5°	136.9	152.7	212.6	315.4	361.7
135°	143.4	157.9	211.0	297.1	336.8
137.5°	150.1	164.4	210.7	283.4	316.0
140°	155.5	168.8	209.6	272.6	303.0
142.5°	159.9	172.0	209.6	264.9	291.1
145°	166.4	176.9	208.3	253.4	273.2
147.5°	172.9	183.2	208.3	243.8	260.2
150°	177.2	186.4	208.3	238.3	251.6
152.5°	181.5	188.7	208.3	233.9	244.0
155°	188.0	193.3	208.3	228.7	235.3
157.5°	192.9	197.9	208.3	224.1	228.8
160°	196.1	200.1	208.3	221.9	224.5
162.5°	199.4	202.3	208.3	219.7	222.4
165°	202.9	205.5	208.3	216.5	219.1
167.5°	206.1	207.4	209.6	215.1	216.1
170°	208.3	209.6	209.6	215.1	215.1
172.5°	209.4	209.6	209.6	213.9	212.9
175°	211.0	211.0	209.6	212.3	212.3
177.5°	211.0	211.0	209.9	212.1	211.0
180°	211.0	211.0	211.0	211.0	211.0

(END OF REPORT)