

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P854276

Luminaire Tested: SQ2-PW1-075U-100D-940-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P854276
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-11, G2-2308-131-8)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-PW1-075U-100D-940-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7914.5 lumens
Efficiency: N/A
Efficacy: 130.0 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.11 / 1.22
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 60.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P854276

CATALOG NUMBER: SQ2-PW1-075U-100D-940-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P854276

CATALOG NUMBER: SQ2-PW1-075U-100D-940-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	66	66	66	60
1	101	97	93	90	94	91	87	85	79	77	75	69	67	66	59	58	57	52
2	92	85	79	74	86	80	75	71	70	66	63	61	58	56	53	51	49	45
3	85	76	68	63	79	71	65	60	63	58	54	55	51	48	47	45	42	39
4	78	67	60	54	73	63	57	51	56	51	46	49	45	42	43	40	37	34
5	72	60	52	47	67	57	50	45	51	45	41	45	40	37	39	36	33	30
6	66	54	47	41	62	52	44	39	46	40	36	41	36	32	36	32	29	27
7	62	49	42	36	58	47	40	35	42	36	32	37	32	29	33	29	26	24
8	57	45	37	32	54	43	36	31	38	33	28	34	29	26	30	26	24	21
9	53	41	34	29	50	39	32	28	35	30	26	31	27	24	28	24	21	19
10	50	38	31	26	47	36	30	25	33	27	23	29	25	21	26	22	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	34781	34781	34781
5°	34548	34814	35148
10°	34611	35015	35452
15°	34603	35254	35666
20°	34617	35216	34969
25°	34429	34467	32493
30°	34194	32473	29375
35°	33928	29883	26528
40°	33253	27242	23438
45°	31949	24501	20473
50°	29735	21901	17520
55°	27201	19347	14207
60°	24380	16827	12255
65°	21318	14499	10896
70°	17434	12883	9880
75°	13568	11135	9089
80°	10107	9540	8015
85°	6836	7225	4557

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 31949 cd/sqm



TEST NUMBER: P854276

CATALOG NUMBER: SQ2-PW1-075U-100D-940-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	205.1	2.6
10°-20°	594.3	7.5
20°-30°	874.6	11.1
30°-40°	956.3	12.1
40°-50°	857.9	10.8
50°-60°	639.9	8.1
60°-70°	404.4	5.1
70°-80°	200.3	2.5
80°-90°	47.4	0.6
90°-100°	191.4	2.4
100°-110°	634.6	8.0
110°-120°	629.9	8.0
120°-130°	513.0	6.5
130°-140°	417.0	5.3
140°-150°	323.8	4.1
150°-160°	233.3	2.9
160°-170°	142.9	1.8
170°-180°	48.3	0.6
0°-30°	1674.1	21.2
0°-40°	2630.4	33.2
0°-60°	4128.1	52.2
0°-90°	4780.3	60.4
90°-120°	1456.0	18.4
90°-150°	2709.8	34.2
90°-180°	3134.0	39.6
0°-180°	7914.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2154	2154	2154	2154	2154	
5°	2132	2166	2148	2150	2169	203
15°	2070	2110	2109	2124	2134	584
25°	1933	1975	1935	1854	1824	890
35°	1721	1703	1516	1384	1346	1074
45°	1399	1287	1073	939	897	1073
55°	966	874	687	539	505	863
65°	558	512	380	305	285	553
75°	218	234	178	150	146	240
85°	37	47	39	27	25	47
90°	0	1	3	4	4	2
95°	27	80	347	124	83	31
105°	111	158	635	1198	1120	117
115°	198	237	512	1065	1245	196
125°	277	307	502	837	986	246
135°	331	365	498	718	810	256
145°	385	413	497	618	676	241
155°	439	454	500	552	572	202
165°	482	487	502	522	527	136
175°	504	504	505	508	507	48
180°	506	506	506	506	506	



TEST NUMBER: P854276

CATALOG NUMBER: SQ2-PW1-075U-100D-940-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2154.2	2154.2	2154.2	2154.2	2154.2
2.5°	2139.4	2166.7	2149.3	2151.0	2155.8
5°	2131.6	2165.7	2148.0	2150.5	2168.6
7.5°	2121.0	2155.5	2142.3	2149.7	2167.3
10°	2111.1	2147.2	2135.7	2146.4	2162.4
12.5°	2098.0	2135.7	2127.5	2139.8	2155.8
15°	2070.1	2110.2	2109.1	2123.6	2133.7
17.5°	2037.7	2077.8	2075.8	2079.6	2084.4
20°	2014.7	2054.8	2049.6	2035.2	2035.2
22.5°	1981.9	2025.2	2011.8	1972.5	1959.7
25°	1932.6	1974.7	1934.7	1854.0	1823.9
27.5°	1875.2	1909.3	1828.8	1714.2	1672.5
30°	1834.1	1860.2	1741.8	1615.8	1575.6
32.5°	1791.5	1801.5	1653.2	1522.1	1478.8
35°	1721.3	1703.2	1516.1	1384.0	1345.9
37.5°	1638.4	1584.7	1384.4	1246.0	1203.9
40°	1577.7	1501.5	1292.5	1154.1	1112.0
42.5°	1510.4	1414.9	1205.5	1067.1	1023.3
45°	1399.2	1286.9	1073.0	938.7	896.6
47.5°	1274.1	1162.5	949.1	819.0	782.9
50°	1183.8	1075.5	871.9	741.7	697.5
52.5°	1091.9	994.8	796.4	662.5	602.4
55°	966.3	874.0	687.3	538.8	504.7
57.5°	837.1	757.2	588.4	453.6	425.5
60°	755.0	684.8	521.1	407.6	379.5
62.5°	676.2	614.0	455.5	365.1	341.8
65°	558.0	511.9	379.5	305.2	285.2
67.5°	443.1	417.5	315.5	250.4	237.2
70°	369.3	361.3	272.9	219.3	209.3
72.5°	305.3	308.5	231.8	189.8	183.0
75°	217.5	233.5	178.5	149.7	145.7
77.5°	148.1	172.2	132.1	110.7	107.5
80°	108.7	132.8	102.6	86.2	86.2
82.5°	75.9	95.2	73.0	64.8	64.8
85°	36.9	47.0	39.0	26.6	24.6
87.5°	9.8	14.9	7.2	5.8	5.8
90°	0.0	1.0	3.1	4.2	4.2
92.5°	8.4	32.4	95.4	30.9	26.0
95°	27.2	80.5	346.9	123.8	82.8
97.5°	50.1	105.8	605.6	353.2	223.2
100°	66.0	119.3	701.2	602.2	399.3
102.5°	83.6	135.3	695.3	920.3	695.3
105°	111.1	158.2	635.1	1198.3	1120.4
107.5°	139.2	181.2	577.5	1226.5	1285.8
110°	155.1	197.1	548.1	1198.6	1318.5



TEST NUMBER: P854276

CATALOG NUMBER: SQ2-PW1-075U-100D-940-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	171.9	213.1	530.5	1149.0	1301.7
115°	198.1	237.0	511.5	1064.8	1245.1
117.5°	224.1	258.7	504.5	984.2	1173.4
120°	240.0	273.8	502.0	933.8	1117.2
122.5°	254.3	287.3	502.0	892.4	1061.9
125°	276.7	307.4	502.0	836.6	986.2
127.5°	295.1	325.3	500.8	794.4	922.3
130°	306.0	337.8	499.9	769.8	884.6
132.5°	316.1	348.7	499.1	749.4	852.7
135°	331.2	365.0	497.8	717.9	810.2
137.5°	347.5	380.1	496.6	687.5	768.9
140°	358.4	390.2	495.7	667.2	742.0
142.5°	368.5	399.5	496.6	646.9	713.5
145°	384.6	413.3	496.8	617.6	676.0
147.5°	402.0	426.0	497.0	592.7	636.2
150°	412.9	434.5	497.8	578.3	615.2
152.5°	423.0	443.7	498.7	566.4	595.9
155°	439.1	454.5	499.9	551.8	572.2
157.5°	454.9	466.8	501.2	541.3	555.9
160°	463.2	473.5	502.0	533.7	545.0
162.5°	471.6	479.4	502.0	528.6	537.5
165°	482.1	487.2	502.0	522.1	527.2
167.5°	491.8	494.4	503.1	516.1	518.8
170°	496.8	497.8	503.1	513.6	514.6
172.5°	500.1	501.2	503.9	511.0	511.3
175°	504.1	504.1	505.2	508.3	507.3
177.5°	506.2	506.2	505.4	507.0	505.4
180°	506.2	506.2	506.2	506.2	506.2



TEST NUMBER: P854276

CATALOG NUMBER: SQ2-PW1-075U-100D-940-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	20.31	21.22	21.18	22.11	23.22	16.79	17.71	17.66	18.59	19.71
	3H	21.63	22.45	22.52	23.35	24.49	18.00	18.82	18.89	19.71	20.86
	4H	22.01	22.78	22.91	23.68	24.84	18.45	19.22	19.35	20.12	21.28
	6H	22.22	22.92	23.13	23.83	25.00	18.77	19.48	19.68	20.39	21.56
	8H	22.25	22.92	23.17	23.85	25.02	18.85	19.52	19.77	20.45	21.61
	12H	22.25	22.89	23.17	23.81	25.00	18.86	19.50	19.79	20.42	21.61
4H	2H	20.42	21.19	21.32	22.09	23.24	17.48	18.25	18.39	19.15	20.31
	3H	21.97	22.61	22.88	23.54	24.71	18.87	19.51	19.79	20.45	21.62
	4H	22.48	23.06	23.40	23.99	25.18	19.42	20.00	20.35	20.93	22.13
	6H	22.81	23.31	23.75	24.26	25.46	19.83	20.33	20.77	21.28	22.48
	8H	22.89	23.36	23.83	24.30	25.51	19.94	20.40	20.88	21.35	22.56
	12H	22.91	23.33	23.87	24.29	25.51	19.96	20.38	20.92	21.35	22.56
8H	4H	22.52	22.99	23.46	23.93	25.14	19.75	20.22	20.70	21.17	22.38
	6H	22.96	23.34	23.92	24.33	25.54	20.26	20.65	21.23	21.64	22.84
	8H	23.10	23.44	24.08	24.42	25.65	20.43	20.77	21.40	21.74	22.97
	12H	23.17	23.47	24.15	24.44	25.72	20.49	20.79	21.47	21.76	23.03
12H	4H	22.48	22.90	23.44	23.87	25.08	19.77	20.19	20.73	21.16	22.37
	6H	22.95	23.29	23.93	24.27	25.49	20.33	20.67	21.30	21.65	22.87
	8H	23.11	23.41	24.09	24.38	25.66	20.52	20.82	21.49	21.79	23.06