

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P519693

Luminaire Tested: **SQ4-075U-0D-830-1D-UNV-STD-W-6**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519693
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-075U-0D-830-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4238.7 lumens
Efficiency: N/A
Efficacy: 153.6 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Indirect

Input Watts (W): 27.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519693
CATALOG NUMBER: SQ4-075U-0D-830-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P519693

CATALOG NUMBER: SQ4-075U-0D-830-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0		
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0		
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0		
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0		
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0		
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0		
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0		
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0		
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0		
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0		
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	3225	38300	10452
100°	3383	32509	26775
105°	3586	22108	31420
110°	3759	15061	30173
115°	3889	10860	24540
120°	3968	8600	18937
125°	3948	7260	14385
130°	3895	6359	11287
135°	3866	5720	9116
140°	3857	5246	7559
145°	3856	4865	6382
150°	3893	4582	5536
155°	3946	4369	4952
160°	3978	4213	4567
165°	4002	4117	4311
170°	4012	4047	4150
175°	4017	4000	4043



TEST NUMBER: P519693

CATALOG NUMBER: SQ4-075U-0D-830-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	306.9	7.2
100°-110°	844.3	19.9
110°-120°	871.5	20.6
120°-130°	698.2	16.5
130°-140°	548.4	12.9
140°-150°	420.3	9.9
150°-160°	302.2	7.1
160°-170°	184.8	4.4
170°-180°	62.3	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	2022.6	47.7
90°-150°	3689.5	87.0
90°-180°	4239.0	100.0
0°-180°	4238.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	1	5	10	12	12	
95°	46	168	543	232	148	51
105°	151	232	930	1417	1322	159
115°	267	325	746	1486	1686	264
125°	368	420	677	1145	1341	328
135°	444	493	658	926	1048	343
145°	514	549	648	789	850	322
155°	581	600	644	709	730	267
165°	628	637	646	673	677	177
175°	651	652	648	656	655	62
180°	651	651	651	651	651	



TEST NUMBER: P519693

CATALOG NUMBER: SQ4-075U-0D-830-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	1.4	5.4	9.7	12.5	12.5
92.5°	19.1	81.6	141.5	54.3	44.6
95°	45.7	167.5	542.7	232.0	148.1
97.5°	74.5	185.7	828.1	638.1	450.2
100°	95.5	197.0	917.8	926.4	755.9
102.5°	115.5	210.5	941.1	1149.3	992.9
105°	150.9	232.1	930.3	1416.8	1322.1
107.5°	184.7	258.9	877.4	1547.8	1576.0
110°	209.0	276.7	837.5	1580.4	1677.8
112.5°	231.2	296.7	797.7	1559.4	1707.7
115°	267.2	325.4	746.2	1485.8	1686.1
117.5°	301.5	355.1	713.5	1382.6	1609.2
120°	322.6	374.0	699.1	1305.2	1539.4
122.5°	341.4	392.8	689.1	1237.4	1459.7
125°	368.2	419.7	677.0	1145.2	1341.4
127.5°	393.7	442.7	668.9	1068.2	1240.4
130°	407.0	457.1	664.5	1022.5	1179.5
132.5°	422.5	472.6	661.2	982.2	1124.1
135°	444.4	493.1	657.6	926.1	1048.0
137.5°	464.9	510.1	654.5	880.8	981.2
140°	480.4	522.3	653.4	850.7	941.4
142.5°	493.7	532.4	651.2	823.8	901.5
145°	513.6	548.8	647.9	789.1	850.0
147.5°	534.9	565.2	646.2	758.4	807.1
150°	548.2	575.3	645.1	741.5	779.4
152.5°	560.4	585.3	644.0	726.9	758.4
155°	581.4	600.4	643.7	709.3	729.6
157.5°	596.7	612.1	643.7	694.7	708.8
160°	607.7	619.9	643.7	686.9	697.7
162.5°	616.6	626.6	644.8	680.2	688.9
165°	628.5	636.6	646.5	672.9	677.0
167.5°	636.8	643.0	647.9	666.7	667.8
170°	642.3	646.4	647.9	664.5	664.5
172.5°	646.8	648.7	647.9	661.1	660.1
175°	650.6	652.0	647.9	656.2	654.8
177.5°	651.8	651.8	647.3	653.9	651.8
180°	650.6	650.6	650.6	650.6	650.6

(END OF REPORT)