

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519717

Luminaire Tested: **SQ4-100U-0D-830-1D-UNV-STD-W-6**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519717
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-100U-0D-830-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5686.5 lumens
Efficiency: N/A
Efficacy: 151.2 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Indirect

Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519717
CATALOG NUMBER: SQ4-100U-0D-830-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P519717

CATALOG NUMBER: SQ4-100U-0D-830-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20								20				20				20				20
RC	80								50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10				0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10				0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8				0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7				0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6				0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5				0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4				0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4				0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3				0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3				0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3				0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2				0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	4248	52478	14030
100°	4562	43699	35761
105°	4791	29585	42530
110°	5088	20171	40393
115°	5258	14592	32853
120°	5306	11559	25356
125°	5316	9746	19356
130°	5252	8562	15128
135°	5189	7686	12217
140°	5172	7050	10142
145°	5194	6551	8569
150°	5251	6166	7439
155°	5294	5873	6662
160°	5344	5674	6141
165°	5377	5537	5796
170°	5396	5440	5580
175°	5404	5378	5438



TEST NUMBER: P519717

CATALOG NUMBER: SQ4-100U-0D-830-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	409.9	7.2
100°-110°	1131.5	19.9
110°-120°	1166.9	20.5
120°-130°	937.7	16.5
130°-140°	736.9	13.0
140°-150°	565.2	9.9
150°-160°	406.2	7.1
160°-170°	248.4	4.4
170°-180°	83.8	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	2708.2	47.6
90°-150°	4948.1	87.0
90°-180°	5686.0	100.0
0°-180°	5686.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	3	6	11	13	14	
95°	60	222	744	306	199	68
105°	202	311	1245	1900	1790	215
115°	361	437	1003	1985	2257	355
125°	496	564	909	1538	1805	441
135°	596	661	884	1246	1404	462
145°	692	740	872	1060	1141	433
155°	780	806	865	952	982	359
165°	844	855	870	903	910	238
175°	875	876	871	884	881	83
180°	875	875	875	875	875	

TEST NUMBER: P519717

CATALOG NUMBER: SQ4-100U-OD-830-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	2.8	5.5	11.2	12.6	14.0
92.5°	25.2	104.6	187.1	68.3	53.2
95°	60.2	221.8	743.6	305.6	198.8
97.5°	99.7	248.4	1101.5	848.0	614.2
100°	128.8	264.4	1233.7	1242.4	1009.6
102.5°	156.8	282.5	1259.4	1535.0	1314.3
105°	201.6	311.2	1244.9	1900.5	1789.6
107.5°	249.3	346.7	1175.4	2076.7	2117.2
110°	282.9	370.5	1121.6	2114.6	2246.1
112.5°	313.1	397.4	1071.2	2084.7	2278.5
115°	361.3	436.6	1002.6	1984.8	2257.3
117.5°	403.3	478.3	957.5	1844.2	2154.2
120°	431.3	505.2	939.6	1749.1	2061.2
122.5°	458.2	528.8	925.0	1660.2	1955.9
125°	495.7	564.2	908.8	1538.0	1805.0
127.5°	527.6	596.1	899.3	1434.6	1664.9
130°	548.9	617.4	894.8	1371.4	1580.9
132.5°	569.1	634.2	890.3	1318.3	1508.1
135°	596.5	660.9	883.6	1245.7	1404.5
137.5°	627.3	685.9	880.2	1184.6	1320.2
140°	644.1	701.6	878.0	1143.9	1263.1
142.5°	663.2	716.3	875.7	1107.8	1212.6
145°	691.7	739.7	872.4	1060.5	1141.2
147.5°	719.2	761.1	869.3	1020.6	1083.3
150°	739.4	773.6	868.2	996.8	1047.4
152.5°	755.0	787.1	867.1	976.4	1018.3
155°	780.0	806.0	865.4	951.5	981.6
157.5°	802.9	822.9	865.7	933.3	953.9
160°	816.4	834.2	866.8	923.1	938.2
162.5°	827.6	843.2	867.9	914.1	925.9
165°	844.4	855.3	869.6	903.3	910.2
167.5°	857.3	863.8	871.0	896.8	899.0
170°	864.0	869.5	871.0	893.4	893.4
172.5°	869.6	872.9	871.0	888.9	887.8
175°	875.2	876.5	871.0	883.5	880.8
177.5°	877.4	876.3	870.7	878.5	876.3
180°	875.2	875.2	875.2	875.2	875.2

(END OF REPORT)