

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P854318

Luminaire Tested: SQ2-PW1-150U-050D-940-UNV-STD-W-4

Issue Date: 7/12/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P854318  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-14, G2-2308-131-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/12/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2-PW1-150U-050D-940-UNV-STD-W-4  
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 1500 LUMENS PER FOOT  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8817.5 lumens  
Efficiency: N/A  
Efficacy: 118.5 lumens/watt  
Spacing Criteria (0/90/45): 1.27 / 1.11 / 1.22  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 74.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P854318

CATALOG NUMBER: SQ2-PW1-150U-050D-940-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P854318

CATALOG NUMBER: SQ2-PW1-150U-050D-940-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28
1	93	89	85	82	83	80	77	74	63	61	59	47	46	44	32	32	31	24
2	85	78	72	68	76	70	65	61	55	52	49	41	39	38	29	28	26	21
3	78	69	62	57	69	62	56	52	49	45	42	37	34	32	26	24	23	18
4	71	61	54	48	64	55	49	44	44	39	36	33	30	28	23	21	20	16
5	65	54	47	41	58	49	43	38	39	34	31	30	27	24	21	19	18	14
6	60	49	41	36	54	44	37	33	35	30	27	27	24	21	19	17	16	12
7	56	44	36	31	50	40	33	29	32	27	24	24	21	19	17	15	14	11
8	51	40	32	27	46	36	30	25	29	24	21	22	19	17	16	14	12	10
9	48	36	29	24	43	33	27	22	27	22	19	21	17	15	15	13	11	9
10	45	33	26	22	40	30	24	20	24	20	17	19	16	14	14	12	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	17933	17933	17933
5°	17812	17950	18122
10°	17846	18052	18279
15°	17840	18176	18389
20°	17847	18156	18029
25°	17751	17770	16753
30°	17631	16744	15146
35°	17493	15408	13677
40°	17144	14046	12083
45°	16472	12632	10554
50°	15330	11293	9033
55°	14024	9976	7324
60°	12571	8677	6319
65°	10991	7477	5616
70°	8988	6642	5094
75°	6993	5739	4685
80°	5216	4919	4128
85°	3520	3724	2353

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 16472 cd/sqm



TEST NUMBER: P854318

CATALOG NUMBER: SQ2-PW1-150U-050D-940-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	105.8	1.2
10°-20°	306.4	3.5
20°-30°	451.0	5.1
30°-40°	493.0	5.6
40°-50°	442.3	5.0
50°-60°	329.9	3.7
60°-70°	208.5	2.4
70°-80°	103.3	1.2
80°-90°	25.3	0.3
90°-100°	392.1	4.4
100°-110°	1284.0	14.6
110°-120°	1269.4	14.4
120°-130°	1037.7	11.8
130°-140°	846.8	9.6
140°-150°	659.0	7.5
150°-160°	474.5	5.4
160°-170°	290.3	3.3
170°-180°	98.1	1.1
0°-30°	863.1	9.8
0°-40°	1356.2	15.4
0°-60°	2128.4	24.1
0°-90°	2465.5	28.0
90°-120°	2945.6	33.4
90°-150°	5489.1	62.3
90°-180°	6352.0	72.0
0°-180°	8817.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1111	1111	1111	1111	1111	
5°	1099	1117	1108	1109	1118	105
15°	1067	1088	1087	1095	1100	301
25°	996	1018	998	956	940	459
35°	888	878	782	714	694	553
45°	721	664	553	484	462	553
55°	498	451	354	278	260	445
65°	288	264	196	157	147	285
75°	112	120	92	77	75	124
85°	19	24	20	14	13	24
90°	1	3	8	7	8	3
95°	55	160	713	254	165	62
105°	223	318	1274	2422	2300	235
115°	402	480	1036	2140	2512	397
125°	560	624	1021	1687	1982	498
135°	674	745	1012	1455	1640	521
145°	788	846	1010	1252	1372	494
155°	898	928	1016	1120	1164	413
165°	980	990	1021	1060	1071	276
175°	1025	1025	1026	1033	1031	97
180°	1029	1029	1029	1029	1029	



TEST NUMBER: P854318

CATALOG NUMBER: SQ2-PW1-150U-050D-940-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1110.7	1110.7	1110.7	1110.7	1110.7
2.5°	1103.1	1117.1	1108.1	1109.0	1111.5
5°	1099.0	1116.6	1107.5	1108.8	1118.1
7.5°	1093.5	1111.3	1104.5	1108.3	1117.4
10°	1088.5	1107.1	1101.1	1106.6	1114.9
12.5°	1081.7	1101.1	1096.9	1103.2	1111.5
15°	1067.3	1088.0	1087.4	1094.9	1100.1
17.5°	1050.6	1071.3	1070.3	1072.2	1074.7
20°	1038.7	1059.4	1056.7	1049.3	1049.3
22.5°	1021.8	1044.2	1037.3	1017.0	1010.4
25°	996.4	1018.1	997.5	955.9	940.4
27.5°	966.8	984.4	942.9	883.8	862.3
30°	945.7	959.1	898.1	833.1	812.4
32.5°	923.7	928.8	852.4	784.8	762.4
35°	887.5	878.2	781.7	713.6	693.9
37.5°	844.7	817.0	713.8	642.4	620.7
40°	813.4	774.1	666.4	595.0	573.3
42.5°	778.7	729.5	621.6	550.2	527.6
45°	721.4	663.5	553.2	484.0	462.2
47.5°	656.9	599.4	489.3	422.3	403.6
50°	610.3	554.5	449.6	382.4	359.6
52.5°	562.9	512.9	410.6	341.6	310.6
55°	498.2	450.6	354.4	277.8	260.2
57.5°	431.6	390.4	303.4	233.9	219.4
60°	389.3	353.1	268.7	210.2	195.7
62.5°	348.6	316.6	234.8	188.2	176.2
65°	287.7	263.9	195.7	157.4	147.0
67.5°	228.5	215.2	162.7	129.1	122.3
70°	190.4	186.3	140.7	113.1	107.9
72.5°	157.4	159.1	119.5	97.9	94.4
75°	112.1	120.4	92.0	77.2	75.1
77.5°	76.4	88.8	68.1	57.1	55.4
80°	56.1	68.5	52.9	44.4	44.4
82.5°	39.1	49.1	37.7	33.4	33.4
85°	19.0	24.2	20.1	13.7	12.7
87.5°	5.3	8.2	5.1	4.0	4.2
90°	1.1	3.1	8.5	7.4	8.5
92.5°	18.0	65.6	201.4	65.5	52.5
95°	55.0	159.5	712.9	253.9	165.0
97.5°	99.8	210.3	1223.1	739.9	458.6
100°	131.2	236.6	1415.2	1263.8	837.7
102.5°	166.7	269.7	1394.0	1862.2	1443.5
105°	223.2	318.3	1274.5	2421.5	2300.5
107.5°	278.8	366.1	1158.0	2473.8	2606.8
110°	315.2	400.0	1102.1	2412.9	2660.1



TEST NUMBER: P854318

CATALOG NUMBER: SQ2-PW1-150U-050D-940-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	349.9	432.2	1068.3	2307.0	2623.7
115°	401.9	480.5	1035.5	2139.7	2512.0
117.5°	452.5	525.9	1023.0	1975.3	2353.4
120°	485.5	554.8	1019.6	1879.4	2247.6
122.5°	515.1	582.7	1019.6	1796.7	2138.4
125°	559.5	623.6	1020.7	1687.4	1982.1
127.5°	597.2	662.5	1019.4	1606.7	1863.2
130°	620.9	687.1	1018.6	1558.0	1789.6
132.5°	642.0	709.9	1016.0	1516.0	1726.1
135°	673.7	745.1	1012.2	1455.4	1640.5
137.5°	707.2	777.9	1009.9	1392.1	1559.5
140°	730.9	799.1	1009.0	1352.2	1510.4
142.5°	754.6	818.7	1009.0	1309.5	1452.8
145°	788.0	845.9	1010.1	1251.9	1371.8
147.5°	823.1	871.3	1011.6	1201.7	1292.3
150°	845.1	887.5	1013.3	1172.6	1249.1
152.5°	867.1	904.5	1014.1	1148.6	1211.9
155°	898.0	928.0	1016.4	1120.0	1163.5
157.5°	925.7	947.4	1018.8	1097.5	1129.0
160°	943.5	961.0	1019.6	1084.7	1109.5
162.5°	958.7	973.0	1019.6	1074.4	1092.6
165°	980.5	989.8	1020.7	1060.1	1071.4
167.5°	998.9	1003.4	1021.9	1048.9	1055.2
170°	1009.0	1011.1	1022.8	1042.9	1045.0
172.5°	1016.7	1017.9	1025.3	1038.7	1039.1
175°	1024.9	1024.9	1026.0	1033.3	1031.2
177.5°	1029.1	1028.3	1027.4	1032.4	1029.1
180°	1029.1	1029.1	1029.1	1029.1	1029.1



TEST NUMBER: P854318

CATALOG NUMBER: SQ2-PW1-150U-050D-940-UNV-STD-W-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.56	15.24	15.69	16.36	17.91	11.05	11.72	12.18	12.84	14.40
	3H	15.87	16.47	17.01	17.60	19.17	12.24	12.84	13.38	13.97	15.54
	4H	16.23	16.81	17.38	17.94	19.51	12.68	13.25	13.83	14.38	15.96
	6H	16.43	16.95	17.59	18.08	19.67	12.99	13.51	14.14	14.64	16.23
	8H	16.46	16.96	17.62	18.10	19.68	13.05	13.55	14.21	14.70	16.28
	12H	16.45	16.92	17.61	18.06	19.66	13.06	13.53	14.22	14.67	16.28
4H	2H	14.64	15.21	15.80	16.34	17.92	11.71	12.28	12.86	13.41	14.99
	3H	16.17	16.65	17.33	17.80	19.39	13.08	13.55	14.24	14.71	16.30
	4H	16.67	17.11	17.83	18.25	19.86	13.62	14.06	14.78	15.20	16.81
	6H	16.99	17.37	18.16	18.53	20.13	14.01	14.39	15.18	15.55	17.15
	8H	17.07	17.42	18.24	18.57	20.19	14.11	14.46	15.28	15.62	17.24
	12H	17.08	17.39	18.26	18.56	20.18	14.13	14.44	15.31	15.61	17.23
8H	4H	16.70	17.05	17.86	18.20	19.82	13.93	14.28	15.10	15.44	17.05
	6H	17.13	17.41	18.31	18.61	20.23	14.43	14.72	15.62	15.92	17.53
	8H	17.27	17.52	18.46	18.70	20.33	14.59	14.84	15.78	16.02	17.65
	12H	17.33	17.55	18.52	18.72	20.39	14.65	14.86	15.84	16.04	17.71
12H	4H	16.65	16.96	17.83	18.13	19.75	13.94	14.25	15.12	15.42	17.04
	6H	17.12	17.37	18.31	18.54	20.18	14.50	14.75	15.69	15.92	17.56
	8H	17.27	17.49	18.47	18.67	20.33	14.67	14.89	15.87	16.07	17.73