

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519741

Luminaire Tested: **SQ4-125U-0D-830-1D-UNV-STD-W-6**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519741
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-125U-0D-830-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7078.2 lumens
Efficiency: N/A
Efficacy: 149.0 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Indirect

Input Watts (W): 47.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519741
CATALOG NUMBER: SQ4-125U-0D-830-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P519741

CATALOG NUMBER: SQ4-125U-0D-830-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20								20				20				20				20
RC	80								50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10				0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10				0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8				0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7				0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6				0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5				0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4				0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4				0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3				0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3				0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3				0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2				0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	5519	59337	20995
100°	5689	52097	45219
105°	6074	36313	50985
110°	6305	25244	48579
115°	6567	18519	40473
120°	6666	14587	31563
125°	6606	12252	24369
130°	6522	10746	18992
135°	6452	9659	15345
140°	6415	8860	12740
145°	6439	8233	10740
150°	6528	7738	9354
155°	6607	7375	8370
160°	6674	7122	7707
165°	6724	6947	7258
170°	6770	6822	6988
175°	6778	6744	6821



TEST NUMBER: P519741

CATALOG NUMBER: SQ4-125U-0D-830-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	512.9	7.2
100°-110°	1381.7	19.5
110°-120°	1450.0	20.5
120°-130°	1176.7	16.6
130°-140°	922.8	13.0
140°-150°	708.5	10.0
150°-160°	509.4	7.2
160°-170°	311.2	4.4
170°-180°	105.0	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	3344.6	47.3
90°-150°	6152.6	86.9
90°-180°	7078.0	100.0
0°-180°	7078.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	3	8	17	18	18	
95°	78	279	841	430	298	87
105°	256	398	1528	2286	2145	269
115°	451	552	1272	2459	2781	444
125°	616	708	1142	1931	2272	550
135°	742	828	1110	1558	1764	572
145°	858	924	1096	1332	1430	538
155°	974	1009	1087	1195	1233	448
165°	1056	1068	1091	1134	1140	298
175°	1098	1096	1092	1108	1105	104
180°	1096	1096	1096	1096	1096	



TEST NUMBER: P519741

CATALOG NUMBER: SQ4-125U-0D-830-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	2.8	8.3	16.8	18.2	18.2
92.5°	34.1	120.4	238.0	114.6	79.6
95°	78.2	279.0	840.8	430.0	297.5
97.5°	124.9	319.3	1318.8	1101.7	830.8
100°	160.6	335.4	1470.8	1538.8	1276.6
102.5°	195.3	358.1	1521.1	1866.2	1651.0
105°	255.6	397.6	1528.0	2286.1	2145.4
107.5°	312.6	439.3	1463.0	2501.9	2538.2
110°	350.6	470.8	1403.7	2568.8	2701.3
112.5°	390.8	502.3	1346.7	2554.0	2771.7
115°	451.2	552.2	1272.4	2458.6	2780.9
117.5°	506.2	601.0	1214.9	2306.4	2665.3
120°	541.9	633.4	1185.8	2197.1	2565.8
122.5°	573.2	663.6	1164.6	2085.3	2453.0
125°	616.0	707.5	1142.5	1931.1	2272.5
127.5°	657.0	747.2	1128.6	1795.1	2099.9
130°	681.6	771.8	1123.0	1717.1	1984.8
132.5°	706.2	795.2	1117.4	1648.4	1894.3
135°	741.7	827.7	1110.4	1557.9	1764.1
137.5°	775.5	858.0	1106.8	1481.1	1650.4
140°	798.9	878.2	1103.4	1433.8	1586.7
142.5°	823.5	897.3	1101.2	1389.6	1518.5
145°	857.6	924.5	1096.5	1331.9	1430.3
147.5°	894.5	952.7	1091.7	1283.4	1360.7
150°	919.1	969.6	1089.5	1252.9	1317.1
152.5°	941.4	985.4	1088.3	1228.1	1280.3
155°	973.5	1009.0	1086.7	1195.1	1233.3
157.5°	1001.8	1029.3	1087.0	1171.9	1197.6
160°	1019.6	1042.8	1088.1	1158.3	1177.5
162.5°	1035.3	1054.1	1089.2	1147.0	1160.7
165°	1055.9	1068.2	1090.9	1134.3	1139.8
167.5°	1072.7	1079.8	1092.3	1124.4	1126.6
170°	1083.9	1086.6	1092.3	1118.8	1118.8
172.5°	1090.6	1091.1	1093.4	1113.2	1113.2
175°	1097.8	1096.5	1092.3	1107.6	1104.8
177.5°	1100.9	1098.7	1093.1	1102.0	1099.8
180°	1096.5	1096.5	1096.5	1096.5	1096.5

(END OF REPORT)