

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P854363

Luminaire Tested: SQ2-WBM-075U-125D-940-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P854363
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-11, G3-2104-222-8)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-WBM-075U-125D-940-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8877.2 lumens
Efficiency: N/A
Efficacy: 121.6 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.18 / 1.17
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 73
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P854363

CATALOG NUMBER: SQ2-WBM-075U-125D-940-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P854363

CATALOG NUMBER: SQ2-WBM-075U-125D-940-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70	65
1	103	100	97	94	97	94	92	89	84	82	80	74	73	71	65	64	63	59
2	96	90	85	81	91	85	81	77	76	73	70	68	66	64	60	59	57	54
3	89	82	75	71	84	77	72	68	70	66	62	63	59	57	56	54	52	49
4	83	74	67	62	79	70	65	60	64	59	55	58	54	51	52	49	47	44
5	78	67	60	55	73	64	58	53	58	53	50	53	49	46	48	45	43	40
6	72	62	55	49	68	59	53	48	54	49	45	49	45	42	44	41	39	36
7	68	57	49	44	64	54	48	43	50	44	41	45	41	38	41	38	35	33
8	63	52	45	40	60	50	44	39	46	41	37	42	38	35	38	35	33	31
9	59	48	41	37	56	46	40	36	43	37	34	39	35	32	36	32	30	28
10	56	45	38	34	53	43	37	33	40	35	31	37	32	29	34	30	28	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	59473	59473	59473
5°	59940	59221	60026
10°	60581	59940	60599
15°	61553	60740	60495
20°	61855	60458	59369
25°	60690	58772	57774
30°	57586	55754	54178
35°	51637	50407	48846
40°	42392	41456	39943
45°	26508	30102	24048
50°	10482	17804	9367
55°	5084	8087	5025
60°	2386	3956	2183
65°	2139	2300	2059
70°	2096	2143	1945
75°	2040	2040	1847
80°	1962	1962	1767
85°	1760	1760	1760

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 30102 cd/sqm



TEST NUMBER: P854363

CATALOG NUMBER: SQ2-WBM-075U-125D-940-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	352.0	4.0
10°-20°	1028.7	11.6
20°-30°	1520.8	17.1
30°-40°	1571.5	17.7
40°-50°	945.6	10.7
50°-60°	227.3	2.6
60°-70°	62.1	0.7
70°-80°	34.6	0.4
80°-90°	11.3	0.1
90°-100°	190.8	2.1
100°-110°	632.4	7.1
110°-120°	627.7	7.1
120°-130°	511.3	5.8
130°-140°	415.5	4.7
140°-150°	322.7	3.6
150°-160°	232.5	2.6
160°-170°	142.4	1.6
170°-180°	48.1	0.5
0°-30°	2901.5	32.7
0°-40°	4473.0	50.4
0°-60°	5645.8	63.6
0°-90°	5753.8	64.8
90°-120°	1450.9	16.3
90°-150°	2700.4	30.4
90°-180°	3123.0	35.2
0°-180°	8877.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3684	3684	3684	3684	3684	
5°	3698	3687	3654	3706	3704	353
15°	3682	3710	3634	3635	3619	1038
25°	3407	3433	3299	3252	3243	1557
35°	2620	2614	2557	2508	2478	1612
45°	1161	1318	1318	1246	1053	899
55°	181	203	287	194	178	184
65°	56	59	60	56	54	57
75°	33	35	33	32	30	34
85°	10	10	10	10	10	11
90°	0	1	3	4	4	2
95°	27	80	346	123	82	31
105°	111	158	633	1194	1116	117
115°	197	236	510	1061	1241	195
125°	276	306	500	834	983	245
135°	330	364	496	715	807	255
145°	383	412	495	616	674	240
155°	438	453	498	550	570	202
165°	480	486	500	520	525	135
175°	502	502	503	506	506	48
180°	504	504	504	504	504	



TEST NUMBER: P854363

CATALOG NUMBER: SQ2-WBM-075U-125D-940-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3683.5	3683.5	3683.5	3683.5	3683.5
2.5°	3697.0	3687.9	3659.0	3692.7	3686.9
5°	3698.3	3686.9	3653.9	3705.6	3703.6
7.5°	3697.7	3691.7	3663.6	3703.4	3695.3
10°	3695.1	3698.2	3656.0	3699.3	3696.2
12.5°	3693.4	3707.3	3651.8	3682.3	3674.2
15°	3682.4	3710.3	3633.8	3634.6	3619.1
17.5°	3642.3	3676.2	3577.0	3547.6	3528.0
20°	3600.0	3633.1	3518.7	3474.9	3455.3
22.5°	3534.1	3564.7	3437.6	3393.1	3376.7
25°	3406.7	3432.6	3299.0	3252.3	3243.0
27.5°	3235.0	3245.9	3123.2	3077.4	3061.5
30°	3088.8	3089.8	2990.5	2936.0	2906.0
32.5°	2918.9	2911.7	2835.0	2780.3	2742.9
35°	2619.8	2613.6	2557.4	2508.2	2478.2
37.5°	2268.2	2267.2	2213.7	2171.2	2141.0
40°	2011.3	2018.5	1966.9	1913.7	1895.1
42.5°	1703.7	1757.2	1713.4	1655.2	1643.3
45°	1160.9	1317.9	1318.3	1246.3	1053.2
47.5°	664.0	833.4	948.8	734.5	545.3
50°	417.3	545.3	708.8	447.3	372.9
52.5°	296.4	359.2	524.6	314.6	278.2
55°	180.6	203.4	287.3	194.0	178.5
57.5°	109.4	130.7	166.5	130.1	109.9
60°	73.9	93.6	122.5	86.2	67.6
62.5°	65.5	72.7	96.3	67.9	60.8
65°	56.0	59.1	60.2	55.9	53.9
67.5°	49.4	51.5	50.5	49.4	46.3
70°	44.4	46.4	45.4	44.3	41.2
72.5°	39.3	41.4	40.4	39.2	37.0
75°	32.7	34.8	32.7	31.6	29.6
77.5°	25.4	27.2	26.2	25.3	23.2
80°	21.1	22.2	21.1	21.1	19.0
82.5°	16.9	17.1	16.1	16.0	14.8
85°	9.5	10.5	9.5	9.5	9.5
87.5°	3.4	3.6	4.0	4.2	3.4
90°	0.0	1.0	3.1	4.2	4.2
92.5°	8.4	32.3	95.0	30.8	25.9
95°	27.2	80.3	345.7	123.4	82.5
97.5°	49.9	105.5	603.5	352.0	222.5
100°	65.8	118.9	698.7	600.1	397.9
102.5°	83.3	134.8	692.9	917.1	692.9
105°	110.7	157.7	632.9	1194.1	1116.5
107.5°	138.7	180.6	575.5	1222.3	1281.3
110°	154.6	196.4	546.2	1194.4	1313.9



TEST NUMBER: P854363

CATALOG NUMBER: SQ2-WBM-075U-125D-940-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	171.3	212.3	528.7	1145.0	1297.2
115°	197.4	236.2	509.7	1061.1	1240.8
117.5°	223.3	257.8	502.8	980.8	1169.4
120°	239.2	272.9	500.3	930.6	1113.4
122.5°	253.4	286.3	500.3	889.3	1058.2
125°	275.7	306.4	500.3	833.7	982.8
127.5°	294.1	324.1	499.0	791.7	919.1
130°	305.0	336.6	498.2	767.1	881.5
132.5°	315.0	347.5	497.4	746.8	849.8
135°	330.0	363.7	496.1	715.4	807.4
137.5°	346.3	378.8	494.9	685.1	766.2
140°	357.2	388.9	494.0	664.9	739.5
142.5°	367.2	398.1	494.9	644.7	711.1
145°	383.3	411.9	495.1	615.5	673.7
147.5°	400.6	424.5	495.3	590.7	634.0
150°	411.5	433.0	496.1	576.3	613.1
152.5°	421.5	442.2	496.9	564.5	593.9
155°	437.6	452.9	498.2	549.8	570.3
157.5°	453.3	465.1	499.5	539.5	554.0
160°	461.6	471.9	500.3	531.9	543.1
162.5°	470.0	477.8	500.3	526.8	535.6
165°	480.4	485.5	500.3	520.2	525.4
167.5°	490.1	492.7	501.3	514.3	517.0
170°	495.1	496.1	501.3	511.8	512.8
172.5°	498.4	499.4	502.2	509.3	509.5
175°	502.4	502.4	503.4	506.5	505.5
177.5°	504.5	504.5	503.6	505.3	503.6
180°	504.5	504.5	504.5	504.5	504.5



TEST NUMBER: P854363

CATALOG NUMBER: SQ2-WBM-075U-125D-940-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.43	9.24	9.28	10.08	11.14	8.10	8.90	8.95	9.75	10.81
	3H	8.95	9.66	9.81	10.52	11.60	8.60	9.32	9.47	10.18	11.26
	4H	9.21	9.88	10.10	10.75	11.84	8.84	9.51	9.73	10.38	11.47
	6H	9.44	10.05	10.33	10.93	12.03	9.04	9.66	9.94	10.53	11.64
	8H	9.51	10.09	10.41	10.98	12.09	9.11	9.69	10.01	10.58	11.69
	12H	9.55	10.10	10.45	10.98	12.11	9.15	9.71	10.06	10.59	11.72
4H	2H	8.45	9.12	9.33	9.98	11.08	8.14	8.81	9.03	9.68	10.77
	3H	9.18	9.72	10.07	10.62	11.73	8.87	9.41	9.76	10.31	11.42
	4H	9.58	10.08	10.49	10.98	12.11	9.23	9.73	10.14	10.63	11.76
	6H	9.95	10.38	10.87	11.30	12.44	9.58	10.00	10.50	10.92	12.06
	8H	10.08	10.48	11.00	11.39	12.54	9.70	10.09	10.62	11.01	12.16
	12H	10.16	10.51	11.10	11.45	12.60	9.78	10.13	10.72	11.06	12.22
8H	4H	9.66	10.06	10.59	10.97	12.12	9.34	9.74	10.26	10.65	11.80
	6H	10.16	10.48	11.10	11.44	12.59	9.81	10.13	10.75	11.09	12.24
	8H	10.37	10.66	11.33	11.60	12.77	10.01	10.30	10.97	11.25	12.41
	12H	10.53	10.78	11.48	11.72	12.94	10.17	10.42	11.12	11.36	12.58
12H	4H	9.64	9.99	10.57	10.92	12.08	9.32	9.67	10.26	10.61	11.76
	6H	10.17	10.46	11.13	11.41	12.58	9.84	10.12	10.79	11.07	12.24
	8H	10.42	10.67	11.37	11.61	12.83	10.07	10.32	11.03	11.26	12.48