

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936924

Luminaire Tested: SQ4-FB-050U-125D-927-1D-UNV-STD-W-8

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936924
REPORT IS A COMBINATION OF REPORTS P933488 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-050U-125D-927-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9337.8 lumens
Efficiency: N/A
Efficacy: 83.4 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 112
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936924
CATALOG NUMBER: SQ4-FB-050U-125D-927-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P936924

CATALOG NUMBER: SQ4-FB-050U-125D-927-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67	67	67	67
1	101	96	92	88	95	91	87	83	80	78	75	71	69	67	62	61	59	55	55	55	55
2	91	83	76	71	86	78	72	67	70	65	61	61	58	55	54	51	49	45	45	45	45
3	83	72	64	58	77	68	61	55	61	55	50	54	49	45	47	44	41	37	37	37	37
4	75	64	55	48	70	60	52	46	53	47	42	47	42	38	42	38	34	31	31	31	31
5	69	56	47	41	64	53	45	39	47	41	36	42	37	32	37	33	29	26	26	26	26
6	63	50	41	35	59	47	39	34	42	36	31	38	32	28	33	29	25	23	23	23	23
7	58	45	36	30	55	43	35	29	38	32	27	34	29	24	30	26	22	20	20	20	20
8	54	41	32	27	51	39	31	26	35	28	24	31	26	22	27	23	20	17	17	17	17
9	50	37	29	24	47	35	28	23	32	25	21	28	23	19	25	21	17	15	15	15	15
10	47	34	26	21	44	32	25	20	29	23	19	26	21	17	23	19	16	14	14	14	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3760	3760	3760
5°	3673	4347	5054
10°	3332	6336	8380
15°	2832	8277	10118
20°	2306	9592	10312
25°	1923	10038	10103
30°	1622	10101	10084
35°	1434	9933	10344
40°	1250	9715	10614
45°	1131	9556	10656
50°	1038	9412	10479
55°	994	9202	10015
60°	1017	8798	9281
65°	1058	8183	8273
70°	1128	7137	6990
75°	1250	5819	5454
80°	1365	4035	3676
85°	1211	2141	1881

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 10656 cd/sqm



TEST NUMBER: P936924

CATALOG NUMBER: SQ4-FB-050U-125D-927-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.8	1.1
10°-20°	464.7	5.0
20°-30°	812.8	8.7
30°-40°	1046.3	11.2
40°-50°	1168.7	12.5
50°-60°	1119.3	12.0
60°-70°	887.1	9.5
70°-80°	521.6	5.6
80°-90°	146.7	1.6
90°-100°	230.5	2.5
100°-110°	606.1	6.5
110°-120°	628.5	6.7
120°-130°	504.1	5.4
130°-140°	395.5	4.2
140°-150°	303.6	3.3
150°-160°	218.6	2.3
160°-170°	133.8	1.4
170°-180°	45.2	0.5
0°-30°	1382.3	14.8
0°-40°	2428.6	26.0
0°-60°	4716.5	50.5
0°-90°	6271.9	67.2
90°-120°	1465.1	15.7
90°-150°	2668.3	28.6
90°-180°	3066.0	32.8
0°-180°	9337.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	810	810	810	810	810	
5°	790	847	954	1079	1118	73
15°	592	1092	1840	2231	2301	165
25°	378	1238	2192	2288	2291	174
35°	255	1183	2064	2181	2267	159
45°	175	943	1824	2090	2184	135
55°	125	599	1548	1798	1848	114
65°	99	318	1149	1293	1311	98
75°	73	195	631	693	696	76
85°	26	60	156	172	175	28
90°	3	9	24	12	12	4
95°	30	119	397	205	139	34
105°	109	165	670	1017	949	116
115°	194	236	537	1071	1222	192
125°	270	302	488	825	973	240
135°	322	354	473	666	755	249
145°	373	397	467	568	613	234
155°	422	433	467	513	528	194
165°	455	461	467	485	491	128
175°	473	473	470	476	476	45
180°	473	473	473	473	473	



TEST NUMBER: P936924

CATALOG NUMBER: SQ4-FB-050U-125D-927-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	810.5	810.5	810.5	810.5	810.5	810.5	810.5	810.5	810.5	810.5	810.5
2.5°	810.5	810.5	815.7	818.4	823.5	826.1	831.4	836.6	852.2	854.9	860.0
5°	789.6	800.1	834.0	847.0	883.5	933.0	953.9	987.8	1058.1	1078.9	1091.9
7.5°	758.4	781.9	865.2	886.1	977.3	1107.6	1162.3	1235.3	1347.3	1402.1	1446.4
10°	708.9	758.4	906.9	956.4	1105.0	1303.1	1404.7	1506.4	1675.8	1751.4	1780.0
12.5°	654.1	735.0	951.3	1019.0	1232.7	1522.0	1644.5	1756.5	1949.4	2051.0	2066.7
15°	591.6	701.1	992.9	1091.9	1368.2	1704.4	1839.9	1978.1	2157.9	2230.8	2249.1
17.5°	536.8	675.0	1032.0	1136.3	1472.5	1868.6	2006.7	2121.4	2267.3	2316.9	2329.9
20°	469.1	633.3	1058.1	1193.6	1582.0	1988.5	2121.4	2210.0	2309.1	2340.3	2345.5
22.5°	419.6	589.0	1073.8	1214.4	1654.9	2061.4	2173.6	2243.9	2311.6	2322.1	2324.7
25°	377.9	539.5	1071.1	1237.9	1717.5	2105.8	2191.8	2243.9	2283.0	2288.2	2288.2
27.5°	338.8	484.7	1060.7	1243.2	1764.4	2116.2	2184.0	2220.4	2238.7	2249.1	2249.1
30°	304.9	432.6	1034.6	1232.7	1785.2	2105.8	2160.5	2178.7	2197.0	2212.6	2220.4
32.5°	278.9	383.1	995.5	1211.8	1787.8	2079.7	2118.8	2129.2	2155.3	2191.8	2204.8
35°	255.4	333.6	951.3	1183.2	1772.2	2038.0	2064.1	2074.5	2126.6	2181.3	2199.6
37.5°	231.9	297.1	893.9	1133.7	1748.7	1988.5	2006.7	2024.9	2105.8	2170.9	2191.8
40°	208.5	265.8	826.1	1078.9	1712.2	1928.5	1944.2	1972.8	2079.7	2155.3	2176.1
42.5°	190.3	239.8	753.2	1021.6	1665.4	1860.8	1884.3	1925.9	2048.4	2129.2	2152.7
45°	174.6	213.7	675.0	943.4	1605.4	1790.4	1824.3	1881.6	2011.9	2090.2	2111.0
47.5°	159.0	195.4	594.2	862.6	1540.2	1720.0	1764.4	1829.5	1962.4	2038.0	2056.3
50°	145.9	177.3	513.4	776.6	1469.9	1644.5	1696.6	1764.4	1899.9	1970.3	1993.7
52.5°	135.5	161.5	437.8	690.6	1389.1	1566.3	1626.2	1696.6	1824.3	1892.0	1907.7
55°	125.1	148.5	372.7	599.4	1305.7	1482.9	1548.1	1615.8	1740.9	1798.3	1808.7
57.5°	119.9	138.1	317.9	513.4	1217.1	1389.1	1462.1	1524.6	1641.9	1686.1	1696.6
60°	112.0	130.3	276.3	440.4	1120.7	1300.5	1363.0	1425.6	1524.6	1561.1	1568.9
62.5°	104.3	125.1	245.0	370.1	1021.6	1196.2	1258.8	1316.1	1399.5	1425.6	1436.0
65°	99.0	119.9	221.5	317.9	920.0	1086.8	1149.3	1198.8	1266.6	1292.7	1297.8
67.5°	93.8	114.7	203.3	273.7	818.4	977.3	1024.2	1071.1	1123.3	1149.3	1151.9
70°	86.0	109.5	187.6	242.4	714.1	852.2	891.3	940.8	982.5	995.5	1003.4
72.5°	80.8	101.6	177.3	218.9	607.2	732.3	768.8	797.5	834.0	847.0	847.0
75°	73.0	91.2	166.8	195.4	497.8	599.4	630.7	659.4	688.0	693.2	685.5
77.5°	65.1	80.8	143.4	164.2	388.3	474.3	500.3	516.1	539.5	544.7	547.3
80°	54.7	70.4	112.0	127.7	281.4	349.2	367.4	380.5	401.3	401.3	406.6
82.5°	41.7	54.7	80.8	91.2	190.3	239.8	255.4	263.2	276.3	276.3	276.3
85°	26.0	33.9	52.1	59.9	114.7	145.9	156.4	159.0	169.4	172.0	172.0
87.5°	13.0	18.2	33.9	36.5	59.9	75.6	75.6	80.8	80.8	78.2	75.6
90°	3.2	5.7	8.2	8.9	13.9	20.7	24.1	21.4	16.1	12.1	12.1
92.5°	12.7	34.3	55.9	61.3	86.2	119.3	135.8	119.0	85.5	60.3	57.9
95°	30.5	70.0	109.5	119.4	211.9	335.3	397.1	354.4	268.9	204.7	197.5
97.5°	52.7	87.5	122.4	131.1	285.4	491.3	594.2	567.2	513.1	472.6	458.8
100°	69.8	101.4	133.0	140.9	312.2	540.6	654.8	656.8	660.7	663.7	647.2
102.5°	84.5	114.0	143.4	150.8	324.5	556.2	672.0	706.4	775.2	826.8	812.7
105°	109.2	134.1	159.2	165.4	333.6	557.9	670.1	747.2	901.6	1017.3	1009.7
107.5°	134.6	157.8	181.1	187.0	335.3	533.1	631.9	739.6	954.9	1116.3	1118.2
110°	151.7	172.7	193.8	199.0	332.8	511.0	600.2	720.6	961.2	1141.7	1149.6



TEST NUMBER: P936924

CATALOG NUMBER: SQ4-FB-050U-125D-927-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	168.6	188.6	208.6	213.6	332.9	491.9	571.3	694.5	940.8	1125.5	1137.7
115°	194.0	212.4	230.9	235.5	336.0	469.9	536.8	655.4	892.7	1070.6	1087.4
117.5°	219.0	235.8	252.6	256.8	342.2	456.0	512.9	620.0	834.1	994.8	1013.4
120°	233.6	249.4	265.3	269.2	347.3	451.4	503.4	601.2	796.9	943.6	961.7
122.5°	247.9	263.8	279.7	283.7	354.5	448.9	496.1	584.2	760.5	892.6	910.4
125°	269.8	284.3	298.8	302.5	364.4	446.9	488.2	563.0	712.7	825.0	841.5
127.5°	287.6	302.2	316.9	320.6	374.2	445.8	481.5	545.8	674.3	770.7	784.6
130°	297.1	312.9	328.7	332.6	381.4	446.4	478.9	536.2	650.6	736.4	749.2
132.5°	306.9	322.7	338.6	342.5	387.2	446.9	476.8	528.0	630.4	707.2	718.6
135°	321.6	336.0	350.3	353.9	393.5	446.4	472.9	515.8	601.6	665.9	675.8
137.5°	336.5	350.7	365.0	368.5	403.1	449.2	472.3	508.6	581.1	635.5	643.6
140°	348.8	362.0	375.1	378.4	408.9	449.7	470.1	501.4	564.0	611.0	618.5
142.5°	358.4	370.4	382.6	385.6	413.8	451.3	470.1	497.6	552.6	593.9	600.4
145°	373.0	383.5	394.2	396.8	420.2	451.4	466.9	489.4	534.5	568.2	573.1
147.5°	387.5	397.9	408.2	410.7	429.4	454.5	466.9	484.6	520.0	546.5	550.6
150°	397.1	406.4	415.7	418.0	434.4	456.1	466.9	481.9	511.8	534.2	537.5
152.5°	406.9	414.0	421.0	422.8	437.5	457.1	466.9	479.7	505.2	524.4	526.9
155°	421.5	426.7	432.0	433.3	444.5	459.5	466.9	477.1	497.3	512.6	514.3
157.5°	432.3	437.4	442.4	443.8	451.5	461.8	466.9	474.8	490.6	502.4	503.6
160°	439.6	443.6	447.5	448.5	454.7	462.8	466.9	473.7	487.2	497.3	498.0
162.5°	446.9	449.9	452.8	453.6	458.1	464.0	466.9	472.6	484.1	492.6	493.3
165°	454.8	457.5	460.2	460.8	462.8	465.5	466.9	471.0	479.2	485.3	486.0
167.5°	462.2	463.4	464.7	465.0	466.7	468.9	470.1	472.8	478.2	482.2	482.5
170°	466.9	468.2	469.5	469.8	469.9	470.0	470.1	472.8	478.2	482.2	482.2
172.5°	469.5	469.8	470.0	470.1	470.1	470.1	470.1	472.2	476.5	479.6	479.4
175°	472.9	472.9	472.9	472.9	472.0	470.7	470.1	471.4	474.1	476.1	476.1
177.5°	472.9	472.9	472.9	472.9	472.2	471.2	470.7	471.8	473.9	475.5	475.2
180°	472.9	472.9	472.9	472.9	472.9	472.9	472.9	472.9	472.9	472.9	472.9



TEST NUMBER: P936924

CATALOG NUMBER: SQ4-FB-050U-125D-927-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	810.5	810.5
2.5°	865.2	860.0
5°	1112.8	1118.0
7.5°	1498.5	1496.0
10°	1863.4	1886.9
12.5°	2129.2	2134.4
15°	2290.8	2301.2
17.5°	2353.4	2356.0
20°	2356.0	2350.7
22.5°	2327.3	2322.1
25°	2293.4	2290.8
27.5°	2262.1	2264.7
30°	2249.1	2256.9
32.5°	2249.1	2262.1
35°	2254.3	2267.3
37.5°	2251.7	2267.3
40°	2241.3	2259.6
42.5°	2212.6	2225.7
45°	2168.3	2184.0
47.5°	2111.0	2121.4
50°	2038.0	2048.4
52.5°	1946.8	1949.4
55°	1837.3	1847.8
57.5°	1720.0	1722.6
60°	1589.7	1597.6
62.5°	1451.6	1451.6
65°	1305.7	1310.9
67.5°	1154.5	1167.6
70°	1000.8	1003.4
72.5°	849.6	849.6
75°	693.2	695.8
77.5°	544.7	544.7
80°	403.9	406.6
82.5°	278.9	284.1
85°	174.6	174.6
87.5°	80.8	73.0
90°	12.1	12.1
92.5°	48.3	38.7
95°	168.4	139.4
97.5°	403.5	348.2
100°	581.4	515.4
102.5°	756.3	699.9
105°	979.4	949.0
107.5°	1125.5	1132.8
110°	1181.2	1212.8



TEST NUMBER: P936924

CATALOG NUMBER: SQ4-FB-050U-125D-927-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	1186.2	1234.7
115°	1154.7	1222.0
117.5°	1088.1	1162.7
120°	1034.3	1106.8
122.5°	982.0	1053.5
125°	907.3	973.2
127.5°	840.1	895.7
130°	800.6	851.9
132.5°	764.7	810.7
135°	715.5	755.1
137.5°	676.1	708.5
140°	648.9	679.2
142.5°	626.5	652.6
145°	592.9	612.6
147.5°	567.0	583.4
150°	550.8	564.0
152.5°	536.9	546.9
155°	520.9	527.5
157.5°	508.3	512.9
160°	500.7	503.4
162.5°	495.8	498.3
165°	488.6	491.3
167.5°	483.6	484.7
170°	482.2	482.2
172.5°	478.4	477.4
175°	476.1	476.1
177.5°	474.1	472.9
180°	472.9	472.9



TEST NUMBER: P936924
 CATALOG NUMBER: SQ4-FB-050U-125D-927-1D-UNV-STD-W-8

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.03	8.13	7.82	8.95	9.94	20.21	21.31	21.00	22.12	23.12
	3H	7.76	8.75	8.55	9.57	10.60	22.07	23.06	22.87	23.88	24.91
	4H	8.07	9.00	8.88	9.83	10.87	22.73	23.66	23.54	24.49	25.53
	6H	8.33	9.19	9.16	10.03	11.09	23.17	24.03	24.00	24.87	25.93
	8H	8.40	9.23	9.24	10.09	11.14	23.30	24.12	24.13	24.98	26.03
	12H	8.43	9.22	9.27	10.07	11.15	23.37	24.16	24.22	25.01	26.09
4H	2H	14.28	15.21	15.10	16.05	17.08	20.51	21.45	21.33	22.28	23.32
	3H	15.87	16.65	16.70	17.52	18.57	22.58	23.37	23.41	24.23	25.29
	4H	15.97	16.69	16.82	17.55	18.63	23.36	24.08	24.21	24.94	26.02
	6H	16.00	16.62	16.86	17.51	18.59	23.91	24.53	24.77	25.42	26.51
	8H	15.98	16.56	16.84	17.44	18.54	24.08	24.66	24.95	25.55	26.64
	12H	15.95	16.47	16.83	17.37	18.48	24.19	24.71	25.07	25.61	26.72
8H	4H	17.44	18.02	18.30	18.90	20.00	23.44	24.02	24.31	24.90	26.00
	6H	17.69	18.17	18.58	19.10	20.20	24.08	24.56	24.97	25.49	26.59
	8H	17.71	18.14	18.62	19.06	20.17	24.30	24.73	25.21	25.65	26.77
	12H	17.69	18.07	18.60	18.98	20.15	24.46	24.84	25.37	25.75	26.92
12H	4H	17.59	18.12	18.48	19.02	20.12	23.40	23.93	24.29	24.83	25.94
	6H	17.95	18.38	18.86	19.30	20.41	24.07	24.50	24.97	25.41	26.53
	8H	18.03	18.41	18.94	19.32	20.49	24.31	24.69	25.22	25.60	26.76