

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562795

Luminaire Tested: **SQ4-PC3-0U-050D-830-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562795  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PC3-0U-050D-830-1D-UNV-STD-W-6  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.  
DOWNLIGHT 500 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: 3000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2786.3 lumens  
Efficiency: N/A  
Efficacy: 104.4 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')  
CIE Type: Direct

Input Watts (W): 26.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562795  
CATALOG NUMBER: SQ4-PC3-0U-050D-830-1D-UNV-STD-W-6

### Luminous Intensity Polar Plot





TEST NUMBER: P562795

CATALOG NUMBER: SQ4-PC3-0U-050D-830-1D-UNV-STD-W-6

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100	
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	88	87	85			85	
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73	71			71	
3	91	80	72	66	88	79	71	65	76	70	64	73	68	63	71	66	62	60			60	
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	53	51			51	
5	77	64	55	48	74	63	54	48	61	53	48	59	52	47	57	51	47	44			44	
6	71	58	49	42	69	57	48	42	55	47	42	53	46	41	52	46	41	39			39	
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	34			34	
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	31			31	
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	29	28			28	
10	54	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	27	25			25	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6279	6279	6279
5°	6327	6286	6263
10°	6311	6282	6264
15°	6279	6279	6272
20°	6237	6256	6256
25°	6178	6223	6204
30°	6103	6177	6150
35°	6012	6105	6062
40°	5913	5996	5935
45°	5805	5846	5756
50°	5653	5653	5563
55°	5474	5403	5322
60°	5210	5105	5024
65°	4816	4718	4678
70°	4215	4250	4233
75°	3391	3752	3774
80°	2412	3181	3213
85°	1468	2668	2668



TEST NUMBER: P562795

CATALOG NUMBER: SQ4-PC3-0U-050D-830-1D-UNV-STD-W-6

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	96.6	3.5
10°-20°	277.3	10.0
20°-30°	419.9	15.1
30°-40°	503.4	18.1
40°-50°	513.3	18.4
50°-60°	448.1	16.1
60°-70°	320.8	11.5
70°-80°	165.2	5.9
80°-90°	41.8	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	793.8	28.5
0°-40°	1297.2	46.6
0°-60°	2258.5	81.1
0°-90°	2786.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2786.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1021	1021	1021	1021	1021	
5°	1025	1014	1018	1015	1014	97
15°	986	978	986	986	985	278
25°	910	904	917	914	914	419
35°	801	799	813	807	807	501
45°	667	666	672	664	662	514
55°	510	504	504	496	496	455
65°	331	324	324	321	321	327
75°	143	149	158	159	159	154
85°	21	32	38	39	38	29
90°	0	0	0	0	0	



TEST NUMBER: P562795

CATALOG NUMBER: SQ4-PC3-OU-050D-830-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1020.9	1020.9	1020.9	1020.9	1020.9
2.5°	1027.0	1018.1	1020.9	1018.6	1014.9
5°	1024.7	1014.5	1018.1	1015.2	1014.3
7.5°	1017.3	1007.2	1011.9	1009.9	1009.0
10°	1010.5	1000.4	1005.8	1003.9	1003.0
12.5°	1001.5	992.0	998.2	996.3	996.2
15°	986.0	977.6	986.0	985.9	985.0
17.5°	966.5	958.9	967.8	968.4	967.8
20°	952.9	944.6	955.7	954.8	955.7
22.5°	936.2	929.4	941.3	938.9	939.8
25°	910.3	903.9	916.9	914.1	914.1
27.5°	879.7	875.1	889.3	886.3	886.3
30°	859.3	854.7	869.7	865.9	865.9
32.5°	836.6	833.5	847.8	843.2	843.2
35°	800.7	798.8	813.0	807.3	807.3
37.5°	763.6	762.0	774.8	767.9	765.7
40°	736.4	735.5	746.8	739.2	739.2
42.5°	709.2	708.2	718.1	709.0	709.0
45°	667.4	665.5	672.1	663.6	661.7
47.5°	621.8	620.0	624.1	614.8	613.9
50°	590.8	589.0	590.8	582.3	581.4
52.5°	559.1	555.7	556.0	547.5	547.3
55°	510.5	504.0	503.8	496.3	496.3
57.5°	459.0	450.5	451.3	444.8	443.9
60°	423.5	414.3	415.0	409.3	408.4
62.5°	388.7	378.0	380.2	373.8	373.6
65°	330.9	323.5	324.2	321.4	321.4
67.5°	275.3	268.4	273.4	271.1	270.9
70°	234.4	229.8	236.3	236.3	235.4
72.5°	196.6	196.4	204.6	204.6	205.1
75°	142.7	149.2	157.9	158.8	158.8
77.5°	95.3	106.7	116.3	116.6	116.5
80°	68.1	81.0	89.8	91.7	90.7
82.5°	46.1	59.8	67.1	69.0	68.1
85°	20.8	31.9	37.8	38.7	37.8
87.5°	6.0	12.7	15.1	15.1	13.6
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)