

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562819

Luminaire Tested: **SQ4-PC3-0U-075D-830-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562819  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PC3-0U-075D-830-1D-UNV-STD-W-6  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.  
DOWNLIGHT 750 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: 3000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4106.7 lumens  
Efficiency: N/A  
Efficacy: 101.7 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')  
CIE Type: Direct

Input Watts (W): 40.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562819  
CATALOG NUMBER: SQ4-PC3-0U-075D-830-1D-UNV-STD-W-6

### Luminous Intensity Polar Plot





TEST NUMBER: P562819

CATALOG NUMBER: SQ4-PC3-0U-075D-830-1D-UNV-STD-W-6

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	88	87	85
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73	71
3	91	80	72	66	88	79	71	65	76	70	64	73	68	63	71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	53	51
5	77	64	55	48	74	63	54	48	61	53	48	59	52	47	57	51	47	44
6	71	58	49	42	69	57	48	42	55	47	42	53	46	41	52	46	41	39
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	34
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	31
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	29	28
10	54	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	27	25

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	9255	9255	9255
5°	9325	9265	9231
10°	9302	9259	9233
15°	9254	9254	9245
20°	9193	9220	9220
25°	9106	9172	9144
30°	8995	9104	9064
35°	8861	8997	8935
40°	8715	8838	8748
45°	8557	8617	8484
50°	8333	8333	8200
55°	8068	7963	7844
60°	7679	7524	7404
65°	7097	6955	6894
70°	6213	6264	6239
75°	5000	5530	5563
80°	3553	4690	4739
85°	2167	3931	3931



TEST NUMBER: P562819

CATALOG NUMBER: SQ4-PC3-0U-075D-830-1D-UNV-STD-W-6

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	142.4	3.5
10°-20°	408.7	10.0
20°-30°	618.9	15.1
30°-40°	741.9	18.1
40°-50°	756.5	18.4
50°-60°	660.4	16.1
60°-70°	472.8	11.5
70°-80°	243.5	5.9
80°-90°	61.6	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1169.9	28.5
0°-40°	1911.9	46.6
0°-60°	3328.8	81.1
0°-90°	4106.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4106.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1505	1505	1505	1505	1505	
5°	1510	1495	1501	1496	1495	143
15°	1453	1441	1453	1453	1452	410
25°	1342	1332	1352	1347	1347	617
35°	1180	1177	1198	1190	1190	738
45°	984	981	991	978	975	757
55°	752	743	743	732	732	671
65°	488	477	478	474	474	482
75°	210	220	233	234	234	227
85°	31	47	56	57	56	43
90°	0	0	0	0	0	



TEST NUMBER: P562819

CATALOG NUMBER: SQ4-PC3-0U-075D-830-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1504.7	1504.7	1504.7	1504.7	1504.7
2.5°	1513.7	1500.6	1504.7	1501.3	1495.8
5°	1510.3	1495.3	1500.6	1496.3	1495.0
7.5°	1499.4	1484.5	1491.4	1488.5	1487.2
10°	1489.4	1474.4	1482.4	1479.6	1478.3
12.5°	1476.0	1462.1	1471.3	1468.5	1468.2
15°	1453.2	1440.9	1453.2	1453.2	1451.8
17.5°	1424.5	1413.3	1426.4	1427.3	1426.4
20°	1404.4	1392.2	1408.6	1407.2	1408.6
22.5°	1379.9	1369.8	1387.4	1383.8	1385.2
25°	1341.7	1332.2	1351.5	1347.3	1347.3
27.5°	1296.6	1289.8	1310.8	1306.3	1306.3
30°	1266.5	1259.7	1281.8	1276.2	1276.2
32.5°	1233.0	1228.4	1249.5	1242.8	1242.8
35°	1180.1	1177.4	1198.2	1189.9	1189.9
37.5°	1125.5	1123.0	1141.9	1131.8	1128.6
40°	1085.4	1084.0	1100.7	1089.5	1089.5
42.5°	1045.2	1043.9	1058.3	1045.0	1045.0
45°	983.7	980.9	990.6	978.0	975.3
47.5°	916.5	913.8	919.8	906.2	904.8
50°	870.8	868.1	870.8	858.2	856.9
52.5°	824.0	819.1	819.5	807.0	806.7
55°	752.4	742.8	742.6	731.5	731.5
57.5°	676.6	664.0	665.1	655.6	654.3
60°	624.2	610.6	611.6	603.3	601.9
62.5°	572.9	557.1	560.4	550.9	550.6
65°	487.6	476.7	477.9	473.7	473.7
67.5°	405.7	395.6	402.9	399.6	399.3
70°	345.5	338.7	348.3	348.3	346.9
72.5°	289.8	289.5	301.5	301.5	302.3
75°	210.4	219.9	232.7	234.1	234.1
77.5°	140.4	157.3	171.4	171.9	171.7
80°	100.3	119.4	132.4	135.1	133.8
82.5°	68.0	88.2	98.9	101.7	100.3
85°	30.7	47.0	55.7	57.1	55.7
87.5°	8.9	18.7	22.3	22.2	20.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)