

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519716

Luminaire Tested: **SQ4-100U-0D-830-1D-UNV-STD-W-4**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519716
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-100U-0D-830-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3790.9 lumens
Efficiency: N/A
Efficacy: 151.0 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 25.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519716
CATALOG NUMBER: SQ4-100U-0D-830-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P519716

CATALOG NUMBER: SQ4-100U-0D-830-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20								20				20				20	
RC	80								50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	4245	52474	14037
100°	4564	43695	35763
105°	4791	29584	42527
110°	5088	20172	40393
115°	5257	14592	32851
120°	5305	11559	25355
125°	5316	9746	19356
130°	5252	8562	15127
135°	5189	7686	12217
140°	5172	7049	10141
145°	5195	6551	8569
150°	5251	6166	7439
155°	5294	5873	6662
160°	5343	5674	6141
165°	5377	5537	5796
170°	5396	5440	5580
175°	5404	5378	5438



TEST NUMBER: P519716

CATALOG NUMBER: SQ4-100U-0D-830-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	273.2	7.2
100°-110°	754.3	19.9
110°-120°	777.9	20.5
120°-130°	625.1	16.5
130°-140°	491.3	13.0
140°-150°	376.8	9.9
150°-160°	270.8	7.1
160°-170°	165.6	4.4
170°-180°	55.8	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	1805.5	47.6
90°-150°	3298.7	87.0
90°-180°	3791.0	100.0
0°-180°	3790.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	2	4	8	8	9	
95°	40	148	496	204	133	46
105°	134	207	830	1267	1193	143
115°	241	291	668	1323	1505	237
125°	330	376	606	1025	1203	294
135°	398	441	589	830	936	308
145°	461	493	582	707	761	289
155°	520	537	577	634	654	240
165°	563	570	580	602	607	159
175°	584	584	581	589	587	55
180°	584	584	584	584	584	



TEST NUMBER: P519716

CATALOG NUMBER: SQ4-100U-OD-830-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	1.9	3.7	7.5	8.4	9.3
92.5°	16.8	69.7	124.7	45.5	35.5
95°	40.1	147.8	495.7	203.8	132.6
97.5°	66.5	165.6	734.3	565.3	409.4
100°	85.9	176.2	822.4	828.2	673.1
102.5°	104.6	188.3	839.6	1023.3	876.2
105°	134.4	207.4	829.9	1267.0	1193.0
107.5°	166.2	231.2	783.6	1384.5	1411.5
110°	188.6	247.0	747.8	1409.7	1497.4
112.5°	208.7	265.0	714.1	1389.8	1519.0
115°	240.8	291.1	668.4	1323.2	1504.8
117.5°	268.9	318.9	638.3	1229.5	1436.1
120°	287.5	336.8	626.4	1166.0	1374.1
122.5°	305.4	352.5	616.7	1106.8	1303.9
125°	330.5	376.1	605.9	1025.3	1203.3
127.5°	351.8	397.4	599.5	956.4	1110.0
130°	365.9	411.6	596.5	914.3	1053.9
132.5°	379.4	422.8	593.5	878.9	1005.4
135°	397.7	440.6	589.1	830.4	936.3
137.5°	418.2	457.3	586.8	789.8	880.1
140°	429.4	467.8	585.3	762.6	842.0
142.5°	442.1	477.5	583.8	738.5	808.4
145°	461.2	493.1	581.6	707.0	760.8
147.5°	479.5	507.4	579.5	680.4	722.2
150°	492.9	515.7	578.8	664.5	698.3
152.5°	503.4	524.7	578.0	650.9	678.9
155°	520.0	537.3	576.9	634.3	654.4
157.5°	535.3	548.6	577.1	622.2	635.9
160°	544.2	556.1	577.9	615.4	625.5
162.5°	551.7	562.1	578.6	609.4	617.2
165°	562.9	570.2	579.7	602.2	606.8
167.5°	571.5	575.9	580.7	597.9	599.3
170°	576.0	579.6	580.7	595.6	595.6
172.5°	579.7	581.9	580.7	592.6	591.9
175°	583.5	584.4	580.7	589.0	587.2
177.5°	584.9	584.2	580.5	585.7	584.2
180°	583.5	583.5	583.5	583.5	583.5

(END OF REPORT)