

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P563275

Luminaire Tested: **SQ4-PP3-050U-050D-830-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563275
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-050U-050D-830-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5581.8 lumens
Efficiency: N/A
Efficacy: 124.6 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 44.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563275
CATALOG NUMBER: SQ4-PP3-050U-050D-830-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P563275

CATALOG NUMBER: SQ4-PP3-050U-050D-830-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	49				49
1	98	94	90	86	90	86	83	80	73	71	69	61	59	58	49	48	47				42	
2	89	82	76	71	82	76	71	66	64	60	57	54	51	48	44	42	40				36	
3	82	72	65	59	75	67	61	55	57	52	48	48	44	41	39	36	34				30	
4	75	64	56	50	69	59	52	47	51	45	41	42	38	35	35	32	30				26	
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	31	28	26				23	
6	63	51	43	37	58	48	40	35	41	35	31	34	30	27	28	25	23				20	
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20				18	
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18				16	
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	19	16				14	
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15				13	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6632	6632	6632
5°	6681	6640	6617
10°	6670	6623	6594
15°	6626	6590	6554
20°	6582	6545	6495
25°	6504	6459	6394
30°	6384	6349	6269
35°	6216	6174	6096
40°	6018	5979	5911
45°	5853	5812	5755
50°	5643	5607	5553
55°	5351	5280	5240
60°	4871	4731	4709
65°	4292	4113	4098
70°	3705	3552	3552
75°	3189	3144	3099
80°	2812	2844	2777
85°	2202	2399	2399



TEST NUMBER: P563275

CATALOG NUMBER: SQ4-PP3-050U-050D-830-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.0	1.8
10°-20°	291.2	5.2
20°-30°	436.1	7.8
30°-40°	511.5	9.2
40°-50°	513.1	9.2
50°-60°	437.7	7.8
60°-70°	285.5	5.1
70°-80°	143.2	2.6
80°-90°	41.3	0.7
90°-100°	207.4	3.7
100°-110°	563.3	10.1
110°-120°	579.1	10.4
120°-130°	463.0	8.3
130°-140°	363.8	6.5
140°-150°	279.0	5.0
150°-160°	200.6	3.6
160°-170°	122.7	2.2
170°-180°	41.3	0.7
0°-30°	829.2	14.9
0°-40°	1340.7	24.0
0°-60°	2291.6	41.1
0°-90°	2761.6	49.5
90°-120°	1349.8	24.2
90°-150°	2455.6	44.0
90°-180°	2820.0	50.5
0°-180°	5581.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1078	1078	1078	1078	1078	
5°	1082	1072	1076	1072	1072	103
15°	1040	1030	1035	1031	1029	294
25°	958	947	952	943	942	441
35°	828	820	822	813	812	517
45°	673	668	668	662	662	518
55°	499	497	492	490	489	443
65°	295	289	283	281	282	294
75°	134	134	132	131	130	146
85°	31	34	34	34	34	37
90°	1	6	10	12	12	3
95°	31	113	361	157	106	32
105°	100	156	619	943	888	106
115°	178	216	496	986	1124	175
125°	244	278	449	756	892	218
135°	294	327	436	616	694	228
145°	340	365	430	523	562	214
155°	385	398	428	470	483	177
165°	417	422	429	447	449	118
175°	432	433	430	436	435	41
180°	432	432	432	432	432	

TEST NUMBER: P563275

CATALOG NUMBER: SQ4-PP3-050U-050D-830-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1078.3	1078.3	1078.3	1078.3	1078.3
2.5°	1085.1	1076.3	1078.3	1076.7	1072.3
5°	1082.1	1072.0	1075.5	1071.7	1071.7
7.5°	1074.7	1063.7	1067.2	1063.4	1063.2
10°	1067.9	1056.9	1060.4	1056.6	1055.7
12.5°	1058.1	1047.0	1051.3	1046.8	1046.6
15°	1040.5	1030.4	1034.9	1031.0	1029.2
17.5°	1020.7	1009.6	1015.0	1009.7	1009.0
20°	1005.6	994.5	999.9	992.3	992.3
22.5°	987.4	976.3	982.5	972.7	972.7
25°	958.3	947.2	951.7	943.2	942.2
27.5°	923.7	912.8	917.5	907.8	907.7
30°	898.8	888.6	894.0	883.6	882.7
32.5°	871.6	862.1	866.1	855.7	854.7
35°	827.9	819.6	822.2	812.8	811.8
37.5°	782.0	773.5	776.5	768.3	768.0
40°	749.5	743.9	744.7	738.1	736.2
42.5°	719.2	712.9	713.7	707.1	706.7
45°	672.9	668.3	668.2	661.6	661.6
47.5°	623.8	620.2	619.2	613.7	613.5
50°	589.7	587.0	586.0	581.2	580.3
52.5°	554.2	552.9	549.7	545.7	545.5
55°	499.0	497.2	492.4	489.5	488.6
57.5°	439.1	435.4	430.0	425.9	426.6
60°	396.0	392.3	384.6	382.8	382.8
62.5°	354.4	350.0	342.3	339.7	341.2
65°	294.9	289.3	282.6	280.7	281.6
67.5°	240.8	235.8	228.5	228.5	227.8
70°	206.0	203.3	197.5	197.5	197.5
72.5°	175.0	173.7	169.5	169.5	168.8
75°	134.2	134.2	132.3	131.3	130.4
77.5°	100.6	100.9	100.0	99.0	97.3
80°	79.4	81.2	80.3	79.4	78.4
82.5°	59.7	61.6	61.4	59.7	59.5
85°	31.2	34.0	34.0	34.0	34.0
87.5°	8.6	12.4	14.0	14.6	15.4
90°	1.4	5.5	9.7	12.5	12.5
92.5°	12.5	56.8	98.6	42.4	35.8
95°	30.6	113.4	361.1	157.2	105.6
97.5°	50.6	125.2	553.6	430.7	302.5
100°	63.9	133.1	612.5	620.9	501.4
102.5°	77.2	141.0	628.0	767.9	662.5
105°	100.0	155.7	619.4	943.2	887.5
107.5°	123.6	172.8	583.6	1033.7	1049.1
110°	140.3	185.1	556.9	1051.5	1118.0



TEST NUMBER: P563275

CATALOG NUMBER: SQ4-PP3-050U-050D-830-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	154.7	197.4	530.3	1036.7	1136.9
115°	177.8	215.8	495.8	986.4	1123.6
117.5°	199.4	235.8	473.9	915.2	1069.7
120°	213.9	249.2	463.9	867.4	1020.8
122.5°	226.1	261.4	457.2	819.5	967.5
125°	244.4	278.4	448.6	755.8	891.6
127.5°	260.8	294.5	443.9	707.6	824.2
130°	270.8	303.4	441.7	677.4	781.9
132.5°	280.8	313.4	439.4	651.5	744.2
135°	294.4	327.0	436.1	615.7	694.4
137.5°	309.2	338.8	434.4	584.0	650.3
140°	318.0	346.6	433.3	563.8	623.6
142.5°	326.9	353.3	432.2	548.1	598.0
145°	340.3	364.7	430.5	523.1	562.5
147.5°	355.3	376.2	429.2	503.5	534.4
150°	365.3	382.9	429.2	492.2	516.7
152.5°	373.0	388.5	428.0	482.1	502.2
155°	384.7	398.3	427.8	469.7	483.3
157.5°	396.1	406.7	427.8	461.3	471.7
160°	402.8	412.3	427.8	455.7	463.9
162.5°	409.4	416.8	428.9	451.2	457.2
165°	416.7	422.1	429.2	447.2	448.6
167.5°	424.2	426.9	430.5	442.5	443.6
170°	426.4	429.1	430.5	440.3	440.3
172.5°	428.6	430.2	430.5	438.0	438.0
175°	431.9	433.3	430.5	436.1	434.7
177.5°	433.0	433.0	429.7	434.1	431.9
180°	431.9	431.9	431.9	431.9	431.9

(END OF REPORT)