

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563611

Luminaire Tested: **SQ4-PP3-100U-100D-830-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563611
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-100U-100D-830-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11093.2 lumens
Efficiency: N/A
Efficacy: 119.4 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 92.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563611
CATALOG NUMBER: SQ4-PP3-100U-100D-830-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P563611

CATALOG NUMBER: SQ4-PP3-100U-100D-830-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49				
1	98	93	90	86	90	86	83	80	73	70	68	60	59	57	49	48	47	41				
2	89	82	76	71	82	76	70	66	64	60	57	53	50	48	43	41	40	35				
3	81	72	65	59	75	67	60	55	57	52	48	47	44	41	38	36	34	30				
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	32	29	26				
5	68	57	49	43	63	53	46	40	45	40	35	38	34	30	31	28	26	22				
6	63	51	43	37	58	47	40	35	41	35	31	34	30	27	28	25	23	20				
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	22	20	17				
8	54	42	34	29	50	39	32	27	34	28	24	28	24	21	24	20	18	16				
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	19	16	14				
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	13				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12989	12989	12989
5°	13085	13004	12959
10°	13062	12970	12912
15°	12976	12905	12834
20°	12890	12817	12720
25°	12737	12649	12523
30°	12501	12435	12278
35°	12174	12091	11937
40°	11785	11710	11577
45°	11463	11382	11270
50°	11051	10980	10874
55°	10479	10341	10261
60°	9540	9267	9221
65°	8405	8054	8027
70°	7256	6956	6956
75°	6245	6157	6070
80°	5508	5572	5441
85°	4312	4700	4700



TEST NUMBER: P563611

CATALOG NUMBER: SQ4-PP3-100U-100D-830-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	199.7	1.8
10°-20°	570.2	5.1
20°-30°	854.1	7.7
30°-40°	1001.8	9.0
40°-50°	1004.9	9.1
50°-60°	857.2	7.7
60°-70°	559.1	5.0
70°-80°	280.5	2.5
80°-90°	79.4	0.7
90°-100°	409.9	3.7
100°-110°	1131.5	10.2
110°-120°	1166.9	10.5
120°-130°	937.7	8.5
130°-140°	736.9	6.6
140°-150°	565.2	5.1
150°-160°	406.2	3.7
160°-170°	248.4	2.2
170°-180°	83.8	0.8
0°-30°	1623.9	14.6
0°-40°	2625.7	23.7
0°-60°	4487.8	40.5
0°-90°	5406.8	48.7
90°-120°	2708.2	24.4
90°-150°	4948.1	44.6
90°-180°	5686.0	51.3
0°-180°	11093.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2112	2112	2112	2112	2112	
5°	2119	2099	2106	2099	2099	201
15°	2038	2018	2027	2019	2016	575
25°	1877	1855	1864	1847	1845	863
35°	1621	1605	1610	1592	1590	1013
45°	1318	1309	1308	1296	1296	1015
55°	977	974	964	959	957	868
65°	578	567	553	550	552	576
75°	263	263	259	257	255	285
85°	61	66	67	67	67	72
90°	3	6	11	13	14	7
95°	60	222	744	306	199	64
105°	202	311	1245	1900	1790	215
115°	361	437	1003	1985	2257	355
125°	496	564	909	1538	1805	441
135°	596	661	884	1246	1404	462
145°	692	740	872	1060	1141	433
155°	780	806	865	952	982	359
165°	844	855	870	903	910	238
175°	875	876	871	884	881	83
180°	875	875	875	875	875	

TEST NUMBER: P563611

CATALOG NUMBER: SQ4-PP3-100U-100D-830-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2111.8	2111.8	2111.8	2111.8	2111.8
2.5°	2125.1	2107.7	2111.8	2108.6	2099.9
5°	2119.2	2099.3	2106.2	2098.8	2098.8
7.5°	2104.7	2083.0	2089.9	2082.5	2082.2
10°	2091.4	2069.7	2076.6	2069.2	2067.4
12.5°	2072.2	2050.4	2058.8	2049.9	2049.6
15°	2037.7	2017.8	2026.6	2019.1	2015.5
17.5°	1998.9	1977.2	1987.8	1977.4	1975.9
20°	1969.3	1947.5	1958.2	1943.3	1943.3
22.5°	1933.7	1912.0	1924.1	1904.9	1904.9
25°	1876.7	1855.0	1863.8	1847.1	1845.3
27.5°	1809.0	1787.6	1796.8	1777.9	1777.5
30°	1760.1	1740.2	1750.9	1730.5	1728.7
32.5°	1706.8	1688.4	1696.1	1675.7	1673.9
35°	1621.3	1605.0	1610.2	1591.7	1589.8
37.5°	1531.4	1514.7	1520.6	1504.7	1504.0
40°	1467.7	1456.8	1458.4	1445.4	1441.8
42.5°	1408.5	1396.2	1397.7	1384.8	1384.0
45°	1317.8	1308.7	1308.5	1295.6	1295.6
47.5°	1221.5	1214.7	1212.6	1201.9	1201.5
50°	1154.9	1149.5	1147.5	1138.2	1136.4
52.5°	1085.3	1082.8	1076.4	1068.6	1068.3
55°	977.2	973.6	964.3	958.7	956.9
57.5°	859.9	852.6	842.1	834.0	835.5
60°	775.5	768.2	753.3	749.6	749.6
62.5°	694.1	685.4	670.4	665.2	668.1
65°	577.5	566.6	553.4	549.7	551.5
67.5°	471.6	461.8	447.5	447.5	446.0
70°	403.5	398.0	386.8	386.8	386.8
72.5°	342.8	340.2	332.0	332.0	330.6
75°	262.8	262.8	259.1	257.2	255.4
77.5°	196.9	197.6	195.8	193.9	190.6
80°	155.5	159.1	157.3	155.4	153.6
82.5°	117.0	120.6	120.3	117.0	116.6
85°	61.1	66.5	66.6	66.6	66.6
87.5°	16.8	23.2	25.9	26.2	28.0
90°	2.8	5.5	11.2	12.6	14.0
92.5°	25.2	104.6	187.1	68.3	53.2
95°	60.2	221.8	743.6	305.6	198.8
97.5°	99.7	248.4	1101.5	848.0	614.2
100°	128.8	264.4	1233.7	1242.4	1009.6
102.5°	156.8	282.5	1259.4	1535.0	1314.3
105°	201.6	311.2	1244.9	1900.5	1789.6
107.5°	249.3	346.7	1175.4	2076.7	2117.2
110°	282.9	370.5	1121.6	2114.6	2246.1

TEST NUMBER: P563611

CATALOG NUMBER: SQ4-PP3-100U-100D-830-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	313.1	397.4	1071.2	2084.7	2278.5
115°	361.3	436.6	1002.6	1984.8	2257.3
117.5°	403.3	478.3	957.5	1844.2	2154.2
120°	431.3	505.2	939.6	1749.1	2061.2
122.5°	458.2	528.8	925.0	1660.2	1955.9
125°	495.7	564.2	908.8	1538.0	1805.0
127.5°	527.6	596.1	899.3	1434.6	1664.9
130°	548.9	617.4	894.8	1371.4	1580.9
132.5°	569.1	634.2	890.3	1318.3	1508.1
135°	596.5	660.9	883.6	1245.7	1404.5
137.5°	627.3	685.9	880.2	1184.6	1320.2
140°	644.1	701.6	878.0	1143.9	1263.1
142.5°	663.2	716.3	875.7	1107.8	1212.6
145°	691.7	739.7	872.4	1060.5	1141.2
147.5°	719.2	761.1	869.3	1020.6	1083.3
150°	739.4	773.6	868.2	996.8	1047.4
152.5°	755.0	787.1	867.1	976.4	1018.3
155°	780.0	806.0	865.4	951.5	981.6
157.5°	802.9	822.9	865.7	933.3	953.9
160°	816.4	834.2	866.8	923.1	938.2
162.5°	827.6	843.2	867.9	914.1	925.9
165°	844.4	855.3	869.6	903.3	910.2
167.5°	857.3	863.8	871.0	896.8	899.0
170°	864.0	869.5	871.0	893.4	893.4
172.5°	869.6	872.9	871.0	888.9	887.8
175°	875.2	876.5	871.0	883.5	880.8
177.5°	877.4	876.3	870.7	878.5	876.3
180°	875.2	875.2	875.2	875.2	875.2

(END OF REPORT)