

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P520364

Luminaire Tested: **SQ4-F-150U-050D-830-1D-UNV-STD-W-4**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P520364
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G3-1910-536-17)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-F-150U-050D-830-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7585.4 lumens
Efficiency: N/A
Efficacy: 136.2 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 55.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P520364
CATALOG NUMBER: SQ4-F-150U-050D-830-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P520364

CATALOG NUMBER: SQ4-F-150U-050D-830-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	51	51	51	33	33	33	25
1	92	88	84	81	82	79	75	73	61	59	57	44	43	42	29	29	28	21
2	84	77	71	66	74	69	64	59	53	50	47	39	37	35	26	25	23	18
3	76	67	60	55	68	60	54	49	47	43	39	34	32	29	23	21	20	15
4	70	59	52	46	62	53	47	42	41	37	33	30	27	25	20	18	17	13
5	64	53	45	39	57	47	41	36	37	32	29	27	24	22	18	16	15	11
6	59	47	39	34	52	42	36	31	33	28	25	24	21	19	16	14	13	10
7	54	42	35	29	48	38	31	27	30	25	22	22	19	16	15	13	11	8
8	50	38	31	26	44	34	28	23	27	22	19	20	17	15	14	12	10	8
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	13	11	9	7
10	43	32	25	20	39	29	23	18	23	18	15	17	14	12	12	10	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6415	6415	6415
5°	6430	6352	6404
10°	6409	6330	6374
15°	6365	6285	6338
20°	6305	6232	6279
25°	6234	6158	6216
30°	6147	6098	6139
35°	6081	6007	6038
40°	5963	5908	5920
45°	5842	5792	5792
50°	5718	5664	5637
55°	5585	5511	5480
60°	5375	5288	5255
65°	5122	5017	4958
70°	4769	4672	4570
75°	4281	4149	4050
80°	3464	3411	3310
85°	2064	2371	2467



TEST NUMBER: P520364

CATALOG NUMBER: SQ4-F-150U-050D-830-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.6	0.9
10°-20°	186.8	2.5
20°-30°	280.6	3.7
30°-40°	334.9	4.4
40°-50°	343.2	4.5
50°-60°	306.1	4.0
60°-70°	228.0	3.0
70°-80°	123.7	1.6
80°-90°	30.5	0.4
90°-100°	409.8	5.4
100°-110°	1108.2	14.6
110°-120°	1165.1	15.4
120°-130°	946.4	12.5
130°-140°	742.3	9.8
140°-150°	569.7	7.5
150°-160°	409.7	5.4
160°-170°	250.3	3.3
170°-180°	84.4	1.1
0°-30°	533.0	7.0
0°-40°	867.9	11.4
0°-60°	1517.2	20.0
0°-90°	1899.4	25.0
90°-120°	2683.1	35.4
90°-150°	4941.5	65.1
90°-180°	5686.0	75.0
0°-180°	7585.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	695	695	695	695	695	
5°	694	693	686	692	692	66
15°	666	665	658	664	664	188
25°	612	611	605	609	611	282
35°	540	538	533	533	536	337
45°	448	449	444	443	444	346
55°	347	347	343	340	341	309
65°	235	234	230	227	227	232
75°	120	119	116	114	114	127
85°	20	21	22	23	23	27
90°	2	6	12	13	12	5
95°	64	223	682	353	210	67
105°	206	318	1229	1813	1739	217
115°	363	443	1020	1974	2228	358
125°	496	569	919	1551	1822	443
135°	595	666	894	1252	1417	460
145°	692	744	882	1072	1153	433
155°	781	812	874	961	993	360
165°	851	859	878	912	917	240
175°	883	882	879	890	889	84
180°	882	882	882	882	882	

TEST NUMBER: P520364

CATALOG NUMBER: SQ4-F-150U-050D-830-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	695.3	695.3	695.3	695.3	695.3
2.5°	697.5	696.1	690.0	695.3	694.5
5°	694.3	693.4	685.9	692.4	691.5
7.5°	689.3	687.5	680.2	686.5	685.6
10°	684.1	682.3	675.7	681.3	680.4
12.5°	677.4	676.3	669.0	674.6	674.4
15°	666.4	664.6	658.0	663.6	663.6
17.5°	651.9	650.8	644.5	649.8	649.1
20°	642.2	640.3	634.7	639.5	639.5
22.5°	630.3	629.2	623.6	627.5	628.2
25°	612.4	610.6	604.9	608.7	610.6
27.5°	592.7	591.2	586.5	589.0	590.3
30°	577.0	577.0	572.4	573.4	576.2
32.5°	562.9	562.9	557.5	558.5	559.8
35°	539.9	538.0	533.3	533.4	536.1
37.5°	513.0	512.1	509.1	508.6	509.3
40°	495.1	494.2	490.5	491.5	491.5
42.5°	477.3	476.4	472.6	471.3	472.8
45°	447.7	448.6	443.9	443.0	443.9
47.5°	418.5	418.5	414.7	412.2	413.7
50°	398.4	398.4	394.6	392.7	392.7
52.5°	377.5	378.3	373.8	371.2	371.9
55°	347.2	347.2	342.6	339.7	340.7
57.5°	313.7	313.7	309.0	306.3	307.8
60°	291.3	291.3	286.6	283.9	284.8
62.5°	269.0	269.0	264.4	261.5	261.7
65°	234.6	233.6	229.8	227.1	227.1
67.5°	201.5	199.1	196.2	192.5	192.5
70°	176.8	175.9	173.2	169.4	169.4
72.5°	154.5	152.8	150.1	147.0	147.0
75°	120.1	119.1	116.4	114.5	113.6
77.5°	86.0	85.3	85.1	82.4	83.2
80°	65.2	65.2	64.2	62.3	62.3
82.5°	46.5	47.2	45.7	45.3	44.5
85°	19.5	21.4	22.4	23.3	23.3
87.5°	4.1	7.0	7.6	8.6	8.4
90°	1.9	5.6	12.4	13.3	12.4
92.5°	27.0	98.3	193.9	84.1	61.0
95°	63.6	223.2	681.6	352.7	209.7
97.5°	102.1	256.0	1062.4	879.2	645.7
100°	131.0	269.3	1180.9	1231.6	995.8
102.5°	157.5	287.7	1222.7	1498.7	1322.4
105°	206.0	318.3	1229.3	1813.4	1739.1
107.5°	250.8	353.3	1175.6	2009.7	2034.4
110°	285.7	378.6	1127.8	2062.4	2167.3



TEST NUMBER: P520364

CATALOG NUMBER: SQ4-F-150U-050D-830-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	316.9	403.8	1083.7	2051.8	2228.1
115°	362.7	443.4	1019.6	1973.6	2228.1
117.5°	407.4	483.2	977.2	1854.2	2142.5
120°	434.8	509.0	952.2	1768.6	2062.9
122.5°	460.6	533.4	937.0	1676.8	1973.2
125°	496.5	568.9	919.0	1550.7	1821.7
127.5°	529.6	600.6	908.3	1447.8	1686.1
130°	547.8	621.1	903.8	1384.2	1599.6
132.5°	566.8	639.3	899.2	1326.9	1525.2
135°	595.2	665.8	894.2	1252.1	1417.3
137.5°	623.9	690.5	890.1	1191.4	1326.0
140°	643.6	705.8	888.6	1152.4	1272.1
142.5°	662.6	721.1	885.5	1117.0	1222.0
145°	692.0	744.0	881.9	1071.7	1153.4
147.5°	718.8	764.9	877.7	1030.6	1093.4
150°	738.6	779.4	876.2	1008.4	1058.5
152.5°	756.8	792.4	875.4	987.7	1028.8
155°	781.2	811.9	874.3	961.4	993.0
157.5°	806.7	828.0	874.5	943.1	963.9
160°	821.2	838.8	875.3	931.6	946.4
162.5°	832.6	847.2	876.0	922.4	933.6
165°	850.6	858.9	878.1	912.4	917.1
167.5°	862.9	868.7	878.3	903.8	906.0
170°	870.5	873.3	879.0	900.0	900.0
172.5°	876.6	877.1	879.0	895.3	894.6
175°	882.9	881.9	879.0	890.4	888.6
177.5°	885.0	882.8	878.8	886.4	884.2
180°	881.9	881.9	881.9	881.9	881.9

(END OF REPORT)