

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P564595

Luminaire Tested: **SQ4-PW1-025U-125D-830-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564595
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-025U-125D-830-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8190.8 lumens
Efficiency: N/A
Efficacy: 105.1 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 77.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564595
CATALOG NUMBER: SQ4-PW1-025U-125D-830-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P564595

CATALOG NUMBER: SQ4-PW1-025U-125D-830-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	115	115	115	115	110	110	110	110	102	102	102	94	94	94	87	87	87	83
1	105	101	97	93	101	97	93	90	90	87	84	83	81	79	77	75	74	71
2	96	88	82	77	92	85	79	74	79	74	70	73	69	66	68	65	62	59
3	88	78	70	64	84	75	68	62	70	64	59	65	60	56	60	56	53	50
4	81	69	61	54	77	67	59	53	62	56	51	58	53	48	54	50	46	43
5	74	62	53	47	71	60	52	46	56	49	44	52	46	42	49	44	40	38
6	68	56	47	41	65	54	46	40	50	44	39	47	41	37	44	39	35	33
7	63	51	42	36	61	49	41	36	46	39	34	43	37	33	40	35	31	29
8	59	46	38	32	57	45	37	32	42	35	31	40	34	29	37	32	28	26
9	55	42	34	29	53	41	34	29	39	32	28	36	31	27	34	29	26	24
10	52	39	31	26	50	38	31	26	36	29	25	34	28	24	32	27	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16493	16493	16493
5°	16600	16468	16395
10°	16467	16334	16245
15°	16292	16112	16051
20°	16097	15850	15819
25°	15873	15584	15536
30°	15537	15302	15202
35°	15096	14883	14794
40°	14625	14397	14340
45°	14056	13871	13810
50°	13473	13360	13270
55°	12845	12845	12642
60°	12060	12293	11858
65°	11036	11586	10761
70°	9729	10664	9474
75°	8308	9544	8085
80°	6443	8033	6528
85°	4171	6168	5505



TEST NUMBER: P564595

CATALOG NUMBER: SQ4-PW1-025U-125D-830-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	252.5	3.1
10°-20°	712.9	8.7
20°-30°	1057.4	12.9
30°-40°	1237.3	15.1
40°-50°	1231.7	15.0
50°-60°	1063.7	13.0
60°-70°	765.6	9.3
70°-80°	401.5	4.9
80°-90°	100.7	1.2
90°-100°	102.8	1.3
100°-110°	270.3	3.3
110°-120°	280.3	3.4
120°-130°	224.9	2.7
130°-140°	176.4	2.2
140°-150°	135.4	1.7
150°-160°	97.5	1.2
160°-170°	59.7	0.7
170°-180°	20.2	0.2
0°-30°	2022.8	24.7
0°-40°	3260.0	39.8
0°-60°	5555.4	67.8
0°-90°	6823.2	83.3
90°-120°	653.5	8.0
90°-150°	1190.2	14.5
90°-180°	1368.0	16.7
0°-180°	8190.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2681	2681	2681	2681	2681	
5°	2688	2658	2667	2660	2655	255
15°	2558	2526	2530	2525	2521	721
25°	2339	2300	2296	2282	2289	1075
35°	2010	1983	1982	1963	1970	1257
45°	1616	1602	1595	1590	1588	1247
55°	1198	1195	1198	1181	1179	1069
65°	758	781	796	765	739	751
75°	350	382	402	375	340	375
85°	59	78	87	83	78	78
90°	1	4	11	5	5	3
95°	14	53	177	91	62	15
105°	49	74	299	454	423	52
115°	87	105	239	478	545	85
125°	120	135	218	368	434	107
135°	143	158	211	297	337	111
145°	166	177	208	253	273	104
155°	188	193	208	229	235	86
165°	203	206	208	216	219	57
175°	211	211	210	212	212	20
180°	211	211	211	211	211	



TEST NUMBER: P564595

CATALOG NUMBER: SQ4-PW1-025U-125D-830-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2681.4	2681.4	2681.4	2681.4	2681.4
2.5°	2696.5	2674.3	2681.4	2675.4	2662.5
5°	2688.5	2658.4	2667.2	2660.0	2655.4
7.5°	2661.1	2633.3	2639.8	2632.2	2629.4
10°	2636.5	2608.8	2615.2	2605.7	2601.0
12.5°	2608.1	2578.6	2585.0	2575.5	2572.7
15°	2558.5	2526.2	2530.2	2525.3	2520.7
17.5°	2500.9	2468.1	2468.7	2461.2	2460.2
20°	2459.3	2424.6	2421.5	2412.2	2416.8
22.5°	2413.9	2377.4	2374.3	2361.2	2367.6
25°	2338.8	2299.5	2296.3	2282.3	2289.2
27.5°	2251.9	2213.1	2213.1	2193.5	2200.8
30°	2187.6	2150.7	2154.5	2131.1	2140.4
32.5°	2119.6	2086.3	2088.4	2065.0	2074.2
35°	2010.4	1982.7	1982.1	1963.3	1970.3
37.5°	1898.9	1874.4	1870.6	1859.8	1861.6
40°	1821.4	1800.7	1793.1	1786.0	1786.0
42.5°	1740.2	1721.2	1713.7	1708.5	1706.6
45°	1615.9	1602.0	1594.6	1589.9	1587.6
47.5°	1493.1	1480.1	1473.7	1470.3	1468.0
50°	1408.0	1398.8	1396.2	1389.1	1386.8
52.5°	1323.0	1317.4	1314.9	1305.9	1303.6
55°	1197.8	1195.4	1197.8	1181.2	1178.9
57.5°	1067.3	1071.0	1078.7	1056.4	1050.8
60°	980.4	989.7	999.3	973.1	963.9
62.5°	891.6	906.4	919.9	889.9	876.9
65°	758.3	781.4	796.1	764.9	739.4
67.5°	629.8	658.5	676.1	642.4	613.8
70°	541.0	573.3	593.0	559.2	526.8
72.5°	463.5	499.5	515.5	483.6	451.2
75°	349.6	382.0	401.6	374.8	340.2
77.5°	248.1	278.5	294.8	271.5	242.9
80°	181.9	214.2	226.8	207.4	184.3
82.5°	129.0	155.8	164.4	152.7	137.0
85°	59.1	77.5	87.4	82.6	78.0
87.5°	15.4	28.9	38.1	37.0	38.9
90°	1.4	4.0	10.8	5.4	5.4
92.5°	5.7	27.4	60.6	26.8	17.3
95°	13.5	53.2	177.2	91.3	62.2
97.5°	23.5	58.4	265.1	210.8	155.3
100°	31.1	62.8	292.1	296.1	229.9
102.5°	37.6	67.2	299.7	368.8	312.2
105°	48.7	73.8	298.9	453.8	423.3
107.5°	60.1	83.3	281.9	497.9	505.3
110°	67.6	88.8	267.8	509.3	541.0

TEST NUMBER: P564595

CATALOG NUMBER: SQ4-PW1-025U-125D-830-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	75.2	95.3	254.8	502.1	550.8
115°	86.6	105.1	239.4	477.6	545.1
117.5°	97.7	114.6	228.8	443.7	518.6
120°	104.1	120.0	224.5	420.9	493.7
122.5°	110.6	126.5	221.3	398.2	469.9
125°	120.4	134.9	217.8	368.0	434.2
127.5°	128.2	143.0	214.8	343.7	399.5
130°	132.5	148.4	213.7	328.5	380.1
132.5°	136.9	152.7	212.6	315.4	361.7
135°	143.4	157.9	211.0	297.1	336.8
137.5°	150.1	164.4	210.7	283.4	316.0
140°	155.5	168.8	209.6	272.6	303.0
142.5°	159.9	172.0	209.6	264.9	291.1
145°	166.4	176.9	208.3	253.4	273.2
147.5°	172.9	183.2	208.3	243.8	260.2
150°	177.2	186.4	208.3	238.3	251.6
152.5°	181.5	188.7	208.3	233.9	244.0
155°	188.0	193.3	208.3	228.7	235.3
157.5°	192.9	197.9	208.3	224.1	228.8
160°	196.1	200.1	208.3	221.9	224.5
162.5°	199.4	202.3	208.3	219.7	222.4
165°	202.9	205.5	208.3	216.5	219.1
167.5°	206.1	207.4	209.6	215.1	216.1
170°	208.3	209.6	209.6	215.1	215.1
172.5°	209.4	209.6	209.6	213.9	212.9
175°	211.0	211.0	209.6	212.3	212.3
177.5°	211.0	211.0	209.9	212.1	211.0
180°	211.0	211.0	211.0	211.0	211.0

(END OF REPORT)