

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P564643

Luminaire Tested: **SQ4-PW1-050U-075D-830-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564643
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-050U-075D-830-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6845.3 lumens
Efficiency: N/A
Efficacy: 117.0 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 58.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564643
CATALOG NUMBER: SQ4-PW1-050U-075D-830-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P564643

CATALOG NUMBER: SQ4-PW1-050U-075D-830-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59
1	100	96	92	88	93	89	86	83	78	75	73	67	65	63	57	56	55	50
2	91	84	77	72	85	78	73	68	68	64	60	59	56	53	50	48	46	42
3	83	74	66	60	77	69	62	57	60	55	51	52	48	45	45	42	39	36
4	76	65	57	51	71	61	54	48	54	48	43	46	42	39	40	37	34	31
5	70	58	50	44	65	55	47	42	48	42	38	42	37	34	36	32	30	27
6	64	52	44	38	60	49	42	36	43	37	33	38	33	29	33	29	26	23
7	60	47	39	33	55	44	37	32	39	33	29	34	30	26	30	26	23	21
8	55	43	35	30	52	40	33	28	36	30	26	31	27	23	27	24	21	19
9	52	39	32	26	48	37	30	25	33	27	23	29	24	21	25	22	19	17
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9727	9727	9727
5°	9789	9712	9669
10°	9711	9633	9581
15°	9608	9502	9466
20°	9494	9348	9329
25°	9361	9191	9163
30°	9163	9025	8965
35°	8903	8778	8725
40°	8625	8491	8457
45°	8290	8181	8144
50°	7946	7879	7826
55°	7575	7575	7455
60°	7113	7251	6993
65°	6509	6833	6347
70°	5739	6289	5588
75°	4900	5630	4767
80°	3801	4739	3850
85°	2456	3642	3246



TEST NUMBER: P564643

CATALOG NUMBER: SQ4-PW1-050U-075D-830-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.9	2.2
10°-20°	420.4	6.1
20°-30°	623.6	9.1
30°-40°	729.7	10.7
40°-50°	726.4	10.6
50°-60°	627.3	9.2
60°-70°	451.5	6.6
70°-80°	236.8	3.5
80°-90°	60.4	0.9
90°-100°	207.4	3.0
100°-110°	563.3	8.2
110°-120°	579.1	8.5
120°-130°	463.0	6.8
130°-140°	363.8	5.3
140°-150°	279.0	4.1
150°-160°	200.6	2.9
160°-170°	122.7	1.8
170°-180°	41.3	0.6
0°-30°	1192.9	17.4
0°-40°	1922.6	28.1
0°-60°	3276.4	47.9
0°-90°	4025.1	58.8
90°-120°	1349.8	19.7
90°-150°	2455.6	35.9
90°-180°	2820.0	41.2
0°-180°	6845.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1581	1581	1581	1581	1581	
5°	1586	1568	1573	1569	1566	150
15°	1509	1490	1492	1489	1487	425
25°	1379	1356	1354	1346	1350	634
35°	1186	1169	1169	1158	1162	741
45°	953	945	940	938	936	735
55°	706	705	706	697	695	630
65°	447	461	470	451	436	443
75°	206	225	237	221	201	221
85°	35	46	52	49	46	46
90°	1	6	10	12	12	3
95°	31	113	361	157	106	32
105°	100	156	619	943	888	106
115°	178	216	496	986	1124	175
125°	244	278	449	756	892	218
135°	294	327	436	616	694	228
145°	340	365	430	523	562	214
155°	385	398	428	470	483	177
165°	417	422	429	447	449	118
175°	432	433	430	436	435	41
180°	432	432	432	432	432	

TEST NUMBER: P564643

CATALOG NUMBER: SQ4-PW1-050U-075D-830-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1581.4	1581.4	1581.4	1581.4	1581.4
2.5°	1590.3	1577.2	1581.4	1577.8	1570.2
5°	1585.5	1567.8	1573.0	1568.8	1566.0
7.5°	1569.4	1553.0	1556.8	1552.3	1550.7
10°	1554.9	1538.5	1542.4	1536.7	1534.0
12.5°	1538.2	1520.7	1524.5	1518.9	1517.3
15°	1508.9	1489.8	1492.2	1489.3	1486.6
17.5°	1474.9	1455.6	1456.0	1451.5	1451.0
20°	1450.4	1430.0	1428.1	1422.6	1425.3
22.5°	1423.6	1402.1	1400.2	1392.5	1396.3
25°	1379.3	1356.2	1354.3	1346.0	1350.1
27.5°	1328.1	1305.2	1305.2	1293.6	1298.0
30°	1290.2	1268.4	1270.7	1256.9	1262.3
32.5°	1250.0	1230.4	1231.7	1217.8	1223.3
35°	1185.7	1169.3	1169.0	1157.9	1162.0
37.5°	1119.9	1105.5	1103.2	1096.8	1097.9
40°	1074.2	1062.0	1057.5	1053.3	1053.3
42.5°	1026.3	1015.1	1010.7	1007.6	1006.5
45°	953.0	944.8	940.5	937.6	936.3
47.5°	880.5	872.9	869.1	867.1	865.8
50°	830.4	824.9	823.4	819.2	817.9
52.5°	780.2	777.0	775.5	770.2	768.8
55°	706.4	705.0	706.4	696.6	695.2
57.5°	629.5	631.7	636.2	623.0	619.7
60°	578.2	583.7	589.4	573.9	568.5
62.5°	525.8	534.5	542.5	524.8	517.2
65°	447.2	460.9	469.5	451.1	436.1
67.5°	371.4	388.3	398.8	378.9	362.0
70°	319.1	338.1	349.7	329.8	310.7
72.5°	273.4	294.6	304.0	285.2	266.1
75°	206.2	225.3	236.9	221.1	200.6
77.5°	146.3	164.3	173.9	160.1	143.2
80°	107.3	126.4	133.8	122.3	108.7
82.5°	76.1	91.9	97.0	90.1	80.8
85°	34.8	45.7	51.6	48.7	46.0
87.5°	9.2	17.6	23.1	23.7	24.8
90°	1.4	5.5	9.7	12.5	12.5
92.5°	12.5	56.8	98.6	42.4	35.8
95°	30.6	113.4	361.1	157.2	105.6
97.5°	50.6	125.2	553.6	430.7	302.5
100°	63.9	133.1	612.5	620.9	501.4
102.5°	77.2	141.0	628.0	767.9	662.5
105°	100.0	155.7	619.4	943.2	887.5
107.5°	123.6	172.8	583.6	1033.7	1049.1
110°	140.3	185.1	556.9	1051.5	1118.0

TEST NUMBER: P564643

CATALOG NUMBER: SQ4-PW1-050U-075D-830-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	154.7	197.4	530.3	1036.7	1136.9
115°	177.8	215.8	495.8	986.4	1123.6
117.5°	199.4	235.8	473.9	915.2	1069.7
120°	213.9	249.2	463.9	867.4	1020.8
122.5°	226.1	261.4	457.2	819.5	967.5
125°	244.4	278.4	448.6	755.8	891.6
127.5°	260.8	294.5	443.9	707.6	824.2
130°	270.8	303.4	441.7	677.4	781.9
132.5°	280.8	313.4	439.4	651.5	744.2
135°	294.4	327.0	436.1	615.7	694.4
137.5°	309.2	338.8	434.4	584.0	650.3
140°	318.0	346.6	433.3	563.8	623.6
142.5°	326.9	353.3	432.2	548.1	598.0
145°	340.3	364.7	430.5	523.1	562.5
147.5°	355.3	376.2	429.2	503.5	534.4
150°	365.3	382.9	429.2	492.2	516.7
152.5°	373.0	388.5	428.0	482.1	502.2
155°	384.7	398.3	427.8	469.7	483.3
157.5°	396.1	406.7	427.8	461.3	471.7
160°	402.8	412.3	427.8	455.7	463.9
162.5°	409.4	416.8	428.9	451.2	457.2
165°	416.7	422.1	429.2	447.2	448.6
167.5°	424.2	426.9	430.5	442.5	443.6
170°	426.4	429.1	430.5	440.3	440.3
172.5°	428.6	430.2	430.5	438.0	438.0
175°	431.9	433.3	430.5	436.1	434.7
177.5°	433.0	433.0	429.7	434.1	431.9
180°	431.9	431.9	431.9	431.9	431.9

(END OF REPORT)