

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563034

Luminaire Tested: **SQ4-PC3-125U-100D-830-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563034
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-125U-100D-830-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8358.3 lumens
Efficiency: N/A
Efficacy: 129.6 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 64.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563034
CATALOG NUMBER: SQ4-PC3-125U-100D-830-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P563034

CATALOG NUMBER: SQ4-PC3-125U-100D-830-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44
1	96	92	88	85	88	84	81	78	70	68	66	57	55	54	44	43	42	37
2	88	80	74	69	80	74	69	64	61	58	54	50	47	45	39	37	36	31
3	80	71	63	58	73	65	59	54	54	49	46	44	41	38	35	32	30	26
4	73	62	55	49	67	57	51	45	48	43	39	39	35	32	31	28	26	22
5	67	56	48	42	61	51	44	39	43	37	33	35	31	28	28	25	23	19
6	62	50	42	36	56	46	39	34	39	33	29	32	28	24	25	22	20	17
7	57	45	37	31	52	41	34	29	35	29	25	29	25	22	23	20	18	15
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	27	22	18	22	18	15	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12298	12298	12298
5°	12390	12310	12265
10°	12360	12303	12267
15°	12295	12295	12283
20°	12214	12250	12250
25°	12099	12186	12149
30°	11952	12096	12044
35°	11773	11955	11871
40°	11579	11743	11624
45°	11369	11449	11272
50°	11072	11072	10894
55°	10719	10581	10422
60°	10202	9998	9839
65°	9431	9241	9160
70°	8257	8322	8290
75°	6645	7347	7390
80°	4723	6227	6296
85°	2879	5229	5229



TEST NUMBER: P563034

CATALOG NUMBER: SQ4-PC3-125U-100D-830-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.1	1.5
10°-20°	362.0	4.3
20°-30°	548.2	6.6
30°-40°	657.2	7.9
40°-50°	670.1	8.0
50°-60°	585.0	7.0
60°-70°	418.8	5.0
70°-80°	215.7	2.6
80°-90°	56.3	0.7
90°-100°	342.0	4.1
100°-110°	921.1	11.0
110°-120°	966.7	11.6
120°-130°	784.4	9.4
130°-140°	615.2	7.4
140°-150°	472.3	5.7
150°-160°	339.6	4.1
160°-170°	207.5	2.5
170°-180°	70.0	0.8
0°-30°	1036.3	12.4
0°-40°	1693.6	20.3
0°-60°	2948.7	35.3
0°-90°	3639.5	43.5
90°-120°	2229.8	26.7
90°-150°	4101.8	49.1
90°-180°	4719.0	56.5
0°-180°	8358.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1333	1333	1333	1333	1333	
5°	1338	1325	1329	1326	1324	127
15°	1287	1276	1287	1287	1286	363
25°	1188	1180	1197	1193	1193	547
35°	1045	1043	1061	1054	1054	654
45°	871	869	878	866	864	671
55°	666	658	658	648	648	594
65°	432	422	423	420	420	427
75°	186	195	206	207	207	201
85°	27	42	49	51	49	37
90°	2	6	11	12	12	5
95°	52	186	561	287	198	54
105°	170	265	1019	1524	1430	179
115°	301	368	848	1639	1854	296
125°	411	472	762	1287	1515	367
135°	494	552	740	1039	1176	382
145°	572	616	731	888	954	359
155°	649	673	724	797	822	299
165°	704	712	727	756	760	199
175°	732	731	728	738	737	70
180°	731	731	731	731	731	



TEST NUMBER: P563034

CATALOG NUMBER: SQ4-PC3-125U-100D-830-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1332.9	1332.9	1332.9	1332.9	1332.9
2.5°	1340.8	1329.2	1332.9	1329.8	1325.0
5°	1337.8	1324.6	1329.2	1325.5	1324.3
7.5°	1328.2	1314.9	1321.0	1318.6	1317.3
10°	1319.3	1306.0	1313.2	1310.7	1309.4
12.5°	1307.5	1295.2	1303.3	1300.8	1300.6
15°	1287.2	1276.4	1287.2	1287.2	1286.0
17.5°	1261.8	1251.9	1263.5	1264.3	1263.5
20°	1244.0	1233.2	1247.7	1246.5	1247.7
22.5°	1222.3	1213.4	1229.0	1225.8	1227.0
25°	1188.5	1180.1	1197.1	1193.4	1193.4
27.5°	1148.5	1142.5	1161.1	1157.2	1157.2
30°	1121.9	1115.8	1135.4	1130.5	1130.5
32.5°	1092.2	1088.1	1106.8	1100.9	1100.9
35°	1045.3	1042.9	1061.4	1054.0	1054.0
37.5°	997.0	994.8	1011.5	1002.6	999.7
40°	961.4	960.2	975.0	965.1	965.1
42.5°	925.9	924.7	937.5	925.6	925.6
45°	871.3	868.9	877.5	866.3	863.9
47.5°	811.8	809.4	814.8	802.7	801.5
50°	771.4	768.9	771.4	760.2	759.0
52.5°	729.9	725.5	725.9	714.8	714.6
55°	666.4	658.0	657.8	647.9	647.9
57.5°	599.3	588.2	589.2	580.8	579.6
60°	552.9	540.8	541.8	534.4	533.2
62.5°	507.5	493.5	496.4	488.0	487.7
65°	432.0	422.3	423.3	419.6	419.6
67.5°	359.4	350.5	356.9	354.0	353.7
70°	306.1	300.0	308.5	308.5	307.3
72.5°	256.7	256.5	267.1	267.1	267.8
75°	186.4	194.8	206.1	207.3	207.3
77.5°	124.4	139.4	151.8	152.3	152.0
80°	88.9	105.8	117.2	119.7	118.5
82.5°	60.2	78.1	87.6	90.1	88.9
85°	27.2	41.6	49.4	50.6	49.4
87.5°	8.3	17.7	22.0	22.1	20.2
90°	1.9	5.5	11.2	12.1	12.1
92.5°	22.7	80.3	158.7	76.4	53.1
95°	52.1	186.0	560.6	286.7	198.3
97.5°	83.2	212.9	879.2	734.5	553.9
100°	107.1	223.6	980.5	1025.9	851.1
102.5°	130.2	238.7	1014.0	1244.1	1100.6
105°	170.4	265.1	1018.7	1524.1	1430.3
107.5°	208.4	292.9	975.3	1667.9	1692.1
110°	233.7	313.8	935.8	1712.6	1800.9



TEST NUMBER: P563034

CATALOG NUMBER: SQ4-PC3-125U-100D-830-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	260.5	334.8	897.8	1702.7	1847.8
115°	300.8	368.1	848.3	1639.1	1854.0
117.5°	337.5	400.6	809.9	1537.6	1776.9
120°	361.3	422.3	790.6	1464.7	1710.6
122.5°	382.2	442.4	776.4	1390.2	1635.3
125°	410.6	471.6	761.7	1287.4	1515.0
127.5°	438.0	498.1	752.4	1196.7	1399.9
130°	454.4	514.5	748.7	1144.7	1323.2
132.5°	470.8	530.2	744.9	1099.0	1262.9
135°	494.5	551.8	740.3	1038.6	1176.1
137.5°	517.0	572.0	737.9	987.4	1100.3
140°	532.6	585.4	735.6	955.8	1057.8
142.5°	549.0	598.2	734.1	926.4	1012.4
145°	571.7	616.4	731.0	888.0	953.5
147.5°	596.3	635.1	727.8	855.6	907.1
150°	612.7	646.4	726.3	835.3	878.1
152.5°	627.6	656.9	725.6	818.7	853.5
155°	649.0	672.7	724.4	796.7	822.2
157.5°	667.8	686.2	724.6	781.3	798.4
160°	679.8	695.2	725.4	772.2	785.0
162.5°	690.2	702.7	726.1	764.7	773.8
165°	704.0	712.2	727.2	756.2	759.8
167.5°	715.1	719.9	728.2	749.6	751.1
170°	722.6	724.4	728.2	745.9	745.9
172.5°	727.1	727.4	728.9	742.1	742.1
175°	731.9	731.0	728.2	738.4	736.6
177.5°	733.9	732.5	728.7	734.7	733.2
180°	731.0	731.0	731.0	731.0	731.0

(END OF REPORT)