

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P563058

Luminaire Tested: **SQ4-PC3-125U-125D-830-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563058
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-125U-125D-830-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9362.7 lumens
Efficiency: N/A
Efficacy: 124.3 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563058
CATALOG NUMBER: SQ4-PC3-125U-125D-830-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P563058

CATALOG NUMBER: SQ4-PC3-125U-125D-830-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	93	90	86	90	86	83	80	73	71	68	61	59	57	49	48	47	42
2	89	82	75	70	82	75	70	66	64	60	57	53	50	48	43	42	40	35
3	81	72	64	59	75	66	60	55	56	52	48	47	44	41	38	36	34	30
4	74	63	56	49	68	59	52	46	50	45	40	42	38	35	34	31	29	25
5	68	56	48	42	63	52	45	40	45	39	35	38	33	30	31	28	25	22
6	63	51	42	37	58	47	40	35	40	35	30	34	30	26	28	25	22	19
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	26	22	20	17
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	18	15
9	50	38	30	25	46	35	28	24	30	25	21	26	22	19	22	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15694	15694	15694
5°	15812	15709	15651
10°	15773	15700	15655
15°	15691	15691	15675
20°	15588	15634	15634
25°	15440	15552	15504
30°	15252	15437	15370
35°	15025	15256	15149
40°	14777	14985	14833
45°	14508	14611	14385
50°	14128	14128	13903
55°	13681	13504	13301
60°	13020	12758	12555
65°	12033	11793	11691
70°	10537	10620	10580
75°	8477	9375	9432
80°	6025	7948	8033
85°	3663	6669	6669



TEST NUMBER: P563058

CATALOG NUMBER: SQ4-PC3-125U-125D-830-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	161.0	1.7
10°-20°	462.0	4.9
20°-30°	699.6	7.5
30°-40°	838.7	9.0
40°-50°	855.2	9.1
50°-60°	746.5	8.0
60°-70°	534.4	5.7
70°-80°	275.3	2.9
80°-90°	71.3	0.8
90°-100°	342.0	3.7
100°-110°	921.1	9.8
110°-120°	966.7	10.3
120°-130°	784.4	8.4
130°-140°	615.2	6.6
140°-150°	472.3	5.0
150°-160°	339.6	3.6
160°-170°	207.5	2.2
170°-180°	70.0	0.7
0°-30°	1322.5	14.1
0°-40°	2161.2	23.1
0°-60°	3762.9	40.2
0°-90°	4643.9	49.6
90°-120°	2229.8	23.8
90°-150°	4101.8	43.8
90°-180°	4719.0	50.4
0°-180°	9362.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1701	1701	1701	1701	1701	
5°	1707	1690	1696	1692	1690	162
15°	1643	1629	1643	1643	1641	463
25°	1517	1506	1528	1523	1523	698
35°	1334	1331	1354	1345	1345	834
45°	1112	1109	1120	1106	1102	856
55°	850	840	840	827	827	758
65°	551	539	540	536	536	545
75°	238	249	263	265	265	257
85°	35	53	63	64	63	47
90°	2	6	11	12	12	5
95°	52	186	561	287	198	54
105°	170	265	1019	1524	1430	179
115°	301	368	848	1639	1854	296
125°	411	472	762	1287	1515	367
135°	494	552	740	1039	1176	382
145°	572	616	731	888	954	359
155°	649	673	724	797	822	299
165°	704	712	727	756	760	199
175°	732	731	728	738	737	70
180°	731	731	731	731	731	

TEST NUMBER: P563058

CATALOG NUMBER: SQ4-PC3-125U-125D-830-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1701.0	1701.0	1701.0	1701.0	1701.0
2.5°	1711.0	1696.3	1701.0	1697.0	1690.9
5°	1707.3	1690.3	1696.2	1691.5	1689.9
7.5°	1695.0	1678.0	1685.8	1682.7	1681.1
10°	1683.6	1666.7	1675.8	1672.6	1671.0
12.5°	1668.5	1652.8	1663.2	1660.0	1659.7
15°	1642.7	1628.8	1642.7	1642.6	1641.1
17.5°	1610.2	1597.6	1612.4	1613.4	1612.4
20°	1587.6	1573.7	1592.3	1590.7	1592.3
22.5°	1559.8	1548.4	1568.3	1564.3	1565.8
25°	1516.7	1505.9	1527.7	1523.0	1523.0
27.5°	1465.7	1458.0	1481.7	1476.7	1476.7
30°	1431.6	1423.9	1449.0	1442.7	1442.7
32.5°	1393.8	1388.6	1412.4	1404.9	1404.9
35°	1334.0	1330.9	1354.5	1345.0	1345.0
37.5°	1272.3	1269.5	1290.8	1279.4	1275.7
40°	1226.9	1225.4	1244.2	1231.6	1231.6
42.5°	1181.5	1180.0	1196.3	1181.2	1181.2
45°	1111.9	1108.8	1119.8	1105.6	1102.5
47.5°	1036.0	1032.9	1039.8	1024.3	1022.8
50°	984.3	981.3	984.3	970.1	968.6
52.5°	931.4	925.9	926.4	912.2	911.9
55°	850.5	839.7	839.5	826.9	826.9
57.5°	764.8	750.6	751.9	741.1	739.6
60°	705.6	690.2	691.4	681.9	680.4
62.5°	647.6	629.8	633.4	622.7	622.4
65°	551.2	538.9	540.2	535.5	535.5
67.5°	458.6	447.2	455.5	451.7	451.4
70°	390.6	382.9	393.7	393.7	392.2
72.5°	327.6	327.3	340.8	340.8	341.8
75°	237.8	248.6	263.0	264.6	264.6
77.5°	158.8	177.9	193.7	194.3	194.0
80°	113.4	135.0	149.6	152.7	151.2
82.5°	76.9	99.6	111.8	114.9	113.4
85°	34.6	53.1	63.0	64.5	63.0
87.5°	10.5	22.3	27.4	27.6	25.1
90°	1.9	5.5	11.2	12.1	12.1
92.5°	22.7	80.3	158.7	76.4	53.1
95°	52.1	186.0	560.6	286.7	198.3
97.5°	83.2	212.9	879.2	734.5	553.9
100°	107.1	223.6	980.5	1025.9	851.1
102.5°	130.2	238.7	1014.0	1244.1	1100.6
105°	170.4	265.1	1018.7	1524.1	1430.3
107.5°	208.4	292.9	975.3	1667.9	1692.1
110°	233.7	313.8	935.8	1712.6	1800.9



TEST NUMBER: P563058

CATALOG NUMBER: SQ4-PC3-125U-125D-830-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	260.5	334.8	897.8	1702.7	1847.8
115°	300.8	368.1	848.3	1639.1	1854.0
117.5°	337.5	400.6	809.9	1537.6	1776.9
120°	361.3	422.3	790.6	1464.7	1710.6
122.5°	382.2	442.4	776.4	1390.2	1635.3
125°	410.6	471.6	761.7	1287.4	1515.0
127.5°	438.0	498.1	752.4	1196.7	1399.9
130°	454.4	514.5	748.7	1144.7	1323.2
132.5°	470.8	530.2	744.9	1099.0	1262.9
135°	494.5	551.8	740.3	1038.6	1176.1
137.5°	517.0	572.0	737.9	987.4	1100.3
140°	532.6	585.4	735.6	955.8	1057.8
142.5°	549.0	598.2	734.1	926.4	1012.4
145°	571.7	616.4	731.0	888.0	953.5
147.5°	596.3	635.1	727.8	855.6	907.1
150°	612.7	646.4	726.3	835.3	878.1
152.5°	627.6	656.9	725.6	818.7	853.5
155°	649.0	672.7	724.4	796.7	822.2
157.5°	667.8	686.2	724.6	781.3	798.4
160°	679.8	695.2	725.4	772.2	785.0
162.5°	690.2	702.7	726.1	764.7	773.8
165°	704.0	712.2	727.2	756.2	759.8
167.5°	715.1	719.9	728.2	749.6	751.1
170°	722.6	724.4	728.2	745.9	745.9
172.5°	727.1	727.4	728.9	742.1	742.1
175°	731.9	731.0	728.2	738.4	736.6
177.5°	733.9	732.5	728.7	734.7	733.2
180°	731.0	731.0	731.0	731.0	731.0

(END OF REPORT)