

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563298

Luminaire Tested: **SQ4-PP3-050U-075D-830-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563298  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-050U-075D-830-1D-UNV-STD-W-4  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 500 LUMENS PER FOOT  
Light Source: 3000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4593.1 lumens  
Efficiency: N/A  
Efficacy: 126.5 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 36.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563298  
CATALOG NUMBER: SQ4-PP3-050U-075D-830-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P563298

CATALOG NUMBER: SQ4-PP3-050U-075D-830-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59
1	100	96	92	88	93	90	86	83	78	75	73	67	65	64	57	56	55	50
2	91	84	78	73	85	79	73	69	69	64	61	59	56	54	51	49	47	42
3	83	74	67	61	78	69	63	58	61	56	51	53	49	46	45	42	40	36
4	76	66	58	52	71	62	54	49	54	48	44	47	43	39	40	37	34	31
5	70	58	50	44	65	55	48	42	48	43	38	42	38	34	36	33	30	27
6	65	53	44	38	60	49	42	37	44	38	33	38	33	30	33	29	27	24
7	60	47	39	34	56	45	37	32	40	34	29	35	30	26	30	26	24	21
8	56	43	35	30	52	41	34	29	36	30	26	32	27	24	28	24	21	19
9	52	39	32	27	48	37	30	26	33	27	23	29	25	21	26	22	19	17
10	48	36	29	24	45	34	28	23	31	25	21	27	22	19	24	20	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	9776	9776	9776
5°	9848	9787	9753
10°	9831	9761	9718
15°	9766	9712	9660
20°	9701	9646	9574
25°	9585	9519	9425
30°	9408	9359	9240
35°	9163	9099	8985
40°	8869	8814	8713
45°	8627	8566	8481
50°	8318	8263	8184
55°	7887	7782	7723
60°	7180	6975	6940
65°	6324	6062	6041
70°	5460	5236	5236
75°	4702	4634	4570
80°	4144	4192	4096
85°	3239	3536	3536



TEST NUMBER: P563298

CATALOG NUMBER: SQ4-PP3-050U-075D-830-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	100.2	2.2
10°-20°	286.1	6.2
20°-30°	428.5	9.3
30°-40°	502.6	10.9
40°-50°	504.2	11.0
50°-60°	430.1	9.4
60°-70°	280.5	6.1
70°-80°	140.7	3.1
80°-90°	40.1	0.9
90°-100°	138.2	3.0
100°-110°	375.5	8.2
110°-120°	386.1	8.4
120°-130°	308.7	6.7
130°-140°	242.5	5.3
140°-150°	186.0	4.0
150°-160°	133.7	2.9
160°-170°	81.8	1.8
170°-180°	27.6	0.6
0°-30°	814.8	17.7
0°-40°	1317.4	28.7
0°-60°	2251.7	49.0
0°-90°	2713.0	59.1
90°-120°	899.8	19.6
90°-150°	1637.0	35.6
90°-180°	1880.0	40.9
0°-180°	4593.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1060	1060	1060	1060	1060	
5°	1063	1053	1057	1053	1053	101
15°	1022	1012	1017	1013	1011	288
25°	942	931	935	927	926	433
35°	814	805	808	799	798	508
45°	661	657	656	650	650	509
55°	490	488	484	481	480	436
65°	290	284	278	276	277	289
75°	132	132	130	129	128	143
85°	31	33	33	33	33	36
90°	1	4	6	8	8	3
95°	20	76	241	105	70	22
105°	67	104	413	629	592	71
115°	118	144	330	658	749	117
125°	163	186	299	504	594	145
135°	196	218	291	410	463	152
145°	227	243	287	349	375	142
155°	256	266	285	313	322	118
165°	278	281	286	298	299	78
175°	288	289	287	291	290	27
180°	288	288	288	288	288	

TEST NUMBER: P563298

CATALOG NUMBER: SQ4-PP3-050U-075D-830-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1059.6	1059.6	1059.6	1059.6	1059.6
2.5°	1066.3	1057.5	1059.6	1058.0	1053.6
5°	1063.3	1053.3	1056.8	1053.1	1053.1
7.5°	1056.0	1045.1	1048.6	1044.9	1044.7
10°	1049.4	1038.5	1041.9	1038.2	1037.3
12.5°	1039.7	1028.8	1033.0	1028.5	1028.4
15°	1022.4	1012.4	1016.8	1013.1	1011.3
17.5°	1002.9	992.0	997.3	992.1	991.4
20°	988.1	977.2	982.5	975.1	975.1
22.5°	970.2	959.3	965.4	955.7	955.7
25°	941.6	930.7	935.1	926.8	925.8
27.5°	907.6	896.9	901.5	892.0	891.9
30°	883.1	873.1	878.5	868.2	867.3
32.5°	856.4	847.1	851.0	840.8	839.9
35°	813.5	805.3	807.9	798.6	797.7
37.5°	768.3	760.0	763.0	755.0	754.6
40°	736.4	731.0	731.8	725.2	723.4
42.5°	706.7	700.5	701.3	694.8	694.4
45°	661.2	656.6	656.5	650.0	650.0
47.5°	612.9	609.4	608.4	603.0	602.9
50°	579.5	576.7	575.7	571.1	570.2
52.5°	544.5	543.3	540.1	536.2	536.0
55°	490.3	488.5	483.8	481.0	480.1
57.5°	431.4	427.8	422.5	418.5	419.2
60°	389.1	385.5	378.0	376.1	376.1
62.5°	348.2	343.9	336.3	333.8	335.2
65°	289.7	284.3	277.7	275.8	276.7
67.5°	236.6	231.7	224.5	224.5	223.8
70°	202.4	199.7	194.1	194.1	194.1
72.5°	172.0	170.7	166.6	166.6	165.9
75°	131.9	131.9	130.0	129.1	128.2
77.5°	98.8	99.2	98.2	97.3	95.6
80°	78.0	79.8	78.9	78.0	77.1
82.5°	58.7	60.5	60.4	58.7	58.5
85°	30.6	33.4	33.4	33.4	33.4
87.5°	8.4	11.8	13.2	13.6	14.3
90°	0.9	3.6	6.5	8.3	8.3
92.5°	8.3	37.8	65.7	28.2	23.9
95°	20.4	75.6	240.7	104.8	70.4
97.5°	33.7	83.5	369.1	287.1	201.7
100°	42.6	88.8	408.3	413.9	334.3
102.5°	51.5	94.0	418.7	511.9	441.7
105°	66.7	103.8	413.0	628.8	591.7
107.5°	82.4	115.2	389.1	689.1	699.4
110°	93.5	123.4	371.3	701.0	745.4



TEST NUMBER: P563298

CATALOG NUMBER: SQ4-PP3-050U-075D-830-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	103.1	131.6	353.5	691.1	757.9
115°	118.5	143.9	330.5	657.6	749.1
117.5°	133.0	157.2	315.9	610.1	713.1
120°	142.6	166.1	309.3	578.2	680.5
122.5°	150.7	174.3	304.8	546.3	645.0
125°	163.0	185.6	299.1	503.9	594.4
127.5°	173.9	196.3	295.9	471.8	549.4
130°	180.6	202.3	294.4	451.6	521.3
132.5°	187.2	208.9	293.0	434.4	496.1
135°	196.3	218.0	290.7	410.4	463.0
137.5°	206.1	225.8	289.6	389.3	433.5
140°	212.0	231.0	288.9	375.9	415.7
142.5°	218.0	235.5	288.1	365.4	398.7
145°	226.8	243.1	287.0	348.7	375.0
147.5°	236.8	250.8	286.1	335.6	356.3
150°	243.5	255.3	286.1	328.1	344.4
152.5°	248.7	259.0	285.4	321.4	334.8
155°	256.5	265.5	285.2	313.2	322.2
157.5°	264.1	271.1	285.2	307.6	314.4
160°	268.5	274.9	285.2	303.8	309.3
162.5°	273.0	277.8	285.9	300.8	304.8
165°	277.8	281.4	286.1	298.2	299.1
167.5°	282.8	284.6	287.0	295.0	295.7
170°	284.3	286.1	287.0	293.5	293.5
172.5°	285.7	286.8	287.0	292.0	292.0
175°	288.0	288.9	287.0	290.7	289.8
177.5°	288.7	288.7	286.5	289.4	288.0
180°	288.0	288.0	288.0	288.0	288.0

(END OF REPORT)