

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563394

Luminaire Tested: **SQ4-PP3-075U-075D-830-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563394
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-075U-075D-830-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5538.8 lumens
Efficiency: N/A
Efficacy: 130.3 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 42.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563394
CATALOG NUMBER: SQ4-PP3-075U-075D-830-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P563394

CATALOG NUMBER: SQ4-PP3-075U-075D-830-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	98	94	90	86	90	86	83	80	73	71	68	61	59	57	49	48	47	42
2	89	82	76	71	82	76	70	66	64	60	57	53	51	48	43	42	40	35
3	81	72	65	59	75	67	60	55	57	52	48	47	44	41	39	36	34	30
4	75	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	29	26
5	68	57	49	43	63	53	46	40	45	40	35	38	34	30	31	28	26	22
6	63	51	43	37	58	47	40	35	41	35	31	34	30	27	28	25	23	20
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20	18
8	54	42	34	29	50	39	32	27	34	28	24	28	24	21	24	20	18	16
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9776	9776	9776
5°	9848	9787	9753
10°	9831	9761	9718
15°	9766	9712	9660
20°	9701	9646	9574
25°	9585	9519	9425
30°	9408	9359	9240
35°	9163	9099	8985
40°	8869	8814	8713
45°	8627	8566	8481
50°	8318	8263	8184
55°	7887	7782	7723
60°	7180	6975	6940
65°	6324	6062	6041
70°	5460	5236	5236
75°	4702	4634	4570
80°	4144	4192	4096
85°	3239	3536	3536



TEST NUMBER: P563394

CATALOG NUMBER: SQ4-PP3-075U-075D-830-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.2	1.8
10°-20°	286.1	5.2
20°-30°	428.5	7.7
30°-40°	502.6	9.1
40°-50°	504.2	9.1
50°-60°	430.1	7.8
60°-70°	280.5	5.1
70°-80°	140.7	2.5
80°-90°	40.1	0.7
90°-100°	204.6	3.7
100°-110°	562.9	10.2
110°-120°	581.0	10.5
120°-130°	465.5	8.4
130°-140°	365.6	6.6
140°-150°	280.2	5.1
150°-160°	201.4	3.6
160°-170°	123.2	2.2
170°-180°	41.5	0.7
0°-30°	814.8	14.7
0°-40°	1317.4	23.8
0°-60°	2251.7	40.7
0°-90°	2713.0	49.0
90°-120°	1348.4	24.3
90°-150°	2459.7	44.4
90°-180°	2826.0	51.0
0°-180°	5538.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1060	1060	1060	1060	1060	
5°	1063	1053	1057	1053	1053	101
15°	1022	1012	1017	1013	1011	288
25°	942	931	935	927	926	433
35°	814	805	808	799	798	508
45°	661	657	656	650	650	509
55°	490	488	484	481	480	436
65°	290	284	278	276	277	289
75°	132	132	130	129	128	143
85°	31	33	33	33	33	36
90°	1	4	6	8	8	3
95°	30	112	362	155	99	32
105°	101	155	620	944	881	106
115°	178	217	497	990	1124	176
125°	246	280	451	763	894	219
135°	296	329	438	617	699	229
145°	342	366	432	526	567	215
155°	388	400	429	473	486	178
165°	419	424	431	449	451	118
175°	434	435	432	437	436	41
180°	434	434	434	434	434	

TEST NUMBER: P563394

CATALOG NUMBER: SQ4-PP3-075U-075D-830-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1059.6	1059.6	1059.6	1059.6	1059.6
2.5°	1066.3	1057.5	1059.6	1058.0	1053.6
5°	1063.3	1053.3	1056.8	1053.1	1053.1
7.5°	1056.0	1045.1	1048.6	1044.9	1044.7
10°	1049.4	1038.5	1041.9	1038.2	1037.3
12.5°	1039.7	1028.8	1033.0	1028.5	1028.4
15°	1022.4	1012.4	1016.8	1013.1	1011.3
17.5°	1002.9	992.0	997.3	992.1	991.4
20°	988.1	977.2	982.5	975.1	975.1
22.5°	970.2	959.3	965.4	955.7	955.7
25°	941.6	930.7	935.1	926.8	925.8
27.5°	907.6	896.9	901.5	892.0	891.9
30°	883.1	873.1	878.5	868.2	867.3
32.5°	856.4	847.1	851.0	840.8	839.9
35°	813.5	805.3	807.9	798.6	797.7
37.5°	768.3	760.0	763.0	755.0	754.6
40°	736.4	731.0	731.8	725.2	723.4
42.5°	706.7	700.5	701.3	694.8	694.4
45°	661.2	656.6	656.5	650.0	650.0
47.5°	612.9	609.4	608.4	603.0	602.9
50°	579.5	576.7	575.7	571.1	570.2
52.5°	544.5	543.3	540.1	536.2	536.0
55°	490.3	488.5	483.8	481.0	480.1
57.5°	431.4	427.8	422.5	418.5	419.2
60°	389.1	385.5	378.0	376.1	376.1
62.5°	348.2	343.9	336.3	333.8	335.2
65°	289.7	284.3	277.7	275.8	276.7
67.5°	236.6	231.7	224.5	224.5	223.8
70°	202.4	199.7	194.1	194.1	194.1
72.5°	172.0	170.7	166.6	166.6	165.9
75°	131.9	131.9	130.0	129.1	128.2
77.5°	98.8	99.2	98.2	97.3	95.6
80°	78.0	79.8	78.9	78.0	77.1
82.5°	58.7	60.5	60.4	58.7	58.5
85°	30.6	33.4	33.4	33.4	33.4
87.5°	8.4	11.8	13.2	13.6	14.3
90°	0.9	3.6	6.5	8.3	8.3
92.5°	12.7	54.4	94.3	36.2	29.7
95°	30.5	111.7	361.8	154.7	98.8
97.5°	49.7	123.8	552.1	425.4	300.1
100°	63.7	131.4	611.9	617.6	503.9
102.5°	77.0	140.3	627.4	766.2	661.9
105°	100.6	154.7	620.2	944.5	881.4
107.5°	123.1	172.6	584.9	1031.9	1050.6
110°	139.4	184.5	558.4	1053.6	1118.6

TEST NUMBER: P563394

CATALOG NUMBER: SQ4-PP3-075U-075D-830-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	154.1	197.8	531.8	1039.6	1138.5
115°	178.1	216.9	497.4	990.5	1124.1
117.5°	201.0	236.7	475.7	921.7	1072.8
120°	215.0	249.3	466.1	870.2	1026.3
122.5°	227.6	261.9	459.4	824.9	973.1
125°	245.5	279.8	451.3	763.4	894.3
127.5°	262.5	295.1	445.9	712.1	826.9
130°	271.3	304.7	443.0	681.6	786.3
132.5°	281.7	315.1	440.8	654.8	749.4
135°	296.3	328.7	438.4	617.4	698.6
137.5°	309.9	340.1	436.3	587.2	654.2
140°	320.2	348.2	435.6	567.1	627.6
142.5°	329.1	354.9	434.1	549.2	601.0
145°	342.4	365.9	431.9	526.1	566.7
147.5°	356.6	376.8	430.8	505.6	538.1
150°	365.5	383.5	430.1	494.3	519.6
152.5°	373.6	390.2	429.3	484.6	505.6
155°	387.6	400.3	429.2	472.8	486.4
157.5°	397.8	408.1	429.2	463.1	472.5
160°	405.2	413.3	429.2	457.9	465.1
162.5°	411.1	417.7	429.9	453.5	459.2
165°	419.0	424.4	431.0	448.6	451.3
167.5°	424.5	428.7	431.9	444.5	445.2
170°	428.2	430.9	431.9	443.0	443.0
172.5°	431.2	432.4	431.9	440.8	440.0
175°	433.8	434.7	431.9	437.4	436.5
177.5°	434.5	434.5	431.6	435.9	434.5
180°	433.8	433.8	433.8	433.8	433.8

(END OF REPORT)