

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519670

Luminaire Tested: **SQ4-050U-0D-830-1D-UNV-STD-W-8**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519670
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-050U-0D-830-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3760.3 lumens
Efficiency: N/A
Efficacy: 158.7 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Indirect

Input Watts (W): 23.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519670
CATALOG NUMBER: SQ4-050U-0D-830-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P519670

CATALOG NUMBER: SQ4-050U-0D-830-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	2154	25486	7447
100°	2263	21696	17759
105°	2376	14721	21091
110°	2522	10016	20106
115°	2587	7216	16353
120°	2631	5706	12558
125°	2621	4810	9562
130°	2592	4226	7482
135°	2561	3794	6040
140°	2554	3479	5007
145°	2555	3233	4224
150°	2594	3048	3670
155°	2611	2903	3280
160°	2636	2800	3036
165°	2653	2733	2856
170°	2663	2689	2750
175°	2667	2658	2684



TEST NUMBER: P519670

CATALOG NUMBER: SQ4-050U-0D-830-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	276.5	7.4
100°-110°	751.0	20.0
110°-120°	772.2	20.5
120°-130°	617.4	16.4
130°-140°	485.1	12.9
140°-150°	372.0	9.9
150°-160°	267.5	7.1
160°-170°	163.6	4.4
170°-180°	55.1	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	1799.7	47.9
90°-150°	3274.1	87.1
90°-180°	3760.0	100.0
0°-180°	3760.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	2	7	13	17	17	
95°	41	151	482	210	141	46
105°	133	208	826	1258	1183	142
115°	237	288	661	1315	1498	234
125°	326	371	598	1008	1189	291
135°	393	436	582	821	926	304
145°	454	486	574	698	750	285
155°	513	531	570	626	644	237
165°	556	563	572	596	598	157
175°	576	578	574	581	580	55
180°	576	576	576	576	576	



TEST NUMBER: P519670

CATALOG NUMBER: SQ4-050U-0D-830-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	1.9	7.3	13.0	16.7	16.7
92.5°	16.7	75.7	131.5	56.5	47.8
95°	40.7	151.2	481.5	209.5	140.7
97.5°	67.4	167.0	738.1	574.3	403.3
100°	85.2	177.5	816.7	827.8	668.5
102.5°	103.0	188.1	837.4	1023.8	883.3
105°	133.3	207.6	825.9	1257.5	1183.3
107.5°	164.8	230.4	778.1	1378.2	1398.9
110°	187.0	246.8	742.6	1402.0	1490.7
112.5°	206.3	263.1	707.0	1382.3	1515.9
115°	237.0	287.7	661.1	1315.2	1498.1
117.5°	265.9	314.4	631.8	1220.2	1426.3
120°	285.2	332.3	618.5	1156.5	1361.1
122.5°	301.5	348.6	609.6	1092.6	1290.0
125°	325.9	371.2	598.1	1007.8	1188.9
127.5°	347.8	392.7	591.8	943.5	1098.9
130°	361.1	404.6	588.9	903.2	1042.6
132.5°	374.4	417.9	585.9	868.7	992.2
135°	392.6	436.0	581.5	820.9	925.9
137.5°	412.2	451.7	579.2	778.7	867.0
140°	424.1	462.1	577.8	751.8	831.5
142.5°	435.9	471.0	576.3	730.8	797.4
145°	453.7	486.3	574.1	697.5	750.0
147.5°	473.7	501.6	572.2	671.3	712.6
150°	487.0	510.6	572.2	656.3	688.9
152.5°	497.4	518.0	570.7	642.8	669.6
155°	513.0	531.1	570.4	626.3	644.4
157.5°	528.1	542.3	570.4	615.1	628.9
160°	537.0	549.7	570.4	607.6	618.5
162.5°	545.9	555.7	571.8	601.7	609.6
165°	555.5	562.8	572.2	596.3	598.1
167.5°	565.5	569.2	574.1	590.0	591.5
170°	568.5	572.1	574.1	587.0	587.0
172.5°	571.5	573.6	574.1	584.1	584.1
175°	575.9	577.7	574.1	581.4	579.6
177.5°	577.4	577.4	573.0	578.8	575.9
180°	575.9	575.9	575.9	575.9	575.9

(END OF REPORT)