

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563514

Luminaire Tested: **SQ4-PP3-0U-100D-830-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563514
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-0U-100D-830-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3603.3 lumens
Efficiency: N/A
Efficacy: 109.9 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563514
CATALOG NUMBER: SQ4-PP3-0U-100D-830-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P563514

CATALOG NUMBER: SQ4-PP3-OU-100D-830-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	109	105	101	97	107	103	99	96	98	95	93	95	92	90	91	89	87	85				
2	100	92	86	80	97	90	84	79	87	82	77	84	79	76	81	77	74	72				
3	92	81	74	67	89	80	73	67	77	71	66	74	69	64	72	67	63	61				
4	84	72	64	57	82	71	63	57	69	62	56	66	60	56	64	59	55	53				
5	77	65	56	50	75	64	56	49	62	54	49	60	53	48	58	52	48	46				
6	72	59	50	44	70	58	49	43	56	49	43	54	48	43	53	47	42	40				
7	66	53	45	39	65	52	44	39	51	44	38	49	43	38	48	42	38	36				
8	62	49	40	35	60	48	40	34	47	39	34	45	39	34	44	38	34	32				
9	58	45	37	31	56	44	36	31	43	36	31	42	35	31	41	35	31	29				
10	54	41	34	28	53	41	33	28	40	33	28	39	33	28	38	32	28	26				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12989	12989	12989
5°	13085	13004	12959
10°	13063	12970	12912
15°	12976	12905	12835
20°	12889	12817	12721
25°	12736	12649	12523
30°	12501	12435	12277
35°	12174	12091	11938
40°	11785	11710	11577
45°	11463	11382	11269
50°	11051	10980	10874
55°	10480	10340	10261
60°	9540	9267	9221
65°	8405	8053	8027
70°	7256	6957	6957
75°	6245	6156	6071
80°	5504	5574	5441
85°	4308	4700	4700



TEST NUMBER: P563514

CATALOG NUMBER: SQ4-PP3-0U-100D-830-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.1	3.7
10°-20°	380.1	10.5
20°-30°	569.4	15.8
30°-40°	667.8	18.5
40°-50°	669.9	18.6
50°-60°	571.5	15.9
60°-70°	372.7	10.3
70°-80°	187.0	5.2
80°-90°	51.7	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1082.6	30.0
0°-40°	1750.4	48.6
0°-60°	2991.8	83.0
0°-90°	3603.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3603.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1408	1408	1408	1408	1408	
5°	1413	1400	1404	1399	1399	134
15°	1358	1345	1351	1346	1344	383
25°	1251	1237	1242	1231	1230	575
35°	1081	1070	1074	1061	1060	675
45°	878	872	872	864	864	676
55°	652	649	643	639	638	579
65°	385	378	369	366	368	384
75°	175	175	173	172	170	190
85°	41	44	44	44	44	49
90°	0	0	0	0	0	



TEST NUMBER: P563514

CATALOG NUMBER: SQ4-PP3-OU-100D-830-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1407.8	1407.8	1407.8	1407.8	1407.8
2.5°	1416.7	1405.1	1407.8	1405.7	1400.0
5°	1412.8	1399.5	1404.1	1399.2	1399.2
7.5°	1403.2	1388.7	1393.3	1388.3	1388.1
10°	1394.3	1379.8	1384.4	1379.4	1378.2
12.5°	1381.4	1367.0	1372.6	1366.6	1366.4
15°	1358.5	1345.2	1351.1	1346.1	1343.7
17.5°	1332.6	1318.1	1325.2	1318.2	1317.3
20°	1312.8	1298.4	1305.4	1295.6	1295.6
22.5°	1289.1	1274.7	1282.7	1269.9	1269.9
25°	1251.1	1236.7	1242.5	1231.4	1230.2
27.5°	1206.0	1191.7	1197.8	1185.3	1185.0
30°	1173.4	1160.1	1167.2	1153.6	1152.4
32.5°	1137.9	1125.6	1130.7	1117.1	1115.9
35°	1080.9	1070.0	1073.5	1061.1	1059.9
37.5°	1020.9	1009.8	1013.7	1003.1	1002.6
40°	978.5	971.2	972.3	963.6	961.2
42.5°	939.0	930.8	931.8	923.2	922.7
45°	878.5	872.5	872.3	863.7	863.7
47.5°	814.4	809.8	808.4	801.3	801.0
50°	769.9	766.3	765.0	758.8	757.6
52.5°	723.5	721.9	717.6	712.4	712.2
55°	651.5	649.1	642.8	639.1	637.9
57.5°	573.3	568.4	561.4	556.0	557.0
60°	517.0	512.2	502.2	499.7	499.7
62.5°	462.7	456.9	446.9	443.5	445.4
65°	385.0	377.7	368.9	366.5	367.7
67.5°	314.4	307.9	298.4	298.3	297.4
70°	269.0	265.4	257.9	257.9	257.9
72.5°	228.5	226.8	221.4	221.3	220.4
75°	175.2	175.2	172.7	171.5	170.3
77.5°	131.3	131.8	130.5	129.3	127.1
80°	103.6	106.1	104.9	103.6	102.4
82.5°	78.0	80.4	80.2	78.0	77.7
85°	40.7	44.3	44.4	44.4	44.4
87.5°	10.9	14.7	15.8	15.8	16.8
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)