

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519694

Luminaire Tested: **SQ4-075U-0D-830-1D-UNV-STD-W-8**

Issue Date: 4/29/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P519694  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22)  
Test Lab: INNOVATION CENTER  
Issue Date: 4/29/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-075U-0D-830-1D-UNV-STD-W-8  
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE  
UPLIGHT 750 LUMENS PER FOOT  
Light Source: 3000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5651.6 lumens  
Efficiency: N/A  
Efficacy: 154.4 lumens/watt  
N/A  
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')  
CIE Type: Indirect

Input Watts (W): 36.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P519694  
CATALOG NUMBER: SQ4-075U-0D-830-1D-UNV-STD-W-8

### Luminous Intensity Polar Plot





TEST NUMBER: P519694

CATALOG NUMBER: SQ4-075U-0D-830-1D-UNV-STD-W-8

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20								20				20				20				20
RC	80								50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10				0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10				0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8				0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7				0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6				0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5				0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4				0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4				0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3				0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3				0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3				0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2				0

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
95°	3223	38300	10454
100°	3384	32511	26773
105°	3586	22108	31418
110°	3759	15062	30174
115°	3888	10860	24540
120°	3968	8600	18937
125°	3949	7259	14385
130°	3895	6359	11286
135°	3865	5720	9116
140°	3857	5246	7559
145°	3856	4865	6382
150°	3893	4582	5536
155°	3946	4369	4951
160°	3978	4214	4567
165°	4002	4117	4311
170°	4012	4046	4150
175°	4017	4000	4043



TEST NUMBER: P519694

CATALOG NUMBER: SQ4-075U-0D-830-1D-UNV-STD-W-8

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	409.2	7.2
100°-110°	1125.7	19.9
110°-120°	1161.9	20.6
120°-130°	931.0	16.5
130°-140°	731.2	12.9
140°-150°	560.3	9.9
150°-160°	402.9	7.1
160°-170°	246.4	4.4
170°-180°	83.0	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	2696.8	47.7
90°-150°	4919.3	87.0
90°-180°	5652.0	100.0
0°-180°	5651.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
90°	2	7	13	17	17	
95°	61	223	724	309	198	68
105°	201	310	1240	1889	1763	212
115°	356	434	995	1981	2248	352
125°	491	560	903	1527	1789	438
135°	592	658	877	1235	1397	457
145°	685	732	864	1052	1133	429
155°	775	800	858	946	973	356
165°	838	849	862	897	903	236
175°	868	869	864	875	873	82
180°	868	868	868	868	868	



TEST NUMBER: P519694

CATALOG NUMBER: SQ4-075U-0D-830-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
90°	1.8	7.3	12.9	16.6	16.6
92.5°	25.5	108.9	188.6	72.4	59.4
95°	60.9	223.3	723.6	309.4	197.5
97.5°	99.3	247.7	1104.2	850.8	600.3
100°	127.4	262.7	1223.8	1235.2	1007.8
102.5°	153.9	280.6	1254.8	1532.4	1323.8
105°	201.2	309.5	1240.4	1889.1	1762.7
107.5°	246.2	345.1	1169.9	2063.7	2101.3
110°	278.7	369.0	1116.7	2107.2	2237.1
112.5°	308.3	395.6	1063.6	2079.2	2277.0
115°	356.2	433.8	994.9	1981.1	2248.2
117.5°	402.0	473.5	951.3	1843.4	2145.6
120°	430.1	498.7	932.1	1740.3	2052.5
122.5°	455.2	523.8	918.8	1649.9	1946.2
125°	491.0	559.6	902.6	1526.9	1788.6
127.5°	524.9	590.3	891.9	1424.3	1653.8
130°	542.7	609.4	886.0	1363.3	1572.6
132.5°	563.3	630.1	881.6	1309.7	1498.8
135°	592.5	657.5	876.8	1234.8	1397.3
137.5°	619.8	680.1	872.7	1174.4	1308.3
140°	640.5	696.4	871.2	1134.2	1255.2
142.5°	658.2	709.8	868.3	1098.4	1202.0
145°	684.8	731.7	863.8	1052.1	1133.3
147.5°	713.2	753.6	861.6	1011.1	1076.1
150°	730.9	767.0	860.1	988.7	1039.2
152.5°	747.2	780.4	858.7	969.3	1011.1
155°	775.2	800.5	858.3	945.7	972.7
157.5°	795.5	816.1	858.3	926.3	945.1
160°	810.3	826.6	858.3	915.9	930.3
162.5°	822.1	835.5	859.8	906.9	918.5
165°	838.0	848.8	862.0	897.2	902.6
167.5°	849.1	857.4	863.8	889.0	890.4
170°	856.5	861.9	863.8	886.0	886.0
172.5°	862.4	864.9	863.8	881.5	880.1
175°	867.5	869.3	863.8	874.9	873.1
177.5°	869.0	869.0	863.1	871.9	869.0
180°	867.5	867.5	867.5	867.5	867.5

(END OF REPORT)