

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563538

Luminaire Tested: **SQ4-PP3-0U-125D-830-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563538
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-0U-125D-830-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4598.3 lumens
Efficiency: N/A
Efficacy: 105.5 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 43.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563538
CATALOG NUMBER: SQ4-PP3-0U-125D-830-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P563538

CATALOG NUMBER: SQ4-PP3-0U-125D-830-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	101	97	107	103	99	96	98	95	93	95	92	90	91	89	87	85
2	100	92	86	80	97	90	84	79	87	82	77	84	79	76	81	77	74	72
3	92	81	74	67	89	80	73	67	77	71	66	74	69	64	72	67	63	61
4	84	72	64	57	82	71	63	57	69	62	56	66	60	56	64	59	55	53
5	77	65	56	50	75	64	56	49	62	54	49	60	53	48	58	52	48	46
6	72	59	50	44	70	58	49	43	56	49	43	54	48	43	53	47	42	40
7	66	53	45	39	65	52	44	39	51	44	38	49	43	38	48	42	38	36
8	62	49	40	35	60	48	40	34	47	39	34	45	39	34	44	38	34	32
9	58	45	37	31	56	44	36	31	43	36	31	42	35	31	41	35	31	29
10	54	41	34	28	53	41	33	28	40	33	28	39	33	28	38	32	28	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16576	16576	16576
5°	16697	16596	16537
10°	16669	16551	16477
15°	16559	16469	16378
20°	16450	16356	16233
25°	16253	16141	15982
30°	15953	15869	15668
35°	15535	15429	15234
40°	15038	14944	14773
45°	14628	14525	14381
50°	14102	14012	13877
55°	13373	13196	13095
60°	12175	11826	11767
65°	10726	10278	10243
70°	9261	8878	8878
75°	7971	7857	7746
80°	7029	7109	6944
85°	5505	6002	6002



TEST NUMBER: P563538

CATALOG NUMBER: SQ4-PP3-0U-125D-830-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	169.9	3.7
10°-20°	485.1	10.5
20°-30°	726.6	15.8
30°-40°	852.2	18.5
40°-50°	854.9	18.6
50°-60°	729.3	15.9
60°-70°	475.6	10.3
70°-80°	238.6	5.2
80°-90°	66.0	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1381.6	30.0
0°-40°	2233.8	48.6
0°-60°	3818.0	83.0
0°-90°	4598.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4598.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1797	1797	1797	1797	1797	
5°	1803	1786	1792	1786	1786	171
15°	1734	1717	1724	1718	1715	489
25°	1597	1578	1586	1571	1570	734
35°	1379	1366	1370	1354	1353	862
45°	1121	1113	1113	1102	1102	863
55°	831	828	820	816	814	739
65°	491	482	471	468	469	490
75°	224	224	220	219	217	243
85°	52	57	57	57	57	63
90°	0	0	0	0	0	



TEST NUMBER: P563538

CATALOG NUMBER: SQ4-PP3-OU-125D-830-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1796.6	1796.6	1796.6	1796.6	1796.6
2.5°	1807.9	1793.2	1796.6	1793.9	1786.5
5°	1802.9	1786.0	1791.9	1785.6	1785.6
7.5°	1790.6	1772.1	1778.0	1771.7	1771.4
10°	1779.3	1760.8	1766.7	1760.4	1758.8
12.5°	1762.9	1744.4	1751.6	1744.0	1743.7
15°	1733.6	1716.7	1724.2	1717.8	1714.7
17.5°	1700.6	1682.1	1691.1	1682.3	1681.0
20°	1675.4	1656.9	1665.9	1653.3	1653.3
22.5°	1645.1	1626.7	1636.9	1620.6	1620.6
25°	1596.6	1578.2	1585.6	1571.4	1569.9
27.5°	1539.0	1520.8	1528.6	1512.5	1512.2
30°	1497.4	1480.5	1489.6	1472.2	1470.7
32.5°	1452.1	1436.4	1442.9	1425.6	1424.1
35°	1379.3	1365.5	1369.9	1354.1	1352.6
37.5°	1302.8	1288.6	1293.7	1280.1	1279.5
40°	1248.6	1239.4	1240.8	1229.7	1226.6
42.5°	1198.3	1187.8	1189.1	1178.1	1177.5
45°	1121.1	1113.4	1113.2	1102.2	1102.2
47.5°	1039.2	1033.4	1031.7	1022.5	1022.2
50°	982.5	977.9	976.2	968.3	966.8
52.5°	923.3	921.2	915.8	909.2	908.9
55°	831.4	828.3	820.4	815.6	814.1
57.5°	731.6	725.4	716.4	709.5	710.8
60°	659.8	653.6	640.9	637.7	637.7
62.5°	590.5	583.1	570.3	566.0	568.4
65°	491.3	482.0	470.8	467.7	469.2
67.5°	401.2	392.9	380.7	380.7	379.5
70°	343.3	338.6	329.1	329.1	329.1
72.5°	291.6	289.5	282.5	282.5	281.2
75°	223.6	223.6	220.4	218.8	217.3
77.5°	167.5	168.2	166.6	165.0	162.2
80°	132.3	135.3	133.8	132.2	130.7
82.5°	99.5	102.6	102.3	99.5	99.2
85°	52.0	56.6	56.7	56.7	56.7
87.5°	13.9	18.8	20.2	20.2	21.4
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)