

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563730

Luminaire Tested: **SQ4-PP3-125U-125D-830-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563730
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-125U-125D-830-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9318.9 lumens
Efficiency: N/A
Efficacy: 123.8 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563730
CATALOG NUMBER: SQ4-PP3-125U-125D-830-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P563730

CATALOG NUMBER: SQ4-PP3-125U-125D-830-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	49
1	98	94	90	86	90	86	83	80	73	71	69	61	59	58	49	48	47	42
2	89	82	76	71	82	76	71	66	64	60	57	54	51	48	44	42	40	35
3	81	72	65	59	75	67	60	55	57	52	48	47	44	41	39	36	34	30
4	75	64	56	50	69	59	52	47	50	45	41	42	38	35	35	32	30	26
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	31	28	26	23
6	63	51	43	37	58	48	40	35	41	35	31	34	30	27	28	25	23	20
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20	18
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16576	16576	16576
5°	16697	16596	16537
10°	16669	16551	16477
15°	16559	16469	16378
20°	16450	16356	16233
25°	16253	16141	15982
30°	15953	15869	15668
35°	15535	15429	15234
40°	15038	14944	14773
45°	14628	14525	14381
50°	14102	14012	13877
55°	13373	13196	13095
60°	12175	11826	11767
65°	10726	10278	10243
70°	9261	8878	8878
75°	7971	7857	7746
80°	7029	7109	6944
85°	5505	6002	6002



TEST NUMBER: P563730

CATALOG NUMBER: SQ4-PP3-125U-125D-830-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	169.9	1.8
10°-20°	485.1	5.2
20°-30°	726.6	7.8
30°-40°	852.2	9.1
40°-50°	854.9	9.2
50°-60°	729.3	7.8
60°-70°	475.6	5.1
70°-80°	238.6	2.6
80°-90°	67.8	0.7
90°-100°	342.0	3.7
100°-110°	921.1	9.9
110°-120°	966.7	10.4
120°-130°	784.4	8.4
130°-140°	615.2	6.6
140°-150°	472.3	5.1
150°-160°	339.6	3.6
160°-170°	207.5	2.2
170°-180°	70.0	0.8
0°-30°	1381.6	14.8
0°-40°	2233.8	24.0
0°-60°	3818.0	41.0
0°-90°	4600.0	49.4
90°-120°	2229.8	23.9
90°-150°	4101.8	44.0
90°-180°	4719.0	50.6
0°-180°	9318.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1797	1797	1797	1797	1797	
5°	1803	1786	1792	1786	1786	171
15°	1734	1717	1724	1718	1715	489
25°	1597	1578	1586	1571	1570	734
35°	1379	1366	1370	1354	1353	862
45°	1121	1113	1113	1102	1102	863
55°	831	828	820	816	814	739
65°	491	482	471	468	469	490
75°	224	224	220	219	217	243
85°	52	57	57	57	57	61
90°	2	6	11	12	12	6
95°	52	186	561	287	198	54
105°	170	265	1019	1524	1430	179
115°	301	368	848	1639	1854	296
125°	411	472	762	1287	1515	367
135°	494	552	740	1039	1176	382
145°	572	616	731	888	954	359
155°	649	673	724	797	822	299
165°	704	712	727	756	760	199
175°	732	731	728	738	737	70
180°	731	731	731	731	731	

TEST NUMBER: P563730

CATALOG NUMBER: SQ4-PP3-125U-125D-830-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1796.6	1796.6	1796.6	1796.6	1796.6
2.5°	1807.9	1793.2	1796.6	1793.9	1786.5
5°	1802.9	1786.0	1791.9	1785.6	1785.6
7.5°	1790.6	1772.1	1778.0	1771.7	1771.4
10°	1779.3	1760.8	1766.7	1760.4	1758.8
12.5°	1762.9	1744.4	1751.6	1744.0	1743.7
15°	1733.6	1716.7	1724.2	1717.8	1714.7
17.5°	1700.6	1682.1	1691.1	1682.3	1681.0
20°	1675.4	1656.9	1665.9	1653.3	1653.3
22.5°	1645.1	1626.7	1636.9	1620.6	1620.6
25°	1596.6	1578.2	1585.6	1571.4	1569.9
27.5°	1539.0	1520.8	1528.6	1512.5	1512.2
30°	1497.4	1480.5	1489.6	1472.2	1470.7
32.5°	1452.1	1436.4	1442.9	1425.6	1424.1
35°	1379.3	1365.5	1369.9	1354.1	1352.6
37.5°	1302.8	1288.6	1293.7	1280.1	1279.5
40°	1248.6	1239.4	1240.8	1229.7	1226.6
42.5°	1198.3	1187.8	1189.1	1178.1	1177.5
45°	1121.1	1113.4	1113.2	1102.2	1102.2
47.5°	1039.2	1033.4	1031.7	1022.5	1022.2
50°	982.5	977.9	976.2	968.3	966.8
52.5°	923.3	921.2	915.8	909.2	908.9
55°	831.4	828.3	820.4	815.6	814.1
57.5°	731.6	725.4	716.4	709.5	710.8
60°	659.8	653.6	640.9	637.7	637.7
62.5°	590.5	583.1	570.3	566.0	568.4
65°	491.3	482.0	470.8	467.7	469.2
67.5°	401.2	392.9	380.7	380.7	379.5
70°	343.3	338.6	329.1	329.1	329.1
72.5°	291.6	289.5	282.5	282.5	281.2
75°	223.6	223.6	220.4	218.8	217.3
77.5°	167.5	168.2	166.6	165.0	162.2
80°	132.3	135.3	133.8	132.2	130.7
82.5°	99.5	102.6	102.3	99.5	99.2
85°	52.0	56.6	56.7	56.7	56.7
87.5°	14.2	19.9	22.4	22.6	23.8
90°	1.9	5.5	11.2	12.1	12.1
92.5°	22.7	80.3	158.7	76.4	53.1
95°	52.1	186.0	560.6	286.7	198.3
97.5°	83.2	212.9	879.2	734.5	553.9
100°	107.1	223.6	980.5	1025.9	851.1
102.5°	130.2	238.7	1014.0	1244.1	1100.6
105°	170.4	265.1	1018.7	1524.1	1430.3
107.5°	208.4	292.9	975.3	1667.9	1692.1
110°	233.7	313.8	935.8	1712.6	1800.9

TEST NUMBER: P563730

CATALOG NUMBER: SQ4-PP3-125U-125D-830-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	260.5	334.8	897.8	1702.7	1847.8
115°	300.8	368.1	848.3	1639.1	1854.0
117.5°	337.5	400.6	809.9	1537.6	1776.9
120°	361.3	422.3	790.6	1464.7	1710.6
122.5°	382.2	442.4	776.4	1390.2	1635.3
125°	410.6	471.6	761.7	1287.4	1515.0
127.5°	438.0	498.1	752.4	1196.7	1399.9
130°	454.4	514.5	748.7	1144.7	1323.2
132.5°	470.8	530.2	744.9	1099.0	1262.9
135°	494.5	551.8	740.3	1038.6	1176.1
137.5°	517.0	572.0	737.9	987.4	1100.3
140°	532.6	585.4	735.6	955.8	1057.8
142.5°	549.0	598.2	734.1	926.4	1012.4
145°	571.7	616.4	731.0	888.0	953.5
147.5°	596.3	635.1	727.8	855.6	907.1
150°	612.7	646.4	726.3	835.3	878.1
152.5°	627.6	656.9	725.6	818.7	853.5
155°	649.0	672.7	724.4	796.7	822.2
157.5°	667.8	686.2	724.6	781.3	798.4
160°	679.8	695.2	725.4	772.2	785.0
162.5°	690.2	702.7	726.1	764.7	773.8
165°	704.0	712.2	727.2	756.2	759.8
167.5°	715.1	719.9	728.2	749.6	751.1
170°	722.6	724.4	728.2	745.9	745.9
172.5°	727.1	727.4	728.9	742.1	742.1
175°	731.9	731.0	728.2	738.4	736.6
177.5°	733.9	732.5	728.7	734.7	733.2
180°	731.0	731.0	731.0	731.0	731.0

(END OF REPORT)