

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519766

Luminaire Tested: **SQ4-150U-0D-830-1D-UNV-STD-W-8**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519766
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-150U-0D-830-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11371.9 lumens
Efficiency: N/A
Efficacy: 148.3 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Indirect

Input Watts (W): 76.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519766
CATALOG NUMBER: SQ4-150U-0D-830-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P519766

CATALOG NUMBER: SQ4-150U-0D-830-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20								20				20				20	
RC	80								50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	6733	72153	22209
100°	6960	62746	52908
105°	7343	43823	61996
110°	7708	30422	58463
115°	7917	22258	48640
120°	8023	17569	38065
125°	7986	14782	29303
130°	7862	12972	22960
135°	7766	11668	18493
140°	7752	10702	15321
145°	7795	9933	12991
150°	7868	9335	11276
155°	7954	8900	10108
160°	8062	8593	9293
165°	8125	8387	8759
170°	8155	8235	8431
175°	8176	8141	8229



TEST NUMBER: P519766

CATALOG NUMBER: SQ4-150U-0D-830-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	819.7	7.2
100°-110°	2216.3	19.5
110°-120°	2330.1	20.5
120°-130°	1892.7	16.6
130°-140°	1484.7	13.1
140°-150°	1139.5	10.0
150°-160°	819.5	7.2
160°-170°	500.6	4.4
170°-180°	168.8	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	5366.2	47.2
90°-150°	9883.0	86.9
90°-180°	11372.0	100.0
0°-180°	11371.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	4	11	25	26	25	
95°	127	446	1363	706	420	141
105°	412	637	2459	3627	3478	434
115°	725	887	2039	3947	4456	716
125°	993	1138	1838	3101	3643	885
135°	1190	1332	1788	2504	2835	920
145°	1384	1488	1764	2143	2307	866
155°	1563	1624	1749	1923	1986	721
165°	1701	1718	1756	1825	1834	479
175°	1766	1764	1758	1781	1777	168
180°	1764	1764	1764	1764	1764	



TEST NUMBER: P519766

CATALOG NUMBER: SQ4-150U-OD-830-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	3.8	11.2	24.7	26.5	24.7
92.5°	53.9	196.5	387.7	168.3	121.9
95°	127.2	446.5	1363.2	705.5	419.6
97.5°	204.3	512.1	2124.9	1758.5	1291.4
100°	262.0	538.6	2361.9	2463.2	1991.6
102.5°	315.2	575.4	2445.4	2997.5	2644.8
105°	412.0	636.6	2458.7	3626.8	3478.3
107.5°	501.6	706.6	2351.2	4019.3	4068.7
110°	571.5	757.1	2255.5	4124.7	4334.5
112.5°	633.8	807.5	2167.5	4103.7	4456.0
115°	725.3	886.8	2039.1	3947.4	4456.0
117.5°	814.9	966.4	1954.4	3708.6	4285.2
120°	869.6	1018.1	1904.3	3537.2	4125.7
122.5°	921.2	1066.7	1873.9	3353.5	3946.4
125°	993.0	1137.8	1837.9	3101.4	3643.4
127.5°	1059.0	1201.2	1816.6	2895.6	3372.3
130°	1095.5	1242.2	1807.5	2768.5	3199.2
132.5°	1133.5	1278.6	1798.4	2653.8	3050.3
135°	1190.4	1331.5	1788.5	2504.2	2834.6
137.5°	1247.8	1381.1	1780.1	2382.8	2652.0
140°	1287.3	1411.6	1777.1	2304.7	2544.1
142.5°	1325.2	1442.2	1771.0	2234.1	2443.9
145°	1384.1	1488.0	1763.8	2143.4	2306.8
147.5°	1437.6	1529.7	1755.5	2061.3	2186.8
150°	1477.1	1558.8	1752.4	2016.7	2116.9
152.5°	1513.6	1584.9	1750.9	1975.3	2057.7
155°	1562.6	1623.8	1748.6	1922.8	1985.9
157.5°	1613.4	1656.1	1749.0	1886.3	1927.8
160°	1642.3	1677.6	1750.5	1863.2	1892.9
162.5°	1665.1	1694.4	1752.0	1844.8	1867.1
165°	1701.2	1717.9	1756.2	1824.8	1834.1
167.5°	1725.8	1737.3	1756.6	1807.6	1812.0
170°	1741.0	1746.6	1758.1	1799.9	1799.9
172.5°	1753.2	1754.3	1758.1	1790.7	1789.2
175°	1765.7	1763.9	1758.1	1780.8	1777.1
177.5°	1769.9	1765.4	1757.7	1772.8	1768.4
180°	1763.8	1763.8	1763.8	1763.8	1763.8

(END OF REPORT)