

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564522

Luminaire Tested: **SQ4-PW1-025U-050D-830-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P564522  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2106-289-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PW1-025U-050D-830-1D-UNV-STD-W-4  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 250 LUMENS PER FOOT  
Light Source: 3000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2732.4 lumens  
Efficiency: N/A  
Efficacy: 123.6 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 22.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P564522  
CATALOG NUMBER: SQ4-PW1-025U-050D-830-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P564522

CATALOG NUMBER: SQ4-PW1-025U-050D-830-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	71	71	71	67				
1	102	97	93	90	96	92	88	85	82	79	77	72	70	68	63	62	61	56				
2	93	85	79	74	87	80	75	70	72	67	64	63	60	57	56	53	51	47				
3	85	75	67	61	79	71	64	59	63	58	54	56	52	49	50	46	44	40				
4	78	66	58	52	73	63	56	50	56	50	46	50	45	42	44	41	38	35				
5	71	59	51	45	67	56	49	43	50	44	40	45	40	36	40	36	33	30				
6	66	53	45	39	62	51	43	38	46	39	35	41	36	32	36	32	29	26				
7	61	48	40	34	57	46	38	33	41	35	31	37	32	28	33	29	26	23				
8	57	44	36	30	53	42	35	29	38	32	27	34	29	25	31	26	23	21				
9	53	40	32	27	50	38	31	26	35	29	25	31	26	23	28	24	21	19				
10	49	37	30	25	47	35	28	24	32	26	22	29	24	21	26	22	19	17				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6600	6600	6600
5°	6642	6590	6561
10°	6589	6535	6501
15°	6519	6446	6423
20°	6441	6343	6330
25°	6351	6236	6217
30°	6217	6123	6083
35°	6040	5955	5920
40°	5852	5761	5738
45°	5625	5551	5526
50°	5391	5347	5309
55°	5139	5139	5059
60°	4825	4919	4744
65°	4416	4637	4307
70°	3893	4268	3790
75°	3326	3818	3233
80°	2577	3214	2614
85°	1673	2467	2202



TEST NUMBER: P564522

CATALOG NUMBER: SQ4-PW1-025U-050D-830-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	67.4	2.5
10°-20°	190.2	7.0
20°-30°	282.1	10.3
30°-40°	330.0	12.1
40°-50°	328.6	12.0
50°-60°	283.7	10.4
60°-70°	204.3	7.5
70°-80°	107.1	3.9
80°-90°	27.3	1.0
90°-100°	68.6	2.5
100°-110°	180.2	6.6
110°-120°	186.9	6.8
120°-130°	149.9	5.5
130°-140°	117.6	4.3
140°-150°	90.3	3.3
150°-160°	65.0	2.4
160°-170°	39.8	1.5
170°-180°	13.4	0.5
0°-30°	539.6	19.7
0°-40°	869.6	31.8
0°-60°	1482.0	54.2
0°-90°	1820.6	66.6
90°-120°	435.7	15.9
90°-150°	793.5	29.0
90°-180°	912.0	33.4
0°-180°	2732.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	715	715	715	715	715	
5°	717	709	712	710	708	68
15°	682	674	675	674	672	192
25°	624	613	613	609	611	287
35°	536	529	529	524	526	335
45°	431	427	425	424	424	333
55°	320	319	320	315	314	285
65°	202	208	212	204	197	200
75°	93	102	107	100	91	100
85°	16	21	23	22	21	21
90°	1	3	7	4	4	1
95°	9	36	118	61	42	10
105°	32	49	199	302	282	34
115°	58	70	160	318	363	57
125°	80	90	145	245	289	71
135°	96	105	141	198	224	74
145°	111	118	139	169	182	69
155°	125	129	139	152	157	58
165°	135	137	139	144	146	38
175°	141	141	140	142	142	13
180°	141	141	141	141	141	

TEST NUMBER: P564522

CATALOG NUMBER: SQ4-PW1-025U-050D-830-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	715.3	715.3	715.3	715.3	715.3
2.5°	719.3	713.4	715.3	713.7	710.2
5°	717.2	709.2	711.5	709.6	708.4
7.5°	709.9	702.5	704.2	702.2	701.4
10°	703.3	695.9	697.6	695.1	693.9
12.5°	695.7	687.9	689.6	687.0	686.3
15°	682.5	673.9	674.9	673.7	672.4
17.5°	667.1	658.4	658.6	656.5	656.3
20°	656.0	646.8	646.0	643.5	644.7
22.5°	643.9	634.2	633.4	629.9	631.6
25°	623.9	613.4	612.6	608.8	610.7
27.5°	600.7	590.4	590.4	585.1	587.1
30°	583.6	573.7	574.7	568.5	571.0
32.5°	565.4	556.5	557.1	550.9	553.3
35°	536.3	528.9	528.7	523.7	525.6
37.5°	506.6	500.0	499.0	496.1	496.6
40°	485.9	480.3	478.3	476.4	476.4
42.5°	464.2	459.2	457.2	455.8	455.3
45°	431.1	427.4	425.4	424.1	423.5
47.5°	398.3	394.8	393.1	392.2	391.6
50°	375.6	373.1	372.5	370.5	369.9
52.5°	352.9	351.4	350.8	348.4	347.7
55°	319.5	318.9	319.5	315.1	314.5
57.5°	284.7	285.7	287.8	281.8	280.3
60°	261.5	264.0	266.6	259.6	257.1
62.5°	237.8	241.8	245.4	237.4	233.9
65°	202.3	208.5	212.4	204.0	197.3
67.5°	168.0	175.7	180.4	171.4	163.7
70°	144.3	152.9	158.2	149.2	140.5
72.5°	123.6	133.3	137.5	129.0	120.4
75°	93.3	101.9	107.1	100.0	90.7
77.5°	66.2	74.3	78.6	72.4	64.8
80°	48.5	57.2	60.5	55.3	49.2
82.5°	34.4	41.6	43.9	40.7	36.6
85°	15.8	20.7	23.3	22.0	20.8
87.5°	4.2	8.0	11.0	10.3	10.8
90°	0.9	2.7	7.2	3.6	3.6
92.5°	3.8	18.2	40.4	17.9	11.5
95°	9.0	35.5	118.1	60.9	41.5
97.5°	15.7	39.0	176.7	140.5	103.5
100°	20.7	41.9	194.8	197.4	153.3
102.5°	25.1	44.8	199.8	245.8	208.1
105°	32.5	49.2	199.3	302.5	282.2
107.5°	40.0	55.6	187.9	331.9	336.9
110°	45.1	59.2	178.5	339.5	360.7

TEST NUMBER: P564522

CATALOG NUMBER: SQ4-PW1-025U-050D-830-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	50.1	63.5	169.9	334.7	367.2
115°	57.7	70.1	159.6	318.4	363.4
117.5°	65.1	76.4	152.6	295.8	345.7
120°	69.4	80.0	149.7	280.6	329.1
122.5°	73.8	84.3	147.5	265.5	313.2
125°	80.3	89.9	145.2	245.4	289.4
127.5°	85.5	95.4	143.2	229.2	266.4
130°	88.4	98.9	142.5	219.0	253.4
132.5°	91.3	101.8	141.7	210.3	241.1
135°	95.6	105.3	140.7	198.1	224.5
137.5°	100.1	109.6	140.5	188.9	210.6
140°	103.7	112.5	139.8	181.7	202.0
142.5°	106.6	114.7	139.8	176.6	194.0
145°	110.9	118.0	138.9	168.9	182.1
147.5°	115.2	122.1	138.9	162.6	173.5
150°	118.1	124.3	138.9	158.9	167.7
152.5°	121.0	125.8	138.9	156.0	162.7
155°	125.3	128.9	138.9	152.5	156.9
157.5°	128.6	131.9	138.9	149.4	152.6
160°	130.7	133.4	138.9	147.9	149.7
162.5°	132.9	134.8	138.9	146.5	148.2
165°	135.3	137.0	138.9	144.3	146.1
167.5°	137.4	138.3	139.8	143.4	144.1
170°	138.9	139.7	139.8	143.4	143.4
172.5°	139.6	139.8	139.8	142.6	141.9
175°	140.7	140.7	139.8	141.6	141.6
177.5°	140.7	140.7	139.9	141.4	140.7
180°	140.7	140.7	140.7	140.7	140.7

(END OF REPORT)