

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P518686

Luminaire Tested: **SQ4-BB-100U-050D-830-1D-UNV-STD-W-8**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P518686
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2009-966-12)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-BB-100U-050D-830-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH BLACK BAFFLE
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9950.6 lumens
Efficiency: N/A
Efficacy: 117.5 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.97 / 0.97
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 84.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P518686
CATALOG NUMBER: SQ4-BB-100U-050D-830-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P518686

CATALOG NUMBER: SQ4-BB-100U-050D-830-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32	24
1	93	89	86	82	82	79	77	74	61	60	58	45	44	43	30	29	29	22
2	85	79	73	69	76	70	66	62	55	52	49	40	39	37	27	26	25	20
3	78	70	63	58	70	63	57	53	49	45	42	36	34	32	25	24	23	18
4	72	62	55	50	64	56	50	45	44	40	37	33	31	28	23	21	20	16
5	66	56	49	43	59	50	44	39	40	36	32	30	27	25	21	19	18	15
6	61	50	43	38	55	45	39	35	36	32	28	27	25	22	19	18	17	13
7	57	46	38	33	51	41	35	31	33	29	25	25	22	20	18	16	15	12
8	53	41	34	30	47	38	31	27	30	26	23	23	20	18	17	15	14	11
9	49	38	31	26	44	34	28	24	28	23	20	21	19	17	16	14	13	10
10	46	35	28	24	41	32	26	22	26	21	19	20	17	15	15	13	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9151	9151	9151
5°	9003	8981	9048
10°	8424	8536	8775
15°	7658	7901	8341
20°	6798	7151	7778
25°	5920	6389	7146
30°	5071	5628	6548
35°	4205	4777	5826
40°	3230	3820	4964
45°	2335	2893	3994
50°	1591	2156	3168
55°	1034	1559	2462
60°	593	1098	1780
65°	157	670	901
70°	78	208	259
75°	34	18	0
80°	27	0	0
85°	0	0	0



TEST NUMBER: P518686

CATALOG NUMBER: SQ4-BB-100U-050D-830-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	181.0	1.8
10°-20°	462.9	4.7
20°-30°	579.5	5.8
30°-40°	535.3	5.4
40°-50°	359.7	3.6
50°-60°	185.8	1.9
60°-70°	58.2	0.6
70°-80°	3.7	0.0
80°-90°	2.5	0.0
90°-100°	546.5	5.5
100°-110°	1508.6	15.2
110°-120°	1555.9	15.6
120°-130°	1250.3	12.6
130°-140°	982.6	9.9
140°-150°	753.6	7.6
150°-160°	541.6	5.4
160°-170°	331.2	3.3
170°-180°	111.7	1.1
0°-30°	1223.5	12.3
0°-40°	1758.8	17.7
0°-60°	2304.3	23.2
0°-90°	2368.6	23.8
90°-120°	3611.0	36.3
90°-150°	6597.5	66.3
90°-180°	7582.0	76.2
0°-180°	9950.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1984	1984	1984	1984	1984	
5°	1944	1924	1939	1946	1954	180
15°	1604	1598	1654	1710	1746	447
25°	1163	1172	1255	1341	1404	533
35°	747	765	848	948	1034	462
45°	358	380	443	530	612	281
55°	129	150	194	249	306	120
65°	14	28	61	74	82	24
75°	2	2	1	0	0	3
85°	0	0	0	0	0	0
90°	4	7	15	17	19	6
95°	80	296	991	408	265	86
105°	269	415	1660	2534	2386	286
115°	482	582	1337	2646	3010	473
125°	661	752	1212	2051	2407	588
135°	795	881	1178	1661	1873	615
145°	922	986	1163	1414	1522	577
155°	1040	1075	1154	1269	1309	479
165°	1126	1140	1159	1204	1214	317
175°	1167	1169	1161	1178	1174	111
180°	1167	1167	1167	1167	1167	

TEST NUMBER: P518686

CATALOG NUMBER: SQ4-BB-100U-050D-830-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1983.6	1983.6	1983.6	1983.6	1983.6
2.5°	1988.2	1969.4	1974.4	1974.2	1969.0
5°	1944.2	1924.5	1939.4	1946.3	1953.8
7.5°	1862.1	1846.7	1875.3	1896.8	1912.4
10°	1798.4	1785.2	1822.3	1851.6	1873.2
12.5°	1724.7	1714.5	1759.4	1799.6	1827.1
15°	1603.5	1597.9	1654.4	1709.9	1746.5
17.5°	1473.8	1473.6	1538.1	1607.0	1651.1
20°	1384.8	1387.6	1456.7	1532.7	1584.4
22.5°	1295.7	1302.3	1376.1	1455.4	1514.5
25°	1163.1	1172.5	1255.2	1341.1	1403.9
27.5°	1035.6	1049.3	1136.4	1225.7	1302.2
30°	952.0	967.9	1056.6	1150.5	1229.3
32.5°	869.8	888.8	975.2	1074.5	1154.8
35°	746.6	765.4	848.3	948.2	1034.5
37.5°	619.3	637.7	718.8	817.0	910.3
40°	536.4	557.1	634.3	729.6	824.3
42.5°	461.2	481.8	554.5	648.1	737.6
45°	357.9	379.5	443.4	529.7	612.2
47.5°	272.3	295.8	351.8	429.9	505.2
50°	221.7	245.1	300.4	369.2	441.4
52.5°	181.0	203.7	253.5	318.4	384.6
55°	128.6	150.2	193.8	248.9	306.1
57.5°	88.9	107.4	146.6	192.6	237.4
60°	64.3	82.1	119.0	156.3	192.9
62.5°	42.8	59.1	95.2	123.8	148.4
65°	14.4	27.5	61.4	74.1	82.5
67.5°	7.3	8.8	32.2	34.0	36.8
70°	5.8	5.8	15.4	16.4	19.2
72.5°	4.2	4.2	6.1	7.9	8.4
75°	1.9	1.9	1.0	0.0	0.0
77.5°	1.0	1.0	0.8	0.0	0.0
80°	1.0	1.0	0.0	0.0	0.0
82.5°	0.2	0.2	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.7	1.5	3.0	3.4	3.7
90°	3.7	7.4	14.9	16.8	18.7
92.5°	33.6	139.5	249.4	91.0	70.9
95°	80.3	295.7	991.4	407.5	265.1
97.5°	132.9	331.2	1468.6	1130.7	818.9
100°	171.8	352.5	1644.9	1656.5	1346.1
102.5°	209.1	376.7	1679.2	2046.7	1752.4
105°	268.9	414.9	1659.8	2534.0	2386.1
107.5°	332.3	462.3	1567.2	2768.9	2823.0
110°	377.1	494.0	1495.5	2819.5	2994.7



TEST NUMBER: P518686

CATALOG NUMBER: SQ4-BB-100U-050D-830-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	417.5	529.9	1428.3	2779.6	3038.1
115°	481.7	582.1	1336.8	2646.4	3009.7
117.5°	537.7	637.8	1276.7	2459.0	2872.3
120°	575.1	673.6	1252.8	2332.1	2748.3
122.5°	610.9	705.1	1233.4	2213.6	2607.9
125°	660.9	752.2	1211.7	2050.6	2406.6
127.5°	703.5	794.8	1199.0	1912.9	2219.9
130°	731.9	823.2	1193.0	1828.6	2107.9
132.5°	758.8	845.7	1187.1	1757.8	2010.8
135°	795.4	881.2	1178.1	1660.9	1872.7
137.5°	836.4	914.6	1173.6	1579.5	1760.3
140°	858.8	935.5	1170.6	1525.3	1684.1
142.5°	884.2	955.1	1167.7	1477.0	1616.9
145°	922.3	986.2	1163.2	1413.9	1521.6
147.5°	958.9	1014.8	1159.1	1360.7	1444.3
150°	985.8	1031.4	1157.6	1329.0	1396.6
152.5°	1006.7	1049.4	1156.1	1301.9	1357.7
155°	1039.9	1074.6	1153.8	1268.6	1308.8
157.5°	1070.6	1097.2	1154.2	1244.5	1271.8
160°	1088.5	1112.2	1155.7	1230.8	1250.9
162.5°	1103.4	1124.2	1157.2	1218.8	1234.5
165°	1125.8	1140.4	1159.4	1204.5	1213.6
167.5°	1143.0	1151.8	1161.3	1195.7	1198.6
170°	1152.0	1159.3	1161.3	1191.2	1191.2
172.5°	1159.4	1163.8	1161.3	1185.2	1183.7
175°	1166.9	1168.7	1161.3	1178.0	1174.4
177.5°	1169.9	1168.4	1160.9	1171.3	1168.4
180°	1166.9	1166.9	1166.9	1166.9	1166.9

(END OF REPORT)