

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P518878

Luminaire Tested: **SQ4-BB-150U-050D-830-1D-UNV-STD-W-8**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P518878
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2009-966-12)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-BB-150U-050D-830-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH BLACK BAFFLE
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13741.8 lumens
Efficiency: N/A
Efficacy: 122.8 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.97 / 0.97
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 111.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P518878
CATALOG NUMBER: SQ4-BB-150U-050D-830-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P518878

CATALOG NUMBER: SQ4-BB-150U-050D-830-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	99	99	99	99	87	87	87	87	65	65	65	45	45	45	26	26	26	17
1	91	87	84	81	80	77	74	72	58	56	54	40	39	38	24	23	23	16
2	83	77	71	67	73	68	63	60	51	48	46	36	34	33	22	21	20	14
3	76	68	61	56	67	60	55	51	46	42	39	32	30	29	20	19	18	13
4	70	60	53	48	62	54	48	43	41	37	34	29	27	25	18	17	16	12
5	64	54	47	41	57	48	42	37	37	33	30	26	24	22	17	15	14	11
6	59	48	41	36	52	43	37	33	33	29	26	24	21	19	15	14	13	10
7	55	44	37	32	48	39	33	29	30	26	23	22	19	17	14	13	12	9
8	51	40	33	28	45	36	30	25	28	23	20	20	18	16	13	12	11	8
9	47	36	29	25	42	32	27	23	25	21	18	19	16	14	12	11	10	8
10	44	33	27	22	39	30	24	20	23	19	16	17	15	13	11	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9151	9151	9151
5°	9003	8981	9048
10°	8424	8536	8775
15°	7658	7901	8341
20°	6798	7151	7778
25°	5920	6389	7146
30°	5071	5628	6548
35°	4205	4777	5826
40°	3230	3820	4964
45°	2335	2893	3994
50°	1591	2156	3168
55°	1034	1559	2462
60°	593	1098	1780
65°	157	670	901
70°	78	208	259
75°	34	18	0
80°	27	0	0
85°	0	0	0



TEST NUMBER: P518878

CATALOG NUMBER: SQ4-BB-150U-050D-830-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	181.0	1.3
10°-20°	462.9	3.4
20°-30°	579.5	4.2
30°-40°	535.3	3.9
40°-50°	359.7	2.6
50°-60°	185.8	1.4
60°-70°	58.2	0.4
70°-80°	3.7	0.0
80°-90°	3.7	0.0
90°-100°	819.7	6.0
100°-110°	2216.3	16.1
110°-120°	2330.1	17.0
120°-130°	1892.7	13.8
130°-140°	1484.7	10.8
140°-150°	1139.5	8.3
150°-160°	819.5	6.0
160°-170°	500.6	3.6
170°-180°	168.8	1.2
0°-30°	1223.5	8.9
0°-40°	1758.8	12.8
0°-60°	2304.3	16.8
0°-90°	2369.9	17.2
90°-120°	5366.2	39.0
90°-150°	9883.0	71.9
90°-180°	11372.0	82.8
0°-180°	13741.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1984	1984	1984	1984	1984	
5°	1944	1924	1939	1946	1954	180
15°	1604	1598	1654	1710	1746	447
25°	1163	1172	1255	1341	1404	533
35°	747	765	848	948	1034	462
45°	358	380	443	530	612	281
55°	129	150	194	249	306	120
65°	14	28	61	74	82	24
75°	2	2	1	0	0	3
85°	0	0	0	0	0	0
90°	4	11	25	26	25	9
95°	127	446	1363	706	420	133
105°	412	637	2459	3627	3478	434
115°	725	887	2039	3947	4456	716
125°	993	1138	1838	3101	3643	885
135°	1190	1332	1788	2504	2835	920
145°	1384	1488	1764	2143	2307	866
155°	1563	1624	1749	1923	1986	721
165°	1701	1718	1756	1825	1834	479
175°	1766	1764	1758	1781	1777	168
180°	1764	1764	1764	1764	1764	



TEST NUMBER: P518878

CATALOG NUMBER: SQ4-BB-150U-050D-830-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1983.6	1983.6	1983.6	1983.6	1983.6
2.5°	1988.2	1969.4	1974.4	1974.2	1969.0
5°	1944.2	1924.5	1939.4	1946.3	1953.8
7.5°	1862.1	1846.7	1875.3	1896.8	1912.4
10°	1798.4	1785.2	1822.3	1851.6	1873.2
12.5°	1724.7	1714.5	1759.4	1799.6	1827.1
15°	1603.5	1597.9	1654.4	1709.9	1746.5
17.5°	1473.8	1473.6	1538.1	1607.0	1651.1
20°	1384.8	1387.6	1456.7	1532.7	1584.4
22.5°	1295.7	1302.3	1376.1	1455.4	1514.5
25°	1163.1	1172.5	1255.2	1341.1	1403.9
27.5°	1035.6	1049.3	1136.4	1225.7	1302.2
30°	952.0	967.9	1056.6	1150.5	1229.3
32.5°	869.8	888.8	975.2	1074.5	1154.8
35°	746.6	765.4	848.3	948.2	1034.5
37.5°	619.3	637.7	718.8	817.0	910.3
40°	536.4	557.1	634.3	729.6	824.3
42.5°	461.2	481.8	554.5	648.1	737.6
45°	357.9	379.5	443.4	529.7	612.2
47.5°	272.3	295.8	351.8	429.9	505.2
50°	221.7	245.1	300.4	369.2	441.4
52.5°	181.0	203.7	253.5	318.4	384.6
55°	128.6	150.2	193.8	248.9	306.1
57.5°	88.9	107.4	146.6	192.6	237.4
60°	64.3	82.1	119.0	156.3	192.9
62.5°	42.8	59.1	95.2	123.8	148.4
65°	14.4	27.5	61.4	74.1	82.5
67.5°	7.3	8.8	32.2	34.0	36.8
70°	5.8	5.8	15.4	16.4	19.2
72.5°	4.2	4.2	6.1	7.9	8.4
75°	1.9	1.9	1.0	0.0	0.0
77.5°	1.0	1.0	0.8	0.0	0.0
80°	1.0	1.0	0.0	0.0	0.0
82.5°	0.2	0.2	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.8	2.2	4.9	5.3	4.9
90°	3.8	11.2	24.7	26.5	24.7
92.5°	53.9	196.5	387.7	168.3	121.9
95°	127.2	446.5	1363.2	705.5	419.6
97.5°	204.3	512.1	2124.9	1758.5	1291.4
100°	262.0	538.6	2361.9	2463.2	1991.6
102.5°	315.2	575.4	2445.4	2997.5	2644.8
105°	412.0	636.6	2458.7	3626.8	3478.3
107.5°	501.6	706.6	2351.2	4019.3	4068.7
110°	571.5	757.1	2255.5	4124.7	4334.5



TEST NUMBER: P518878

CATALOG NUMBER: SQ4-BB-150U-050D-830-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	633.8	807.5	2167.5	4103.7	4456.0
115°	725.3	886.8	2039.1	3947.4	4456.0
117.5°	814.9	966.4	1954.4	3708.6	4285.2
120°	869.6	1018.1	1904.3	3537.2	4125.7
122.5°	921.2	1066.7	1873.9	3353.5	3946.4
125°	993.0	1137.8	1837.9	3101.4	3643.4
127.5°	1059.0	1201.2	1816.6	2895.6	3372.3
130°	1095.5	1242.2	1807.5	2768.5	3199.2
132.5°	1133.5	1278.6	1798.4	2653.8	3050.3
135°	1190.4	1331.5	1788.5	2504.2	2834.6
137.5°	1247.8	1381.1	1780.1	2382.8	2652.0
140°	1287.3	1411.6	1777.1	2304.7	2544.1
142.5°	1325.2	1442.2	1771.0	2234.1	2443.9
145°	1384.1	1488.0	1763.8	2143.4	2306.8
147.5°	1437.6	1529.7	1755.5	2061.3	2186.8
150°	1477.1	1558.8	1752.4	2016.7	2116.9
152.5°	1513.6	1584.9	1750.9	1975.3	2057.7
155°	1562.6	1623.8	1748.6	1922.8	1985.9
157.5°	1613.4	1656.1	1749.0	1886.3	1927.8
160°	1642.3	1677.6	1750.5	1863.2	1892.9
162.5°	1665.1	1694.4	1752.0	1844.8	1867.1
165°	1701.2	1717.9	1756.2	1824.8	1834.1
167.5°	1725.8	1737.3	1756.6	1807.6	1812.0
170°	1741.0	1746.6	1758.1	1799.9	1799.9
172.5°	1753.2	1754.3	1758.1	1790.7	1789.2
175°	1765.7	1763.9	1758.1	1780.8	1777.1
177.5°	1769.9	1765.4	1757.7	1772.8	1768.4
180°	1763.8	1763.8	1763.8	1763.8	1763.8

(END OF REPORT)