

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P519982

Luminaire Tested: **SQ4-F-075U-050D-830-1D-UNV-STD-W-8**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519982
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G3-1910-536-17)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-F-075U-050D-830-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9448.9 lumens
Efficiency: N/A
Efficacy: 130.9 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 72.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519982
CATALOG NUMBER: SQ4-F-075U-050D-830-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P519982

CATALOG NUMBER: SQ4-F-075U-050D-830-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40
1	96	91	87	84	87	83	80	77	68	66	64	54	53	51	42	41	40	34
2	87	80	74	68	79	73	68	63	60	56	53	48	45	43	37	35	33	28
3	79	70	63	57	72	64	58	53	53	48	44	42	39	36	32	30	28	24
4	72	62	54	48	66	56	50	44	47	42	38	37	34	31	29	26	24	20
5	66	55	47	41	60	50	43	38	42	36	32	33	30	27	26	23	21	18
6	61	49	41	35	55	45	38	33	37	32	28	30	26	23	23	21	19	15
7	56	44	36	31	51	41	34	29	34	28	25	27	23	20	21	19	16	14
8	52	40	32	27	47	37	30	25	31	25	22	25	21	18	20	17	15	12
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13	11
10	45	33	26	22	41	31	24	20	26	21	17	21	17	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6415	6415	6415
5°	6431	6353	6404
10°	6409	6330	6374
15°	6366	6285	6338
20°	6305	6232	6278
25°	6235	6159	6215
30°	6148	6098	6137
35°	6080	6007	6038
40°	5964	5908	5918
45°	5841	5793	5793
50°	5718	5664	5637
55°	5584	5509	5479
60°	5376	5289	5255
65°	5120	5019	4958
70°	4771	4669	4570
75°	4279	4148	4048
80°	3462	3414	3313
85°	2064	2366	2461



TEST NUMBER: P519982

CATALOG NUMBER: SQ4-F-075U-050D-830-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.2	1.4
10°-20°	373.6	4.0
20°-30°	561.2	5.9
30°-40°	669.8	7.1
40°-50°	686.4	7.3
50°-60°	612.2	6.5
60°-70°	455.9	4.8
70°-80°	247.5	2.6
80°-90°	59.5	0.6
90°-100°	409.2	4.3
100°-110°	1125.7	11.9
110°-120°	1161.9	12.3
120°-130°	931.0	9.9
130°-140°	731.2	7.7
140°-150°	560.4	5.9
150°-160°	402.9	4.3
160°-170°	246.4	2.6
170°-180°	83.0	0.9
0°-30°	1066.0	11.3
0°-40°	1735.8	18.4
0°-60°	3034.4	32.1
0°-90°	3797.3	40.2
90°-120°	2696.8	28.5
90°-150°	4919.3	52.1
90°-180°	5652.0	59.8
0°-180°	9448.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1390	1390	1390	1390	1390	
5°	1389	1387	1372	1385	1383	132
15°	1333	1329	1316	1327	1327	376
25°	1225	1221	1210	1218	1221	564
35°	1080	1076	1067	1067	1072	674
45°	895	897	888	886	888	691
55°	694	694	685	680	681	618
65°	469	467	460	454	454	465
75°	240	238	233	229	227	254
85°	39	43	45	46	46	55
90°	2	7	13	17	17	5
95°	61	223	724	309	198	64
105°	201	310	1240	1889	1763	212
115°	356	434	995	1981	2248	352
125°	491	560	903	1527	1789	438
135°	592	658	877	1235	1397	457
145°	685	732	864	1052	1133	429
155°	775	800	858	946	973	356
165°	838	849	862	897	903	236
175°	868	869	864	875	873	82
180°	868	868	868	868	868	

TEST NUMBER: P519982

CATALOG NUMBER: SQ4-F-075U-050D-830-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1390.5	1390.5	1390.5	1390.5	1390.5
2.5°	1395.0	1392.1	1380.1	1390.4	1389.1
5°	1388.7	1386.8	1371.9	1384.9	1383.0
7.5°	1378.6	1375.0	1360.4	1373.0	1371.1
10°	1368.2	1364.5	1351.4	1362.5	1360.8
12.5°	1354.7	1352.6	1338.0	1349.2	1348.8
15°	1332.9	1329.2	1316.1	1327.2	1327.2
17.5°	1303.8	1301.6	1288.9	1299.6	1298.1
20°	1284.4	1280.8	1269.5	1278.8	1278.8
22.5°	1260.6	1258.4	1247.2	1255.1	1256.5
25°	1224.9	1221.2	1210.0	1217.5	1221.1
27.5°	1185.3	1182.5	1173.1	1177.9	1180.5
30°	1154.1	1154.1	1144.8	1146.8	1152.2
32.5°	1125.8	1125.8	1115.0	1116.9	1119.5
35°	1079.6	1076.0	1066.6	1066.7	1072.2
37.5°	1026.0	1024.2	1018.2	1017.1	1018.6
40°	990.3	988.5	981.0	982.8	982.8
42.5°	954.6	952.7	945.2	942.7	945.6
45°	895.3	897.2	887.9	886.1	887.9
47.5°	836.9	836.9	829.5	824.3	827.2
50°	796.7	796.7	789.2	785.5	785.5
52.5°	755.0	756.5	747.5	742.4	743.9
55°	694.3	694.3	685.0	679.5	681.3
57.5°	627.3	627.3	618.0	612.5	615.8
60°	582.7	582.7	573.3	567.8	569.6
62.5°	538.0	538.0	528.6	523.1	523.4
65°	469.1	467.3	459.8	454.2	454.2
67.5°	402.8	398.1	392.4	385.0	385.0
70°	353.7	351.8	346.2	338.8	338.8
72.5°	309.0	305.7	300.1	294.1	294.1
75°	240.1	238.3	232.7	229.0	227.1
77.5°	172.0	170.6	170.1	165.0	166.4
80°	130.3	130.3	128.5	124.7	124.7
82.5°	93.1	94.6	91.2	90.4	88.9
85°	39.0	42.7	44.7	46.5	46.5
87.5°	7.8	13.3	13.0	15.3	15.3
90°	1.9	7.2	12.9	16.6	16.6
92.5°	25.4	108.9	188.7	72.4	59.5
95°	60.9	223.3	723.5	309.4	197.5
97.5°	99.3	247.7	1104.2	850.8	600.3
100°	127.4	262.7	1223.7	1235.2	1007.9
102.5°	154.0	280.6	1254.8	1532.4	1323.8
105°	201.2	309.5	1240.4	1889.0	1762.8
107.5°	246.2	345.2	1169.8	2063.7	2101.3
110°	278.8	368.9	1116.7	2107.2	2237.2



TEST NUMBER: P519982

CATALOG NUMBER: SQ4-F-075U-050D-830-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	308.2	395.6	1063.5	2079.2	2277.0
115°	356.2	433.9	994.8	1981.1	2248.2
117.5°	402.0	473.5	951.3	1843.5	2145.6
120°	430.1	498.6	932.1	1740.3	2052.6
122.5°	455.2	523.8	918.8	1649.9	1946.3
125°	491.0	559.6	902.6	1526.9	1788.6
127.5°	525.0	590.3	891.8	1424.2	1653.8
130°	542.7	609.5	886.0	1363.3	1572.6
132.5°	563.3	630.1	881.6	1309.7	1498.8
135°	592.5	657.5	876.8	1234.9	1397.2
137.5°	619.8	680.1	872.7	1174.4	1308.3
140°	640.5	696.4	871.2	1134.2	1255.1
142.5°	658.2	709.8	868.3	1098.4	1202.0
145°	684.8	731.7	863.9	1052.1	1133.3
147.5°	713.2	753.6	861.6	1011.2	1076.1
150°	730.9	767.0	860.2	988.7	1039.2
152.5°	747.2	780.4	858.7	969.2	1011.2
155°	775.3	800.5	858.3	945.6	972.7
157.5°	795.5	816.1	858.3	926.3	945.1
160°	810.3	826.5	858.3	915.8	930.3
162.5°	822.1	835.5	859.8	906.9	918.5
165°	838.0	848.8	862.0	897.2	902.6
167.5°	849.1	857.4	863.9	889.0	890.4
170°	856.4	861.9	863.9	886.0	886.0
172.5°	862.4	864.9	863.9	881.5	880.1
175°	867.5	869.4	863.9	874.8	873.1
177.5°	869.0	869.0	863.1	871.9	869.0
180°	867.5	867.5	867.5	867.5	867.5

(END OF REPORT)