

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937212

Luminaire Tested: SQ4-FB-075U-100D-830-1D-UNV-STD-W-8

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937212
REPORT IS A COMBINATION OF REPORTS P933519 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-075U-100D-830-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11806.6 lumens
Efficiency: N/A
Efficacy: 115.3 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 102.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937212
CATALOG NUMBER: SQ4-FB-075U-100D-830-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P937212

CATALOG NUMBER: SQ4-FB-075U-100D-830-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	58	58	58	52
1	98	93	89	85	90	86	82	79	73	70	68	61	59	57	50	49	47	47	47	47	42
2	88	80	74	69	81	74	69	64	63	59	55	53	50	47	43	41	39	39	39	39	34
3	80	70	62	56	74	65	58	53	55	50	46	46	42	39	38	35	32	32	32	32	28
4	73	62	53	47	67	57	50	44	49	43	38	41	36	33	33	30	27	27	27	27	24
5	67	55	46	40	61	51	43	37	43	37	33	36	32	28	30	26	23	23	23	23	20
6	61	49	40	34	56	45	38	32	39	33	28	32	28	24	27	23	20	20	20	20	17
7	56	44	35	30	52	41	33	28	35	29	24	29	25	21	24	20	18	18	18	18	15
8	52	39	31	26	48	37	29	24	31	26	21	27	22	19	22	18	16	16	16	16	13
9	49	36	28	23	45	33	26	22	29	23	19	24	20	16	20	17	14	14	14	14	12
10	45	33	25	20	42	31	24	19	26	21	17	22	18	15	19	15	12	12	12	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3645	3645	3645
5°	3561	4213	4900
10°	3230	6142	8123
15°	2745	8024	9809
20°	2235	9299	9997
25°	1864	9730	9794
30°	1572	9792	9775
35°	1390	9629	10028
40°	1211	9418	10289
45°	1097	9263	10330
50°	1006	9124	10158
55°	963	8920	9709
60°	986	8528	8997
65°	1026	7933	8020
70°	1094	6918	6775
75°	1211	5641	5288
80°	1325	3912	3564
85°	1174	2076	1824

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 10330 cd/sqm



TEST NUMBER: P937212

CATALOG NUMBER: SQ4-FB-075U-100D-830-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.6	0.9
10°-20°	450.4	3.8
20°-30°	787.9	6.7
30°-40°	1014.3	8.6
40°-50°	1132.9	9.6
50°-60°	1085.1	9.2
60°-70°	859.9	7.3
70°-80°	505.7	4.3
80°-90°	143.9	1.2
90°-100°	430.5	3.6
100°-110°	1131.8	9.6
110°-120°	1173.5	9.9
120°-130°	941.3	8.0
130°-140°	738.6	6.3
140°-150°	566.9	4.8
150°-160°	408.3	3.5
160°-170°	249.8	2.1
170°-180°	84.4	0.7
0°-30°	1340.0	11.3
0°-40°	2354.3	19.9
0°-60°	4572.2	38.7
0°-90°	6081.6	51.5
90°-120°	2735.8	23.2
90°-150°	4982.6	42.2
90°-180°	5725.0	48.5
0°-180°	11806.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	786	786	786	786	786	
5°	766	821	925	1046	1084	71
15°	574	1059	1784	2163	2231	160
25°	366	1200	2125	2218	2221	169
35°	248	1147	2001	2115	2198	155
45°	169	914	1768	2026	2117	131
55°	121	581	1501	1743	1791	110
65°	96	308	1114	1253	1271	95
75°	71	190	611	672	675	74
85°	25	58	152	167	169	27
90°	6	17	45	23	23	7
95°	57	223	742	382	260	63
105°	204	309	1251	1900	1772	216
115°	362	440	1002	1999	2282	358
125°	504	565	912	1540	1817	447
135°	600	661	883	1244	1410	465
145°	696	741	872	1061	1144	436
155°	787	809	872	957	985	362
165°	849	861	872	906	918	240
175°	883	883	878	889	889	84
180°	883	883	883	883	883	



TEST NUMBER: P937212

CATALOG NUMBER: SQ4-FB-075U-100D-830-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	785.7	785.7	785.7	785.7	785.7	785.7	785.7	785.7	785.7	785.7	785.7
2.5°	785.7	785.7	790.8	793.3	798.4	800.8	805.9	811.0	826.2	828.7	833.7
5°	765.5	775.6	808.5	821.1	856.5	904.5	924.6	957.5	1025.7	1046.0	1058.6
7.5°	735.2	757.9	838.8	859.0	947.4	1073.7	1126.7	1197.5	1306.2	1359.2	1402.2
10°	687.2	735.2	879.2	927.2	1071.2	1263.2	1361.7	1460.3	1624.4	1697.8	1725.5
12.5°	634.1	712.4	922.2	987.8	1195.0	1475.4	1594.1	1702.8	1889.7	1988.3	2003.4
15°	573.5	679.6	962.6	1058.6	1326.4	1652.3	1783.6	1917.5	2091.8	2162.6	2180.3
17.5°	520.4	654.4	1000.5	1101.5	1427.4	1811.4	1945.4	2056.5	2197.9	2245.9	2258.6
20°	454.8	613.9	1025.7	1157.0	1533.5	1927.7	2056.5	2142.4	2238.4	2268.7	2273.8
22.5°	406.8	570.9	1040.9	1177.3	1604.3	1998.4	2107.0	2175.2	2241.0	2251.0	2253.6
25°	366.3	522.9	1038.3	1200.1	1664.9	2041.3	2124.7	2175.2	2213.1	2218.2	2218.2
27.5°	328.4	469.9	1028.3	1205.1	1710.4	2051.5	2117.2	2152.5	2170.2	2180.3	2180.3
30°	295.6	419.4	1002.9	1195.0	1730.6	2041.3	2094.4	2112.1	2129.8	2144.9	2152.5
32.5°	270.4	371.4	965.1	1174.7	1733.1	2016.1	2054.0	2064.1	2089.3	2124.7	2137.3
35°	247.6	323.4	922.2	1147.0	1717.9	1975.7	2000.9	2011.0	2061.5	2114.6	2132.3
37.5°	224.9	288.0	866.5	1099.0	1695.2	1927.7	1945.4	1963.1	2041.3	2104.4	2124.7
40°	202.1	257.7	800.8	1046.0	1659.8	1869.6	1884.7	1912.5	2016.1	2089.3	2109.5
42.5°	184.4	232.4	730.1	990.3	1614.4	1803.9	1826.6	1867.0	1985.7	2064.1	2086.9
45°	169.3	207.2	654.4	914.5	1556.3	1735.6	1768.5	1824.0	1950.3	2026.1	2046.4
47.5°	154.1	189.5	576.0	836.2	1493.1	1667.5	1710.4	1773.6	1902.3	1975.7	1993.4
50°	141.5	171.8	497.7	752.8	1424.9	1594.1	1644.7	1710.4	1841.7	1910.0	1932.6
52.5°	131.4	156.6	424.5	669.5	1346.5	1518.3	1576.4	1644.7	1768.5	1834.2	1849.3
55°	121.2	144.0	361.3	581.1	1265.7	1437.5	1500.6	1566.4	1687.6	1743.2	1753.3
57.5°	116.2	133.9	308.2	497.7	1179.8	1346.5	1417.3	1478.0	1591.6	1634.6	1644.7
60°	108.6	126.3	267.8	426.9	1086.4	1260.7	1321.3	1381.9	1478.0	1513.3	1520.9
62.5°	101.0	121.2	237.5	358.8	990.3	1159.6	1220.2	1275.9	1356.7	1381.9	1392.0
65°	96.0	116.2	214.7	308.2	891.9	1053.5	1114.1	1162.1	1227.8	1253.1	1258.2
67.5°	90.9	111.2	197.0	265.3	793.3	947.4	992.9	1038.3	1088.9	1114.1	1116.7
70°	83.4	106.1	181.9	235.0	692.2	826.2	864.0	912.0	952.5	965.1	972.6
72.5°	78.3	98.6	171.8	212.2	588.6	709.9	745.3	773.1	808.5	821.1	821.1
75°	70.7	88.4	161.7	189.5	482.6	581.1	611.4	639.2	667.0	672.1	664.4
77.5°	63.2	78.3	138.9	159.2	376.5	459.8	485.1	500.2	522.9	528.0	530.6
80°	53.1	68.3	108.6	123.8	272.8	338.5	356.2	368.8	389.1	389.1	394.2
82.5°	40.4	53.1	78.3	88.4	184.4	232.4	247.6	255.2	267.8	267.8	267.8
85°	25.2	32.9	50.6	58.1	111.2	141.5	151.6	154.1	164.2	166.7	166.7
87.5°	12.6	17.7	32.9	35.4	58.1	73.2	73.2	78.3	78.3	75.8	73.2
90°	5.9	10.7	15.5	16.6	26.1	38.7	45.0	40.1	30.0	22.6	22.6
92.5°	23.7	64.1	104.4	114.4	160.9	222.7	253.7	222.4	159.7	112.6	108.1
95°	56.9	130.7	204.4	222.8	395.7	626.2	741.5	661.6	502.0	382.3	368.7
97.5°	98.4	163.5	228.6	244.8	533.1	917.4	1109.5	1059.1	958.2	882.6	856.8
100°	130.4	189.4	248.5	263.2	583.1	1009.5	1222.7	1226.5	1233.8	1239.4	1208.6
102.5°	157.6	212.7	267.8	281.5	605.9	1038.5	1254.8	1319.0	1447.6	1544.0	1517.6
105°	203.9	250.6	297.1	308.8	622.9	1041.8	1251.2	1395.3	1683.4	1899.6	1885.4
107.5°	251.3	294.8	338.2	349.1	626.1	995.4	1180.1	1381.0	1783.0	2084.6	2088.0
110°	283.4	322.6	361.8	371.6	621.3	954.3	1120.8	1345.5	1794.9	2132.0	2146.7



TEST NUMBER: P937212

CATALOG NUMBER: SQ4-FB-075U-100D-830-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	314.7	352.1	389.5	398.8	621.5	918.4	1066.9	1296.9	1756.8	2101.8	2124.4
115°	362.1	396.6	431.2	439.8	627.2	877.2	1002.3	1223.8	1666.9	1999.2	2030.6
117.5°	409.0	440.3	471.7	479.5	639.0	851.5	957.8	1157.7	1557.6	1857.5	1892.3
120°	436.2	465.7	495.2	502.6	648.4	842.8	940.0	1122.7	1488.1	1762.1	1795.9
122.5°	462.9	492.7	522.5	529.9	662.0	838.2	926.4	1090.9	1419.9	1666.7	1700.1
125°	503.8	531.0	558.0	564.8	680.4	834.5	911.5	1051.3	1330.8	1540.4	1571.2
127.5°	537.0	564.4	591.8	598.6	698.8	832.4	899.1	1019.1	1259.1	1439.1	1465.0
130°	554.8	584.2	613.8	621.1	712.2	833.7	894.4	1001.2	1214.9	1375.1	1399.1
132.5°	573.1	602.7	632.2	639.6	723.1	834.5	890.2	985.8	1177.1	1320.5	1342.0
135°	600.4	627.2	654.2	660.9	735.0	833.7	883.2	963.3	1123.4	1243.5	1262.0
137.5°	628.3	654.9	681.4	688.1	752.8	838.9	881.9	949.6	1085.1	1186.6	1201.7
140°	651.4	675.9	700.4	706.5	763.6	839.8	877.8	936.3	1053.2	1141.0	1155.1
142.5°	669.2	691.9	714.5	720.2	772.7	842.8	877.8	929.1	1031.9	1109.0	1121.1
145°	696.4	716.2	735.9	740.9	784.6	842.8	871.9	913.9	998.0	1061.0	1070.1
147.5°	723.7	742.9	762.2	767.0	802.0	848.5	871.9	904.9	971.0	1020.6	1028.3
150°	741.5	758.9	776.3	780.6	811.0	851.6	871.9	899.8	955.6	997.5	1003.7
152.5°	759.8	773.0	786.2	789.5	816.9	853.5	871.9	895.7	943.4	979.1	983.8
155°	787.1	796.8	806.6	809.1	830.0	857.9	871.9	890.8	928.8	957.2	960.3
157.5°	807.2	816.7	826.2	828.6	843.0	862.2	871.9	886.6	916.1	938.2	940.4
160°	820.9	828.3	835.6	837.5	848.9	864.2	871.9	884.5	909.8	928.8	930.0
162.5°	834.5	840.0	845.6	847.0	855.3	866.3	871.9	882.6	903.9	919.9	921.0
165°	849.3	854.3	859.3	860.6	864.3	869.4	871.9	879.5	894.8	906.3	907.5
167.5°	863.0	865.4	867.8	868.3	871.5	875.7	877.8	882.8	892.8	900.4	900.8
170°	871.9	874.3	876.7	877.2	877.4	877.7	877.8	882.8	892.8	900.4	900.4
172.5°	876.7	877.1	877.7	877.8	877.8	877.8	877.8	881.7	889.7	895.6	895.1
175°	883.2	883.2	883.2	883.2	881.3	878.9	877.8	880.3	885.4	889.1	889.1
177.5°	883.2	883.2	883.2	883.2	881.7	879.9	878.9	881.0	884.9	887.8	887.4
180°	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2



TEST NUMBER: P937212

CATALOG NUMBER: SQ4-FB-075U-100D-830-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	785.7	785.7
2.5°	838.8	833.7
5°	1078.8	1083.8
7.5°	1452.6	1450.2
10°	1806.4	1829.1
12.5°	2064.1	2069.2
15°	2220.7	2230.8
17.5°	2281.3	2283.9
20°	2283.9	2278.8
22.5°	2256.1	2251.0
25°	2223.3	2220.7
27.5°	2192.9	2195.5
30°	2180.3	2187.9
32.5°	2180.3	2192.9
35°	2185.3	2197.9
37.5°	2182.8	2197.9
40°	2172.7	2190.4
42.5°	2144.9	2157.5
45°	2102.0	2117.2
47.5°	2046.4	2056.5
50°	1975.7	1985.7
52.5°	1887.2	1889.7
55°	1781.1	1791.3
57.5°	1667.5	1669.9
60°	1541.1	1548.7
62.5°	1407.2	1407.2
65°	1265.7	1270.8
67.5°	1119.2	1131.8
70°	970.1	972.6
72.5°	823.6	823.6
75°	672.1	674.6
77.5°	528.0	528.0
80°	391.6	394.2
82.5°	270.4	275.4
85°	169.3	169.3
87.5°	78.3	70.7
90°	22.6	22.6
92.5°	90.2	72.3
95°	314.5	260.2
97.5°	753.4	650.2
100°	1085.6	962.6
102.5°	1412.3	1306.9
105°	1828.7	1772.1
107.5°	2101.7	2115.3
110°	2205.8	2264.8



TEST NUMBER: P937212

CATALOG NUMBER: SQ4-FB-075U-100D-830-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	2215.0	2305.6
115°	2156.3	2281.9
117.5°	2031.7	2171.1
120°	1931.4	2066.8
122.5°	1833.6	1967.2
125°	1694.2	1817.3
127.5°	1568.8	1672.6
130°	1494.9	1590.8
132.5°	1427.9	1513.7
135°	1336.0	1410.0
137.5°	1262.3	1322.9
140°	1211.8	1268.4
142.5°	1169.9	1218.6
145°	1107.0	1143.9
147.5°	1058.8	1089.4
150°	1028.5	1053.2
152.5°	1002.5	1021.2
155°	972.7	985.1
157.5°	949.1	957.8
160°	935.1	940.0
162.5°	925.8	930.6
165°	912.5	917.5
167.5°	902.9	905.0
170°	900.4	900.4
172.5°	893.3	891.5
175°	889.1	889.1
177.5°	885.3	883.2
180°	883.2	883.2



TEST NUMBER: P937212
 CATALOG NUMBER: SQ4-FB-075U-100D-830-1D-UNV-STD-W-8

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.64	6.55	6.57	7.51	8.76	18.82	19.73	19.75	20.69	21.93
	3H	6.35	7.17	7.29	8.14	9.41	20.66	21.48	21.61	22.45	23.72
	4H	6.65	7.43	7.61	8.40	9.68	21.31	22.09	22.27	23.06	24.34
	6H	6.90	7.62	7.87	8.60	9.89	21.74	22.46	22.71	23.44	24.73
	8H	6.97	7.66	7.95	8.65	9.94	21.86	22.55	22.84	23.54	24.83
	12H	6.99	7.64	7.97	8.63	9.95	21.93	22.59	22.92	23.57	24.89
4H	2H	12.86	13.64	13.83	14.61	15.89	19.10	19.88	20.06	20.85	22.12
	3H	14.43	15.08	15.41	16.09	17.38	21.15	21.80	22.12	22.80	24.09
	4H	14.53	15.13	15.51	16.12	17.44	21.92	22.51	22.90	23.51	24.82
	6H	14.54	15.06	15.54	16.08	17.39	22.46	22.97	23.46	23.99	25.31
	8H	14.52	15.00	15.52	16.01	17.34	22.62	23.10	23.62	24.12	25.45
	12H	14.48	14.92	15.50	15.94	17.28	22.72	23.15	23.74	24.18	25.52
8H	4H	15.98	16.46	16.98	17.47	18.80	21.98	22.46	22.98	23.48	24.80
	6H	16.22	16.62	17.25	17.68	19.00	22.61	23.01	23.64	24.07	25.39
	8H	16.24	16.59	17.27	17.63	18.98	22.83	23.19	23.87	24.23	25.57
	12H	16.21	16.52	17.25	17.56	18.95	22.98	23.29	24.02	24.33	25.71
12H	4H	16.12	16.56	17.14	17.59	18.92	21.94	22.37	22.96	23.40	24.73
	6H	16.48	16.84	17.52	17.87	19.22	22.60	22.95	23.63	23.99	25.33
	8H	16.55	16.86	17.59	17.90	19.29	22.83	23.14	23.87	24.17	25.56