

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519620

Luminaire Tested: **SQ4-WB-150U-125D-830-1D-UNV-STD-W-4**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519620
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2009-966-13)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-150U-125D-830-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9562.4 lumens
Efficiency: N/A
Efficacy: 115.1 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 83.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519620
CATALOG NUMBER: SQ4-WB-150U-125D-830-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P519620

CATALOG NUMBER: SQ4-WB-150U-125D-830-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	47	47	47	41
1	97	93	89	86	88	85	82	79	70	68	66	56	55	53	43	43	42	36
2	89	82	76	72	81	75	70	66	62	59	56	50	48	46	39	38	37	32
3	82	73	66	61	74	67	61	57	56	52	48	45	43	40	36	34	32	28
4	75	65	58	52	68	60	54	49	50	46	42	41	38	35	33	31	29	25
5	69	59	51	46	63	54	48	43	45	41	37	37	34	31	30	28	26	22
6	64	53	45	40	59	49	42	38	41	36	33	34	31	28	28	25	23	20
7	59	48	41	35	54	45	38	33	38	33	29	31	28	25	25	23	21	18
8	55	44	37	32	51	41	34	30	35	30	26	29	25	23	24	21	19	17
9	52	40	33	28	47	37	31	27	32	27	24	27	23	21	22	19	18	15
10	48	37	30	26	44	34	28	24	30	25	22	25	21	19	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	24532	24532	24532
5°	24226	24140	24281
10°	22888	23096	23632
15°	21129	21620	22590
20°	19188	19910	21227
25°	17210	18149	19776
30°	15388	16395	18272
35°	13456	14429	16493
40°	11326	12226	14277
45°	9347	10154	11920
50°	7804	8507	9931
55°	6626	7301	8202
60°	5663	6329	6545
65°	4508	5322	4229
70°	3998	4154	2582
75°	3700	3369	1579
80°	3411	3098	1365
85°	3091	2837	1112



TEST NUMBER: P519620

CATALOG NUMBER: SQ4-WB-150U-125D-830-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	243.9	2.6
10°-20°	634.4	6.6
20°-30°	821.7	8.6
30°-40°	804.6	8.4
40°-50°	615.9	6.4
50°-60°	410.4	4.3
60°-70°	224.0	2.3
70°-80°	93.3	1.0
80°-90°	28.3	0.3
90°-100°	409.8	4.3
100°-110°	1108.2	11.6
110°-120°	1165.1	12.2
120°-130°	946.4	9.9
130°-140°	742.3	7.8
140°-150°	569.7	6.0
150°-160°	409.7	4.3
160°-170°	250.3	2.6
170°-180°	84.4	0.9
0°-30°	1700.0	17.8
0°-40°	2504.6	26.2
0°-60°	3530.9	36.9
0°-90°	3876.5	40.5
90°-120°	2683.1	28.1
90°-150°	4941.5	51.7
90°-180°	5686.0	59.5
0°-180°	9562.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2659	2659	2659	2659	2659	
5°	2616	2590	2606	2612	2622	243
15°	2212	2204	2264	2325	2365	618
25°	1691	1695	1783	1860	1943	777
35°	1195	1200	1281	1367	1464	743
45°	716	730	778	837	914	559
55°	412	429	454	471	510	373
65°	206	224	244	213	194	215
75°	104	104	94	65	44	111
85°	29	29	27	17	10	32
90°	2	6	12	13	12	6
95°	64	223	682	353	210	67
105°	206	318	1229	1813	1739	217
115°	363	443	1020	1974	2228	358
125°	496	569	919	1551	1822	443
135°	595	666	894	1252	1417	460
145°	692	744	882	1072	1153	433
155°	781	812	874	961	993	360
165°	851	859	878	912	917	240
175°	883	882	879	890	888	84
180°	882	882	882	882	882	



TEST NUMBER: P519620

CATALOG NUMBER: SQ4-WB-150U-125D-830-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2659.0	2659.0	2659.0	2659.0	2659.0
2.5°	2665.5	2641.8	2647.8	2647.6	2640.3
5°	2615.8	2589.6	2606.5	2612.5	2621.7
7.5°	2518.7	2498.9	2529.7	2552.5	2571.0
10°	2443.1	2426.0	2465.3	2498.5	2522.5
12.5°	2355.4	2341.0	2389.7	2434.3	2465.5
15°	2212.1	2204.1	2263.5	2325.0	2365.0
17.5°	2058.8	2054.9	2123.0	2194.9	2246.0
20°	1954.3	1953.1	2027.8	2102.6	2162.0
22.5°	1848.8	1851.3	1929.8	2007.6	2075.2
25°	1690.6	1695.2	1782.8	1860.5	1942.6
27.5°	1544.3	1546.3	1636.9	1719.0	1806.6
30°	1444.4	1450.1	1538.9	1623.8	1715.1
32.5°	1344.5	1351.2	1438.1	1525.9	1619.0
35°	1194.7	1200.4	1281.1	1367.3	1464.3
37.5°	1040.3	1048.0	1119.6	1201.1	1296.5
40°	940.4	951.8	1015.1	1091.9	1185.4
42.5°	844.2	858.4	917.1	989.9	1074.3
45°	716.4	730.1	778.2	837.1	913.6
47.5°	606.2	622.0	659.0	709.7	774.9
50°	543.7	558.5	592.7	630.3	691.9
52.5°	488.6	503.5	533.9	562.9	615.3
55°	411.9	429.0	453.9	471.1	509.9
57.5°	348.9	365.3	385.0	392.8	416.3
60°	306.9	325.1	343.0	342.1	354.7
62.5°	268.6	284.1	302.0	289.6	290.3
65°	206.5	223.6	243.8	213.1	193.7
67.5°	166.8	170.5	191.3	148.6	125.5
70°	148.2	148.2	154.0	115.1	95.7
72.5°	130.4	130.4	125.1	93.6	73.3
75°	103.8	103.8	94.5	64.9	44.3
77.5°	80.0	79.1	72.3	48.4	32.2
80°	64.2	64.2	58.3	38.2	25.7
82.5°	50.2	50.2	45.3	29.9	19.1
85°	29.2	29.2	26.8	17.3	10.5
87.5°	10.6	11.4	11.8	8.2	7.1
90°	1.9	5.6	12.3	13.3	12.3
92.5°	27.0	98.2	193.8	84.2	60.9
95°	63.6	223.3	681.6	352.7	209.8
97.5°	102.1	256.0	1062.5	879.3	645.7
100°	131.0	269.3	1180.9	1231.6	995.8
102.5°	157.6	287.7	1222.7	1498.7	1322.4
105°	206.0	318.3	1229.3	1813.4	1739.1
107.5°	250.8	353.3	1175.6	2009.7	2034.4
110°	285.7	378.6	1127.8	2062.4	2167.3



TEST NUMBER: P519620

CATALOG NUMBER: SQ4-WB-150U-125D-830-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	316.9	403.8	1083.7	2051.8	2228.0
115°	362.6	443.4	1019.6	1973.7	2228.0
117.5°	407.4	483.2	977.2	1854.3	2142.6
120°	434.8	509.0	952.2	1768.6	2062.8
122.5°	460.6	533.4	937.0	1676.8	1973.2
125°	496.5	568.9	918.9	1550.7	1821.7
127.5°	529.5	600.6	908.3	1447.8	1686.2
130°	547.7	621.1	903.7	1384.2	1599.6
132.5°	566.7	639.3	899.2	1326.9	1525.2
135°	595.2	665.8	894.2	1252.1	1417.3
137.5°	623.9	690.5	890.1	1191.4	1326.0
140°	643.6	705.8	888.5	1152.3	1272.1
142.5°	662.6	721.1	885.5	1117.1	1221.9
145°	692.0	744.0	881.9	1071.7	1153.4
147.5°	718.8	764.9	877.7	1030.7	1093.4
150°	738.6	779.4	876.2	1008.4	1058.5
152.5°	756.8	792.4	875.4	987.6	1028.9
155°	781.3	811.9	874.3	961.4	993.0
157.5°	806.7	828.1	874.5	943.1	963.9
160°	821.1	838.8	875.3	931.6	946.5
162.5°	832.5	847.2	876.0	922.4	933.5
165°	850.6	858.9	878.1	912.4	917.0
167.5°	862.9	868.7	878.3	903.8	906.0
170°	870.5	873.3	879.1	899.9	899.9
172.5°	876.6	877.1	879.1	895.4	894.6
175°	882.9	881.9	879.1	890.4	888.5
177.5°	884.9	882.7	878.9	886.4	884.2
180°	881.9	881.9	881.9	881.9	881.9

(END OF REPORT)