

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562868

Luminaire Tested: **SQ4-PC3-0U-125D-830-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562868
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-0U-125D-830-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9284.5 lumens
Efficiency: N/A
Efficacy: 101.9 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Direct

Input Watts (W): 91.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562868
CATALOG NUMBER: SQ4-PC3-0U-125D-830-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P562868

CATALOG NUMBER: SQ4-PC3-0U-125D-830-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100													100															
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	88	87	85													85															
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73	71													71															
3	91	80	72	66	88	79	71	65	76	70	64	73	68	63	71	66	62	60													60															
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	53	51													51															
5	77	64	55	48	74	63	54	48	61	53	48	59	52	47	57	51	47	44													44															
6	71	58	49	42	69	57	48	42	55	47	42	53	46	41	52	46	41	39													39															
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	34													34															
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	31													31															
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	29	28													28															
10	54	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	27	25													25															

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15693	15693	15693
5°	15812	15710	15651
10°	15773	15699	15655
15°	15691	15691	15675
20°	15587	15634	15634
25°	15440	15552	15504
30°	15252	15436	15369
35°	15025	15255	15149
40°	14777	14985	14833
45°	14508	14611	14385
50°	14129	14129	13903
55°	13681	13503	13300
60°	13020	12758	12555
65°	12034	11793	11691
70°	10537	10622	10578
75°	8477	9375	9432
80°	6025	7948	8033
85°	3668	6669	6669



TEST NUMBER: P562868

CATALOG NUMBER: SQ4-PC3-0U-125D-830-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	322.0	3.5
10°-20°	923.9	10.0
20°-30°	1399.2	15.1
30°-40°	1677.4	18.1
40°-50°	1710.4	18.4
50°-60°	1493.0	16.1
60°-70°	1068.9	11.5
70°-80°	550.5	5.9
80°-90°	139.2	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2645.0	28.5
0°-40°	4322.4	46.6
0°-60°	7525.8	81.1
0°-90°	9284.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9284.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3402	3402	3402	3402	3402	
5°	3414	3381	3392	3383	3380	324
15°	3285	3258	3285	3285	3282	926
25°	3033	3012	3055	3046	3046	1396
35°	2668	2662	2709	2690	2690	1669
45°	2224	2218	2240	2211	2205	1712
55°	1701	1679	1679	1654	1654	1516
65°	1102	1078	1080	1071	1071	1090
75°	476	497	526	529	529	514
85°	69	106	126	129	126	97
90°	0	0	0	0	0	



TEST NUMBER: P562868

CATALOG NUMBER: SQ4-PC3-0U-125D-830-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3401.9	3401.9	3401.9	3401.9	3401.9
2.5°	3422.1	3392.5	3401.9	3394.1	3381.7
5°	3414.5	3380.6	3392.5	3382.9	3379.9
7.5°	3389.9	3356.1	3371.7	3365.3	3362.2
10°	3367.3	3333.4	3351.5	3345.1	3342.1
12.5°	3337.0	3305.6	3326.3	3320.0	3319.4
15°	3285.4	3257.6	3285.4	3285.3	3282.2
17.5°	3220.5	3195.2	3224.9	3226.7	3224.9
20°	3175.1	3147.4	3184.6	3181.5	3184.6
22.5°	3119.7	3096.9	3136.7	3128.6	3131.6
25°	3033.4	3011.8	3055.4	3046.0	3046.0
27.5°	2931.3	2915.9	2963.4	2953.4	2953.4
30°	2863.3	2847.9	2897.9	2885.3	2885.3
32.5°	2787.7	2777.2	2824.8	2809.7	2809.7
35°	2668.0	2661.8	2708.9	2690.0	2690.0
37.5°	2544.5	2539.0	2581.7	2558.8	2551.4
40°	2453.8	2450.7	2488.4	2463.2	2463.2
42.5°	2363.1	2360.0	2392.7	2362.4	2362.4
45°	2223.8	2217.7	2239.6	2211.1	2204.9
47.5°	2072.0	2065.9	2079.6	2048.6	2045.6
50°	1968.7	1962.5	1968.7	1940.3	1937.2
52.5°	1862.9	1851.8	1852.8	1824.4	1823.8
55°	1701.0	1679.4	1678.9	1653.7	1653.7
57.5°	1529.6	1501.3	1503.8	1482.3	1479.2
60°	1411.2	1380.4	1382.8	1363.8	1360.8
62.5°	1295.2	1259.5	1266.9	1245.5	1244.8
65°	1102.5	1077.8	1080.4	1071.0	1071.0
67.5°	917.3	894.5	911.0	903.4	902.8
70°	781.2	765.8	787.5	787.4	784.3
72.5°	655.2	654.6	681.6	681.7	683.5
75°	475.6	497.2	526.0	529.2	529.2
77.5°	317.5	355.7	387.4	388.7	388.1
80°	226.8	269.9	299.2	305.5	302.4
82.5°	153.7	199.3	223.6	229.9	226.8
85°	69.3	106.3	126.0	129.1	126.0
87.5°	20.2	42.3	50.4	50.3	45.4
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)