

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563516

Luminaire Tested: **SQ4-PP3-0U-100D-830-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563516
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-0U-100D-830-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7206.6 lumens
Efficiency: N/A
Efficacy: 100.5 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Direct

Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563516
CATALOG NUMBER: SQ4-PP3-0U-100D-830-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P563516

CATALOG NUMBER: SQ4-PP3-OU-100D-830-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100	
1	109	105	101	97	107	103	99	96	98	95	93	95	92	90	91	89	87	85			85	
2	100	92	86	80	97	90	84	79	87	82	77	84	79	76	81	77	74	72			72	
3	92	81	74	67	89	80	73	67	77	71	66	74	69	64	72	67	63	61			61	
4	84	72	64	57	82	71	63	57	69	62	56	66	60	56	64	59	55	53			53	
5	77	65	56	50	75	64	56	49	62	54	49	60	53	48	58	52	48	46			46	
6	72	59	50	44	70	58	49	43	56	49	43	54	48	43	53	47	42	40			40	
7	66	53	45	39	65	52	44	39	51	44	38	49	43	38	48	42	38	36			36	
8	62	49	40	35	60	48	40	34	47	39	34	45	39	34	44	38	34	32			32	
9	58	45	37	31	56	44	36	31	43	36	31	42	35	31	41	35	31	29			29	
10	54	41	34	28	53	41	33	28	40	33	28	39	33	28	38	32	28	26			26	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12989	12989	12989
5°	13085	13004	12959
10°	13062	12970	12912
15°	12976	12905	12835
20°	12890	12817	12720
25°	12737	12649	12523
30°	12501	12435	12278
35°	12174	12090	11938
40°	11784	11710	11577
45°	11463	11382	11269
50°	11051	10980	10874
55°	10480	10340	10261
60°	9540	9267	9221
65°	8404	8055	8027
70°	7256	6957	6957
75°	6245	6158	6069
80°	5507	5574	5441
85°	4308	4700	4700



TEST NUMBER: P563516

CATALOG NUMBER: SQ4-PP3-OU-100D-830-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	266.3	3.7
10°-20°	760.2	10.5
20°-30°	1138.7	15.8
30°-40°	1335.7	18.5
40°-50°	1339.8	18.6
50°-60°	1143.0	15.9
60°-70°	745.4	10.3
70°-80°	374.0	5.2
80°-90°	103.5	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2165.2	30.0
0°-40°	3500.9	48.6
0°-60°	5983.7	83.0
0°-90°	7206.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7206.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2816	2816	2816	2816	2816	
5°	2826	2799	2808	2798	2798	268
15°	2717	2690	2702	2692	2687	767
25°	2502	2473	2485	2463	2460	1151
35°	2162	2140	2147	2122	2120	1350
45°	1757	1745	1745	1727	1727	1353
55°	1303	1298	1286	1278	1276	1158
65°	770	756	738	733	735	768
75°	350	350	346	343	340	380
85°	81	89	89	89	89	99
90°	0	0	0	0	0	



TEST NUMBER: P563516

CATALOG NUMBER: SQ4-PP3-OU-100D-830-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2815.7	2815.7	2815.7	2815.7	2815.7
2.5°	2833.5	2810.3	2815.7	2811.5	2799.9
5°	2825.6	2799.0	2808.3	2798.4	2798.4
7.5°	2806.3	2777.4	2786.6	2776.7	2776.2
10°	2788.5	2759.6	2768.8	2758.9	2756.5
12.5°	2762.9	2733.9	2745.1	2733.3	2732.8
15°	2717.0	2690.4	2702.2	2692.2	2687.4
17.5°	2665.2	2636.2	2650.4	2636.5	2634.6
20°	2625.7	2596.7	2610.9	2591.1	2591.1
22.5°	2578.3	2549.3	2565.5	2539.8	2539.8
25°	2502.3	2473.3	2485.0	2462.8	2460.3
27.5°	2412.0	2383.5	2395.7	2370.5	2370.0
30°	2346.8	2320.3	2334.5	2307.3	2304.9
32.5°	2275.8	2251.1	2261.4	2234.2	2231.8
35°	2161.7	2140.0	2146.9	2122.2	2119.8
37.5°	2041.8	2019.6	2027.5	2006.3	2005.3
40°	1956.9	1942.4	1944.6	1927.2	1922.4
42.5°	1878.0	1861.5	1863.6	1846.3	1845.4
45°	1757.0	1745.0	1744.7	1727.4	1727.4
47.5°	1628.7	1619.5	1616.9	1602.5	1602.1
50°	1539.9	1532.6	1530.0	1517.6	1515.2
52.5°	1447.1	1443.7	1435.2	1424.9	1424.4
55°	1303.0	1298.1	1285.7	1278.2	1275.8
57.5°	1146.5	1136.9	1122.8	1112.0	1113.9
60°	1034.0	1024.3	1004.4	999.4	999.4
62.5°	925.4	913.8	893.8	887.0	890.9
65°	769.9	755.5	737.9	733.0	735.4
67.5°	628.8	615.8	596.7	596.7	594.7
70°	538.0	530.7	515.8	515.8	515.8
72.5°	457.0	453.6	442.7	442.7	440.7
75°	350.4	350.4	345.5	343.0	340.5
77.5°	262.6	263.5	261.1	258.5	254.2
80°	207.3	212.1	209.8	207.2	204.8
82.5°	156.0	160.8	160.4	156.0	155.5
85°	81.4	88.7	88.8	88.8	88.8
87.5°	21.7	29.4	31.6	31.6	33.6
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)