

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P563780

Luminaire Tested: **SQ4-PP3-150U-075D-830-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563780
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-150U-075D-830-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 16799.4 lumens
Efficiency: N/A
Efficacy: 128.1 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 131.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563780
CATALOG NUMBER: SQ4-PP3-150U-075D-830-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P563780

CATALOG NUMBER: SQ4-PP3-150U-075D-830-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	32
1	94	90	86	83	84	81	78	75	65	62	60	49	48	47	35	35	34	27
2	86	79	73	68	77	71	66	62	57	53	50	43	41	39	31	30	29	23
3	78	69	62	56	70	62	56	52	50	46	42	38	36	33	28	26	25	20
4	71	61	53	48	64	55	49	44	44	40	36	34	31	28	25	23	21	17
5	65	54	46	41	59	49	42	37	40	35	31	31	27	25	22	20	18	15
6	60	49	41	35	54	44	37	32	36	31	27	28	24	21	20	18	16	13
7	56	44	36	31	50	40	33	28	32	27	24	25	22	19	19	16	14	12
8	51	40	32	27	46	36	29	25	29	24	21	23	19	17	17	15	13	10
9	48	36	29	24	43	33	26	22	27	22	19	21	18	15	16	13	12	9
10	45	33	26	21	40	30	24	20	25	20	17	19	16	14	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9776	9776	9776
5°	9848	9787	9753
10°	9831	9761	9718
15°	9766	9713	9660
20°	9701	9646	9573
25°	9586	9520	9425
30°	9409	9359	9240
35°	9163	9099	8985
40°	8869	8813	8713
45°	8627	8567	8482
50°	8317	8264	8184
55°	7887	7782	7723
60°	7180	6974	6940
65°	6326	6061	6042
70°	5461	5236	5236
75°	4700	4634	4568
80°	4144	4195	4096
85°	3245	3541	3541



TEST NUMBER: P563780

CATALOG NUMBER: SQ4-PP3-150U-075D-830-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	200.4	1.2
10°-20°	572.2	3.4
20°-30°	857.0	5.1
30°-40°	1005.2	6.0
40°-50°	1008.4	6.0
50°-60°	860.2	5.1
60°-70°	561.0	3.3
70°-80°	281.5	1.7
80°-90°	81.6	0.5
90°-100°	819.7	4.9
100°-110°	2216.3	13.2
110°-120°	2330.1	13.9
120°-130°	1892.7	11.3
130°-140°	1484.7	8.8
140°-150°	1139.5	6.8
150°-160°	819.5	4.9
160°-170°	500.6	3.0
170°-180°	168.8	1.0
0°-30°	1629.6	9.7
0°-40°	2634.8	15.7
0°-60°	4503.4	26.8
0°-90°	5427.5	32.3
90°-120°	5366.2	31.9
90°-150°	9883.0	58.8
90°-180°	11372.0	67.7
0°-180°	16799.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2119	2119	2119	2119	2119	
5°	2127	2107	2114	2106	2106	202
15°	2045	2025	2034	2026	2023	577
25°	1883	1862	1870	1854	1852	866
35°	1627	1611	1616	1597	1595	1016
45°	1322	1313	1313	1300	1300	1018
55°	981	977	968	962	960	871
65°	580	569	555	552	554	578
75°	264	264	260	258	256	286
85°	61	67	67	67	67	72
90°	4	11	25	26	25	11
95°	127	446	1363	706	420	133
105°	412	637	2459	3627	3478	434
115°	725	887	2039	3947	4456	716
125°	993	1138	1838	3101	3643	885
135°	1190	1332	1788	2504	2835	920
145°	1384	1488	1764	2143	2307	866
155°	1563	1624	1749	1923	1986	721
165°	1701	1718	1756	1825	1834	479
175°	1766	1764	1758	1781	1777	168
180°	1764	1764	1764	1764	1764	



TEST NUMBER: P563780

CATALOG NUMBER: SQ4-PP3-150U-075D-830-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2119.1	2119.1	2119.1	2119.1	2119.1
2.5°	2132.5	2115.1	2119.1	2116.0	2107.2
5°	2126.6	2106.6	2113.6	2106.1	2106.1
7.5°	2112.1	2090.3	2097.2	2089.8	2089.4
10°	2098.7	2076.9	2083.8	2076.4	2074.6
12.5°	2079.4	2057.6	2066.0	2057.1	2056.7
15°	2044.8	2024.9	2033.7	2026.2	2022.6
17.5°	2005.8	1984.0	1994.7	1984.3	1982.8
20°	1976.1	1954.3	1965.0	1950.1	1950.1
22.5°	1940.5	1918.7	1930.8	1911.5	1911.5
25°	1883.3	1861.5	1870.3	1853.5	1851.7
27.5°	1815.3	1793.9	1803.0	1784.1	1783.7
30°	1766.3	1746.3	1757.0	1736.5	1734.7
32.5°	1712.8	1694.2	1702.0	1681.5	1679.7
35°	1627.0	1610.6	1615.8	1597.2	1595.4
37.5°	1536.7	1520.0	1525.9	1509.9	1509.2
40°	1472.8	1461.9	1463.5	1450.4	1446.8
42.5°	1413.4	1401.0	1402.6	1389.6	1388.9
45°	1322.4	1313.3	1313.1	1300.1	1300.1
47.5°	1225.8	1218.9	1216.9	1206.1	1205.7
50°	1158.9	1153.5	1151.5	1142.2	1140.4
52.5°	1089.1	1086.6	1080.2	1072.4	1072.0
55°	980.6	977.0	967.6	962.0	960.2
57.5°	862.9	855.6	845.1	836.9	838.4
60°	778.2	770.9	755.9	752.2	752.2
62.5°	696.5	687.8	672.7	667.6	670.5
65°	579.5	568.6	555.3	551.6	553.5
67.5°	473.2	463.4	449.1	449.1	447.6
70°	404.9	399.4	388.2	388.2	388.2
72.5°	344.0	341.4	333.2	333.2	331.7
75°	263.7	263.7	260.0	258.1	256.3
77.5°	197.6	198.3	196.5	194.6	191.3
80°	156.0	159.6	157.9	156.0	154.2
82.5°	117.4	121.0	120.7	117.4	117.0
85°	61.3	66.7	66.9	66.9	66.9
87.5°	17.1	24.4	28.7	29.1	30.2
90°	3.8	11.2	24.7	26.5	24.7
92.5°	53.9	196.5	387.7	168.3	121.9
95°	127.2	446.5	1363.2	705.5	419.6
97.5°	204.3	512.1	2124.9	1758.5	1291.4
100°	262.0	538.6	2361.9	2463.2	1991.6
102.5°	315.2	575.4	2445.4	2997.5	2644.8
105°	412.0	636.6	2458.7	3626.8	3478.3
107.5°	501.6	706.6	2351.2	4019.3	4068.7
110°	571.5	757.1	2255.5	4124.7	4334.5



TEST NUMBER: P563780

CATALOG NUMBER: SQ4-PP3-150U-075D-830-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	633.8	807.5	2167.5	4103.7	4456.0
115°	725.3	886.8	2039.1	3947.4	4456.0
117.5°	814.9	966.4	1954.4	3708.6	4285.2
120°	869.6	1018.1	1904.3	3537.2	4125.7
122.5°	921.2	1066.7	1873.9	3353.5	3946.4
125°	993.0	1137.8	1837.9	3101.4	3643.4
127.5°	1059.0	1201.2	1816.6	2895.6	3372.3
130°	1095.5	1242.2	1807.5	2768.5	3199.2
132.5°	1133.5	1278.6	1798.4	2653.8	3050.3
135°	1190.4	1331.5	1788.5	2504.2	2834.6
137.5°	1247.8	1381.1	1780.1	2382.8	2652.0
140°	1287.3	1411.6	1777.1	2304.7	2544.1
142.5°	1325.2	1442.2	1771.0	2234.1	2443.9
145°	1384.1	1488.0	1763.8	2143.4	2306.8
147.5°	1437.6	1529.7	1755.5	2061.3	2186.8
150°	1477.1	1558.8	1752.4	2016.7	2116.9
152.5°	1513.6	1584.9	1750.9	1975.3	2057.7
155°	1562.6	1623.8	1748.6	1922.8	1985.9
157.5°	1613.4	1656.1	1749.0	1886.3	1927.8
160°	1642.3	1677.6	1750.5	1863.2	1892.9
162.5°	1665.1	1694.4	1752.0	1844.8	1867.1
165°	1701.2	1717.9	1756.2	1824.8	1834.1
167.5°	1725.8	1737.3	1756.6	1807.6	1812.0
170°	1741.0	1746.6	1758.1	1799.9	1799.9
172.5°	1753.2	1754.3	1758.1	1790.7	1789.2
175°	1765.7	1763.9	1758.1	1780.8	1777.1
177.5°	1769.9	1765.4	1757.7	1772.8	1768.4
180°	1763.8	1763.8	1763.8	1763.8	1763.8

(END OF REPORT)