

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P938111

Luminaire Tested: SQ4-FB-125U-125D-830-1D-UNV-STD-W-6

Issue Date: 12/17/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P938111  
REPORT IS A COMBINATION OF REPORTS P933608 AND P933786  
Test Lab: INNOVATION CENTER  
Issue Date: 12/17/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ4-FB-125U-125D-830-1D-UNV-STD-W-6  
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 13014.0 lumens  
Efficiency: N/A  
Efficacy: 115.4 lumens/watt  
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33  
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 112.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P938111  
CATALOG NUMBER: SQ4-FB-125U-125D-830-1D-UNV-STD-W-6

### Luminous Intensity Polar Plot





TEST NUMBER: P938111

CATALOG NUMBER: SQ4-FB-125U-125D-830-1D-UNV-STD-W-6

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45	45	45	45
1	96	92	88	84	88	84	81	77	70	67	65	57	55	53	45	44	42	37	37	37	37
2	87	79	73	68	79	73	67	63	61	56	53	49	46	44	39	37	35	30	30	30	30
3	79	69	62	56	72	64	57	52	53	48	44	43	39	36	34	31	29	25	25	25	25
4	72	61	53	47	66	56	49	43	47	41	37	38	34	31	30	27	25	21	21	21	21
5	66	54	46	39	60	50	42	37	41	36	31	34	29	26	27	23	21	18	18	18	18
6	60	48	40	34	55	44	37	31	37	31	27	30	26	23	24	21	18	15	15	15	15
7	56	43	35	29	51	40	32	27	33	28	23	27	23	20	22	18	16	13	13	13	13
8	52	39	31	26	47	36	29	24	30	25	21	25	20	17	20	16	14	12	12	12	12
9	48	35	28	23	44	33	26	21	27	22	18	23	18	15	18	15	12	10	10	10	10
10	45	32	25	20	41	30	23	19	25	20	16	21	17	14	17	13	11	9	9	9	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4669	4669	4669
5°	4559	5394	6276
10°	4134	7862	10404
15°	3512	10269	12563
20°	2858	11897	12803
25°	2383	12447	12542
30°	2009	12522	12519
35°	1776	12311	12843
40°	1547	12037	13177
45°	1399	11835	13229
50°	1281	11654	13010
55°	1226	11389	12433
60°	1254	10884	11522
65°	1304	10118	10271
70°	1385	8818	8678
75°	1530	7184	6771
80°	1660	4977	4563
85°	1449	2635	2336

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 45°  
 Luminance: 13229 cd/sqm



TEST NUMBER: P938111

CATALOG NUMBER: SQ4-FB-125U-125D-830-1D-UNV-STD-W-6

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	97.6	0.8
10°-20°	432.7	3.3
20°-30°	756.8	5.8
30°-40°	974.2	7.5
40°-50°	1088.2	8.4
50°-60°	1042.2	8.0
60°-70°	826.0	6.3
70°-80°	485.7	3.7
80°-90°	139.1	1.1
90°-100°	539.3	4.1
100°-110°	1417.7	10.9
110°-120°	1470.0	11.3
120°-130°	1179.1	9.1
130°-140°	925.2	7.1
140°-150°	710.1	5.5
150°-160°	511.4	3.9
160°-170°	312.9	2.4
170°-180°	105.7	0.8
0°-30°	1287.1	9.9
0°-40°	2261.3	17.4
0°-60°	4391.7	33.7
0°-90°	5842.5	44.9
90°-120°	3427.0	26.3
90°-150°	6241.4	48.0
90°-180°	7171.0	55.1
0°-180°	13014.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	755	755	755	755	755	
5°	735	789	888	1005	1041	68
15°	551	1017	1713	2077	2143	153
25°	352	1153	2041	2131	2133	162
35°	238	1102	1922	2031	2111	149
45°	163	878	1699	1946	2034	126
55°	116	558	1442	1674	1720	106
65°	92	296	1070	1204	1221	91
75°	68	182	587	646	648	71
85°	24	56	146	160	163	26
90°	8	21	56	28	28	8
95°	71	279	929	479	326	79
105°	255	387	1567	2380	2220	271
115°	454	551	1256	2504	2858	448
125°	631	708	1142	1930	2276	560
135°	752	828	1106	1558	1766	582
145°	872	928	1092	1329	1433	547
155°	986	1014	1092	1199	1234	453
165°	1064	1078	1092	1135	1149	300
175°	1106	1106	1100	1114	1114	105
180°	1106	1106	1106	1106	1106	



TEST NUMBER: P938111

CATALOG NUMBER: SQ4-FB-125U-125D-830-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	754.7	754.7	754.7	754.7	754.7	754.7	754.7	754.7	754.7	754.7	754.7
2.5°	754.7	754.7	759.5	761.9	766.8	769.3	774.1	778.9	793.5	796.0	800.8
5°	735.3	745.0	776.6	788.7	822.6	868.7	888.1	919.7	985.3	1004.7	1016.8
7.5°	706.2	728.0	805.6	825.0	910.0	1031.3	1082.3	1150.3	1254.6	1305.5	1346.8
10°	660.0	706.2	844.4	890.6	1028.9	1213.4	1308.0	1402.6	1560.4	1630.7	1657.4
12.5°	609.1	684.3	885.7	948.8	1147.8	1417.2	1531.2	1635.5	1815.2	1909.8	1924.3
15°	550.8	652.8	924.5	1016.8	1274.0	1587.1	1713.2	1841.8	2009.3	2077.2	2094.2
17.5°	499.9	628.5	961.0	1058.0	1371.1	1739.9	1868.5	1975.3	2111.2	2157.3	2169.5
20°	436.8	589.7	985.3	1111.4	1473.0	1851.6	1975.3	2057.8	2150.0	2179.1	2184.0
22.5°	390.7	548.5	999.8	1130.9	1541.0	1919.5	2023.9	2089.3	2152.4	2162.2	2164.6
25°	351.9	502.3	997.4	1152.6	1599.2	1960.8	2040.9	2089.3	2125.8	2130.6	2130.6
27.5°	315.5	451.3	987.6	1157.5	1642.9	1970.4	2033.5	2067.5	2084.5	2094.2	2094.2
30°	283.9	402.9	963.4	1147.8	1662.3	1960.8	2011.7	2028.7	2045.6	2060.3	2067.5
32.5°	259.6	356.7	926.9	1128.4	1664.7	1936.5	1972.9	1982.6	2006.8	2040.9	2052.9
35°	237.9	310.6	885.7	1101.7	1650.2	1897.7	1921.9	1931.6	1980.2	2031.1	2048.1
37.5°	216.0	276.7	832.4	1055.6	1628.3	1851.6	1868.5	1885.5	1960.8	2021.4	2040.9
40°	194.2	247.5	769.3	1004.7	1594.3	1795.8	1810.3	1837.0	1936.5	2006.8	2026.2
42.5°	177.1	223.2	701.3	951.2	1550.6	1732.7	1754.5	1793.3	1907.3	1982.6	2004.4
45°	162.6	198.9	628.5	878.5	1494.8	1667.1	1698.6	1752.1	1873.4	1946.2	1965.6
47.5°	148.0	182.0	553.2	803.2	1434.2	1601.6	1642.9	1703.5	1827.3	1897.7	1914.7
50°	135.8	165.0	478.1	723.1	1368.6	1531.2	1579.8	1642.9	1769.1	1834.6	1856.4
52.5°	126.2	150.5	407.6	643.1	1293.4	1458.4	1514.2	1579.8	1698.6	1761.7	1776.3
55°	116.4	138.3	347.0	558.1	1215.7	1380.8	1441.5	1504.6	1621.0	1674.4	1684.1
57.5°	111.7	128.6	296.1	478.1	1133.2	1293.4	1361.3	1419.6	1528.8	1570.0	1579.8
60°	104.3	121.3	257.3	410.1	1043.5	1210.9	1269.2	1327.4	1419.6	1453.6	1460.9
62.5°	97.0	116.4	228.1	344.5	951.2	1113.8	1172.1	1225.5	1303.1	1327.4	1337.1
65°	92.3	111.7	206.3	296.1	856.6	1011.9	1070.1	1116.2	1179.3	1203.6	1208.5
67.5°	87.4	106.8	189.3	254.8	761.9	910.0	953.7	997.4	1045.9	1070.1	1072.6
70°	80.1	101.9	174.8	225.7	664.9	793.5	829.9	876.0	914.9	926.9	934.3
72.5°	75.2	94.6	165.0	203.8	565.4	681.9	715.9	742.5	776.6	788.7	788.7
75°	68.0	84.9	155.4	182.0	463.5	558.1	587.3	613.9	640.6	645.5	638.2
77.5°	60.7	75.2	133.5	152.9	361.6	441.7	466.0	480.5	502.3	507.2	509.6
80°	51.0	65.5	104.3	118.9	262.0	325.1	342.2	354.3	373.7	373.7	378.6
82.5°	38.8	51.0	75.2	84.9	177.1	223.2	237.9	245.1	257.3	257.3	257.3
85°	24.3	31.5	48.6	55.8	106.8	135.8	145.6	148.0	157.7	160.1	160.1
87.5°	12.1	17.0	31.5	33.9	55.8	70.4	70.4	75.2	75.2	72.8	70.4
90°	7.5	13.4	19.3	20.7	32.6	48.5	56.4	50.1	37.6	28.2	28.2
92.5°	29.7	80.2	130.7	143.3	201.4	279.0	317.8	278.5	200.0	141.1	135.5
95°	71.3	163.7	256.0	279.2	495.7	784.5	928.8	828.9	628.9	478.9	461.8
97.5°	123.2	204.7	286.2	306.6	667.7	1149.2	1389.9	1326.7	1200.4	1105.5	1073.2
100°	163.4	237.3	311.2	329.6	730.3	1264.6	1531.7	1536.3	1545.6	1552.4	1513.9
102.5°	197.5	266.4	335.5	352.7	759.1	1300.8	1571.8	1652.3	1813.3	1934.1	1901.1
105°	255.4	313.9	372.2	386.8	780.3	1305.0	1567.4	1747.9	2108.8	2379.6	2361.8
107.5°	314.8	369.2	423.7	437.3	784.3	1246.9	1478.3	1730.1	2233.6	2611.2	2615.5
110°	354.9	404.0	453.1	465.5	778.3	1195.4	1404.0	1685.4	2248.4	2670.7	2689.1



TEST NUMBER: P938111

CATALOG NUMBER: SQ4-FB-125U-125D-830-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	394.3	441.1	487.9	499.7	778.6	1150.5	1336.4	1624.4	2200.6	2632.7	2661.1
115°	453.6	496.8	540.1	550.9	785.8	1098.9	1255.5	1533.0	2088.1	2504.3	2543.7
117.5°	512.3	551.6	590.8	600.7	800.4	1066.6	1199.8	1450.3	1951.2	2326.9	2370.5
120°	546.4	583.4	620.3	629.6	812.2	1055.7	1177.5	1406.4	1864.0	2207.3	2249.8
122.5°	579.9	617.2	654.5	663.8	829.3	1050.1	1160.5	1366.6	1778.7	2087.8	2129.6
125°	631.1	665.1	699.0	707.5	852.4	1045.4	1141.9	1317.0	1667.1	1929.7	1968.2
127.5°	672.6	707.0	741.3	749.9	875.4	1042.7	1126.4	1276.6	1577.3	1802.7	1835.2
130°	694.9	731.9	768.8	778.1	892.1	1044.2	1120.3	1254.2	1521.8	1722.5	1752.5
132.5°	718.0	755.0	791.9	801.1	905.8	1045.4	1115.2	1235.0	1474.5	1654.2	1681.0
135°	752.1	785.7	819.4	827.8	920.6	1044.4	1106.3	1206.6	1407.2	1557.7	1580.8
137.5°	787.0	820.3	853.7	862.0	942.9	1050.8	1104.8	1189.6	1359.1	1486.4	1505.3
140°	815.9	846.6	877.3	885.0	956.5	1051.9	1099.6	1172.8	1319.4	1429.2	1447.0
142.5°	838.2	866.6	895.0	902.1	968.0	1055.7	1099.6	1163.9	1292.6	1389.2	1404.5
145°	872.4	897.1	921.9	928.1	982.8	1055.7	1092.1	1144.8	1250.1	1329.0	1340.6
147.5°	906.6	930.7	954.8	960.8	1004.6	1063.0	1092.1	1133.5	1216.4	1278.6	1288.1
150°	928.8	950.6	972.3	977.8	1015.9	1066.7	1092.1	1127.1	1197.1	1249.6	1257.3
152.5°	951.8	968.3	984.9	989.0	1023.4	1069.2	1092.1	1122.0	1181.7	1226.5	1232.4
155°	986.0	998.3	1010.4	1013.5	1039.6	1074.6	1092.1	1115.9	1163.5	1199.1	1203.0
157.5°	1011.3	1023.1	1035.0	1037.9	1056.0	1080.1	1092.1	1110.6	1147.6	1175.3	1178.0
160°	1028.3	1037.5	1046.8	1049.1	1063.5	1082.6	1092.1	1108.0	1139.6	1163.5	1165.0
162.5°	1045.4	1052.3	1059.2	1061.0	1071.4	1085.3	1092.1	1105.5	1132.2	1152.3	1153.8
165°	1063.9	1070.2	1076.6	1078.1	1082.8	1089.0	1092.1	1101.7	1120.9	1135.2	1136.8
167.5°	1081.0	1084.0	1087.0	1087.7	1091.7	1096.9	1099.6	1105.9	1118.4	1127.8	1128.5
170°	1092.1	1095.1	1098.1	1098.8	1099.1	1099.4	1099.6	1105.9	1118.4	1127.8	1127.8
172.5°	1098.1	1098.7	1099.4	1099.6	1099.6	1099.6	1099.6	1104.6	1114.4	1121.9	1121.3
175°	1106.3	1106.3	1106.3	1106.3	1104.1	1101.1	1099.6	1102.7	1109.1	1113.7	1113.7
177.5°	1106.3	1106.3	1106.3	1106.3	1104.6	1102.2	1101.0	1103.5	1108.5	1112.2	1111.5
180°	1106.3	1106.3	1106.3	1106.3	1106.3	1106.3	1106.3	1106.3	1106.3	1106.3	1106.3



TEST NUMBER: P938111

CATALOG NUMBER: SQ4-FB-125U-125D-830-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (continued):**

	80°	90°
0°	754.7	754.7
2.5°	805.6	800.8
5°	1036.2	1041.1
7.5°	1395.4	1392.9
10°	1735.0	1756.9
12.5°	1982.6	1987.4
15°	2133.0	2142.8
17.5°	2191.2	2193.7
20°	2193.7	2188.9
22.5°	2167.0	2162.2
25°	2135.4	2133.0
27.5°	2106.4	2108.7
30°	2094.2	2101.5
32.5°	2094.2	2106.4
35°	2099.1	2111.2
37.5°	2096.6	2111.2
40°	2086.9	2103.9
42.5°	2060.3	2072.4
45°	2019.0	2033.5
47.5°	1965.6	1975.3
50°	1897.7	1907.3
52.5°	1812.7	1815.2
55°	1710.8	1720.5
57.5°	1601.6	1604.0
60°	1480.3	1487.5
62.5°	1351.7	1351.7
65°	1215.7	1220.6
67.5°	1075.0	1087.2
70°	931.8	934.3
72.5°	791.1	791.1
75°	645.5	647.9
77.5°	507.2	507.2
80°	376.1	378.6
82.5°	259.6	264.5
85°	162.6	162.6
87.5°	75.2	68.0
90°	28.2	28.2
92.5°	113.0	90.5
95°	393.9	325.9
97.5°	943.9	814.5
100°	1359.9	1205.8
102.5°	1769.1	1637.1
105°	2290.9	2219.9
107.5°	2632.6	2649.8
110°	2763.0	2836.9





TEST NUMBER: P938111

CATALOG NUMBER: SQ4-FB-125U-125D-830-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (continued):**

	80°	90°
112.5°	2774.6	2888.2
115°	2701.1	2858.4
117.5°	2545.1	2719.6
120°	2419.3	2588.9
122.5°	2296.9	2464.2
125°	2122.3	2276.4
127.5°	1965.2	2095.3
130°	1872.7	1992.8
132.5°	1788.7	1896.2
135°	1673.6	1766.3
137.5°	1581.2	1657.1
140°	1517.9	1588.9
142.5°	1465.5	1526.5
145°	1386.8	1432.9
147.5°	1326.4	1364.7
150°	1288.4	1319.4
152.5°	1255.8	1279.2
155°	1218.5	1234.0
157.5°	1188.9	1199.8
160°	1171.3	1177.5
162.5°	1159.7	1165.7
165°	1143.1	1149.3
167.5°	1131.0	1133.7
170°	1127.8	1127.8
172.5°	1119.0	1116.7
175°	1113.7	1113.7
177.5°	1109.0	1106.3
180°	1106.3	1106.3



TEST NUMBER: P938111  
 CATALOG NUMBER: SQ4-FB-125U-125D-830-1D-UNV-STD-W-6

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.87	6.72	6.86	7.73	9.07	19.03	19.88	20.03	20.89	22.23
	3H	6.58	7.34	7.58	8.36	9.72	20.87	21.63	21.87	22.65	24.01
	4H	6.87	7.60	7.89	8.62	9.99	21.51	22.23	22.52	23.25	24.62
	6H	7.12	7.79	8.15	8.82	10.20	21.94	22.60	22.96	23.63	25.01
	8H	7.19	7.83	8.22	8.87	10.25	22.05	22.69	23.08	23.73	25.11
	12H	7.21	7.81	8.25	8.85	10.25	22.12	22.72	23.16	23.76	25.16
4H	2H	13.07	13.80	14.10	14.82	16.19	19.31	20.03	20.33	21.05	22.42
	3H	14.64	15.25	15.67	16.30	17.68	21.35	21.95	22.38	23.00	24.38
	4H	14.74	15.29	15.78	16.33	17.74	22.11	22.67	23.15	23.71	25.11
	6H	14.75	15.23	15.80	16.29	17.69	22.64	23.12	23.69	24.19	25.59
	8H	14.72	15.17	15.77	16.23	17.64	22.80	23.25	23.85	24.31	25.72
	12H	14.68	15.09	15.75	16.16	17.58	22.89	23.30	23.96	24.37	25.79
8H	4H	16.18	16.63	17.23	17.68	19.10	22.17	22.62	23.22	23.68	25.09
	6H	16.42	16.79	17.49	17.89	19.30	22.79	23.17	23.87	24.26	25.68
	8H	16.44	16.76	17.52	17.85	19.28	23.01	23.34	24.09	24.42	25.85
	12H	16.40	16.69	17.49	17.77	19.24	23.15	23.44	24.24	24.52	25.99
12H	4H	16.32	16.72	17.39	17.80	19.22	22.12	22.53	23.19	23.60	25.02
	6H	16.68	17.00	17.76	18.09	19.52	22.78	23.10	23.86	24.19	25.62
	8H	16.74	17.03	17.83	18.11	19.58	23.00	23.29	24.09	24.37	25.84