

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562723

Luminaire Tested: **SQ4-PC3-075U-075D-830-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562723
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-075U-075D-830-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8347.1 lumens
Efficiency: N/A
Efficacy: 122.8 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 68
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562723
CATALOG NUMBER: SQ4-PC3-075U-075D-830-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P562723

CATALOG NUMBER: SQ4-PC3-075U-075D-830-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	55	55	55	49
1	98	93	90	86	90	86	83	80	73	70	68	60	59	57	49	48	47	42
2	89	82	75	70	82	75	70	66	64	60	56	53	50	48	43	41	40	35
3	81	72	64	58	74	66	60	55	56	51	47	47	43	40	38	36	34	29
4	74	63	55	49	68	59	52	46	50	45	40	42	38	35	34	31	29	25
5	68	56	48	42	62	52	45	40	45	39	35	37	33	30	31	28	25	22
6	63	51	42	37	58	47	40	34	40	34	30	34	29	26	28	25	22	19
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	20	17
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	18	15
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9255	9255	9255
5°	9325	9265	9231
10°	9302	9259	9233
15°	9254	9254	9245
20°	9193	9220	9220
25°	9106	9172	9144
30°	8995	9104	9064
35°	8861	8997	8935
40°	8715	8838	8748
45°	8557	8617	8484
50°	8333	8333	8200
55°	8068	7963	7844
60°	7679	7524	7404
65°	7097	6955	6894
70°	6213	6264	6239
75°	5000	5530	5563
80°	3553	4690	4739
85°	2167	3931	3931



TEST NUMBER: P562723

CATALOG NUMBER: SQ4-PC3-075U-075D-830-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	142.4	1.7
10°-20°	408.7	4.9
20°-30°	618.9	7.4
30°-40°	741.9	8.9
40°-50°	756.5	9.1
50°-60°	660.4	7.9
60°-70°	472.8	5.7
70°-80°	243.5	2.9
80°-90°	63.2	0.8
90°-100°	306.9	3.7
100°-110°	844.3	10.1
110°-120°	871.5	10.4
120°-130°	698.2	8.4
130°-140°	548.4	6.6
140°-150°	420.3	5.0
150°-160°	302.2	3.6
160°-170°	184.8	2.2
170°-180°	62.3	0.7
0°-30°	1169.9	14.0
0°-40°	1911.9	22.9
0°-60°	3328.8	39.9
0°-90°	4108.4	49.2
90°-120°	2022.6	24.2
90°-150°	3689.5	44.2
90°-180°	4239.0	50.8
0°-180°	8347.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1505	1505	1505	1505	1505	
5°	1510	1495	1501	1496	1495	143
15°	1453	1441	1453	1453	1452	410
25°	1342	1332	1352	1347	1347	617
35°	1180	1177	1198	1190	1190	738
45°	984	981	991	978	975	757
55°	752	743	743	732	732	671
65°	488	477	478	474	474	482
75°	210	220	233	234	234	227
85°	31	47	56	57	56	42
90°	1	5	10	12	12	4
95°	46	168	543	232	148	48
105°	151	232	930	1417	1322	159
115°	267	325	746	1486	1686	264
125°	368	420	677	1145	1341	328
135°	444	493	658	926	1048	343
145°	514	549	648	789	850	322
155°	581	600	644	709	730	267
165°	628	637	646	673	677	177
175°	651	652	648	656	655	62
180°	651	651	651	651	651	

TEST NUMBER: P562723

CATALOG NUMBER: SQ4-PC3-075U-075D-830-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1504.7	1504.7	1504.7	1504.7	1504.7
2.5°	1513.7	1500.6	1504.7	1501.3	1495.8
5°	1510.3	1495.3	1500.6	1496.3	1495.0
7.5°	1499.4	1484.5	1491.4	1488.5	1487.2
10°	1489.4	1474.4	1482.4	1479.6	1478.3
12.5°	1476.0	1462.1	1471.3	1468.5	1468.2
15°	1453.2	1440.9	1453.2	1453.2	1451.8
17.5°	1424.5	1413.3	1426.4	1427.3	1426.4
20°	1404.4	1392.2	1408.6	1407.2	1408.6
22.5°	1379.9	1369.8	1387.4	1383.8	1385.2
25°	1341.7	1332.2	1351.5	1347.3	1347.3
27.5°	1296.6	1289.8	1310.8	1306.3	1306.3
30°	1266.5	1259.7	1281.8	1276.2	1276.2
32.5°	1233.0	1228.4	1249.5	1242.8	1242.8
35°	1180.1	1177.4	1198.2	1189.9	1189.9
37.5°	1125.5	1123.0	1141.9	1131.8	1128.6
40°	1085.4	1084.0	1100.7	1089.5	1089.5
42.5°	1045.2	1043.9	1058.3	1045.0	1045.0
45°	983.7	980.9	990.6	978.0	975.3
47.5°	916.5	913.8	919.8	906.2	904.8
50°	870.8	868.1	870.8	858.2	856.9
52.5°	824.0	819.1	819.5	807.0	806.7
55°	752.4	742.8	742.6	731.5	731.5
57.5°	676.6	664.0	665.1	655.6	654.3
60°	624.2	610.6	611.6	603.3	601.9
62.5°	572.9	557.1	560.4	550.9	550.6
65°	487.6	476.7	477.9	473.7	473.7
67.5°	405.7	395.6	402.9	399.6	399.3
70°	345.5	338.7	348.3	348.3	346.9
72.5°	289.8	289.5	301.5	301.5	302.3
75°	210.4	219.9	232.7	234.1	234.1
77.5°	140.4	157.3	171.4	171.9	171.7
80°	100.3	119.4	132.4	135.1	133.8
82.5°	68.0	88.2	98.9	101.7	100.3
85°	30.7	47.0	55.7	57.1	55.7
87.5°	9.2	19.8	24.2	24.7	22.6
90°	1.4	5.4	9.7	12.5	12.5
92.5°	19.1	81.6	141.5	54.3	44.6
95°	45.7	167.5	542.7	232.0	148.1
97.5°	74.5	185.7	828.1	638.1	450.2
100°	95.5	197.0	917.8	926.4	755.9
102.5°	115.5	210.5	941.1	1149.3	992.9
105°	150.9	232.1	930.3	1416.8	1322.1
107.5°	184.7	258.9	877.4	1547.8	1576.0
110°	209.0	276.7	837.5	1580.4	1677.8



TEST NUMBER: P562723

CATALOG NUMBER: SQ4-PC3-075U-075D-830-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	231.2	296.7	797.7	1559.4	1707.7
115°	267.2	325.4	746.2	1485.8	1686.1
117.5°	301.5	355.1	713.5	1382.6	1609.2
120°	322.6	374.0	699.1	1305.2	1539.4
122.5°	341.4	392.8	689.1	1237.4	1459.7
125°	368.2	419.7	677.0	1145.2	1341.4
127.5°	393.7	442.7	668.9	1068.2	1240.4
130°	407.0	457.1	664.5	1022.5	1179.5
132.5°	422.5	472.6	661.2	982.2	1124.1
135°	444.4	493.1	657.6	926.1	1048.0
137.5°	464.9	510.1	654.5	880.8	981.2
140°	480.4	522.3	653.4	850.7	941.4
142.5°	493.7	532.4	651.2	823.8	901.5
145°	513.6	548.8	647.9	789.1	850.0
147.5°	534.9	565.2	646.2	758.4	807.1
150°	548.2	575.3	645.1	741.5	779.4
152.5°	560.4	585.3	644.0	726.9	758.4
155°	581.4	600.4	643.7	709.3	729.6
157.5°	596.7	612.1	643.7	694.7	708.8
160°	607.7	619.9	643.7	686.9	697.7
162.5°	616.6	626.6	644.8	680.2	688.9
165°	628.5	636.6	646.5	672.9	677.0
167.5°	636.8	643.0	647.9	666.7	667.8
170°	642.3	646.4	647.9	664.5	664.5
172.5°	646.8	648.7	647.9	661.1	660.1
175°	650.6	652.0	647.9	656.2	654.8
177.5°	651.8	651.8	647.3	653.9	651.8
180°	650.6	650.6	650.6	650.6	650.6

(END OF REPORT)