

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563035

Luminaire Tested: **SQ4-PC3-125U-100D-830-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563035
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-125U-100D-830-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12537.4 lumens
Efficiency: N/A
Efficacy: 122.0 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 102.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563035
CATALOG NUMBER: SQ4-PC3-125U-100D-830-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P563035

CATALOG NUMBER: SQ4-PC3-125U-100D-830-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44				44
1	96	92	88	85	88	84	81	78	70	68	66	57	55	54	44	43	42	37				37
2	88	80	74	69	80	74	69	64	61	58	54	50	47	45	39	37	36	31				31
3	80	71	63	58	73	65	59	54	54	49	46	44	41	38	35	32	30	26				26
4	73	62	55	49	67	57	51	45	48	43	39	39	35	32	31	28	26	22				22
5	67	56	48	42	61	51	44	39	43	37	33	35	31	28	28	25	23	19				19
6	62	50	42	36	56	46	39	34	39	33	29	32	28	24	25	22	20	17				17
7	57	45	37	31	52	41	34	29	35	29	25	29	25	22	23	20	18	15				15
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13				13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12				12
10	46	34	27	22	42	31	25	21	27	22	18	22	18	15	18	15	13	11				11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12297	12297	12297
5°	12391	12310	12265
10°	12360	12302	12268
15°	12295	12295	12283
20°	12215	12251	12251
25°	12099	12187	12149
30°	11952	12096	12043
35°	11774	11955	11871
40°	11579	11743	11624
45°	11369	11449	11272
50°	11071	11071	10894
55°	10720	10581	10422
60°	10203	9998	9838
65°	9430	9242	9160
70°	8256	8323	8291
75°	6642	7348	7391
80°	4722	6231	6294
85°	2872	5222	5222



TEST NUMBER: P563035

CATALOG NUMBER: SQ4-PC3-125U-100D-830-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.2	1.5
10°-20°	543.0	4.3
20°-30°	822.3	6.6
30°-40°	985.8	7.9
40°-50°	1005.2	8.0
50°-60°	877.5	7.0
60°-70°	628.2	5.0
70°-80°	323.6	2.6
80°-90°	84.4	0.7
90°-100°	512.9	4.1
100°-110°	1381.7	11.0
110°-120°	1450.0	11.6
120°-130°	1176.7	9.4
130°-140°	922.8	7.4
140°-150°	708.5	5.7
150°-160°	509.4	4.1
160°-170°	311.2	2.5
170°-180°	105.0	0.8
0°-30°	1554.5	12.4
0°-40°	2540.3	20.3
0°-60°	4423.0	35.3
0°-90°	5459.2	43.5
90°-120°	3344.6	26.7
90°-150°	6152.6	49.1
90°-180°	7078.0	56.5
0°-180°	12537.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1999	1999	1999	1999	1999	
5°	2007	1987	1994	1988	1986	190
15°	1931	1915	1931	1931	1929	544
25°	1783	1770	1796	1790	1790	820
35°	1568	1564	1592	1581	1581	981
45°	1307	1303	1316	1300	1296	1006
55°	1000	987	987	972	972	891
65°	648	634	635	629	629	641
75°	280	292	309	311	311	302
85°	41	62	74	76	74	55
90°	3	8	17	18	18	7
95°	78	279	841	430	298	82
105°	256	398	1528	2286	2145	269
115°	451	552	1272	2459	2781	444
125°	616	708	1142	1931	2272	550
135°	742	828	1110	1558	1764	572
145°	858	924	1096	1332	1430	538
155°	974	1009	1087	1195	1233	448
165°	1056	1068	1091	1134	1140	298
175°	1098	1096	1092	1108	1105	104
180°	1096	1096	1096	1096	1096	

TEST NUMBER: P563035

CATALOG NUMBER: SQ4-PC3-125U-100D-830-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1999.3	1999.3	1999.3	1999.3	1999.3
2.5°	2011.2	1993.8	1999.3	1994.7	1987.5
5°	2006.8	1986.8	1993.8	1988.2	1986.4
7.5°	1992.3	1972.4	1981.6	1977.8	1976.0
10°	1979.0	1959.1	1969.7	1966.0	1964.2
12.5°	1961.2	1942.7	1954.9	1951.2	1950.8
15°	1930.8	1914.6	1930.8	1930.8	1929.0
17.5°	1892.7	1877.9	1895.3	1896.4	1895.3
20°	1866.1	1849.8	1871.6	1869.8	1871.6
22.5°	1833.5	1820.1	1843.5	1838.7	1840.5
25°	1782.7	1770.1	1795.7	1790.2	1790.2
27.5°	1722.8	1713.7	1741.7	1735.7	1735.7
30°	1682.8	1673.7	1703.1	1695.7	1695.7
32.5°	1638.4	1632.2	1660.2	1651.3	1651.3
35°	1568.0	1564.4	1592.1	1581.0	1581.0
37.5°	1495.4	1492.2	1517.3	1503.9	1499.5
40°	1442.1	1440.3	1462.5	1447.7	1447.7
42.5°	1388.8	1387.0	1406.2	1388.4	1388.4
45°	1307.0	1303.4	1316.2	1299.5	1295.9
47.5°	1217.7	1214.1	1222.2	1204.0	1202.2
50°	1157.0	1153.4	1157.0	1140.3	1138.5
52.5°	1094.8	1088.3	1088.9	1072.2	1071.9
55°	999.7	987.0	986.7	971.9	971.9
57.5°	899.0	882.3	883.8	871.2	869.3
60°	829.4	811.3	812.7	801.5	799.7
62.5°	761.2	740.2	744.6	732.0	731.6
65°	647.9	633.5	635.0	629.4	629.4
67.5°	539.1	525.7	535.4	530.9	530.6
70°	459.1	450.1	462.8	462.8	461.0
72.5°	385.1	384.7	400.6	400.6	401.7
75°	279.5	292.2	309.2	311.0	311.0
77.5°	186.6	209.1	227.7	228.4	228.1
80°	133.3	158.6	175.9	179.5	177.7
82.5°	90.3	117.1	131.4	135.1	133.3
85°	40.7	62.4	74.0	75.9	74.0
87.5°	12.4	26.5	33.0	33.2	30.3
90°	2.8	8.3	16.8	18.2	18.2
92.5°	34.1	120.4	238.0	114.6	79.6
95°	78.2	279.0	840.8	430.0	297.5
97.5°	124.9	319.3	1318.8	1101.7	830.8
100°	160.6	335.4	1470.8	1538.8	1276.6
102.5°	195.3	358.1	1521.1	1866.2	1651.0
105°	255.6	397.6	1528.0	2286.1	2145.4
107.5°	312.6	439.3	1463.0	2501.9	2538.2
110°	350.6	470.8	1403.7	2568.8	2701.3

TEST NUMBER: P563035

CATALOG NUMBER: SQ4-PC3-125U-100D-830-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	390.8	502.3	1346.7	2554.0	2771.7
115°	451.2	552.2	1272.4	2458.6	2780.9
117.5°	506.2	601.0	1214.9	2306.4	2665.3
120°	541.9	633.4	1185.8	2197.1	2565.8
122.5°	573.2	663.6	1164.6	2085.3	2453.0
125°	616.0	707.5	1142.5	1931.1	2272.5
127.5°	657.0	747.2	1128.6	1795.1	2099.9
130°	681.6	771.8	1123.0	1717.1	1984.8
132.5°	706.2	795.2	1117.4	1648.4	1894.3
135°	741.7	827.7	1110.4	1557.9	1764.1
137.5°	775.5	858.0	1106.8	1481.1	1650.4
140°	798.9	878.2	1103.4	1433.8	1586.7
142.5°	823.5	897.3	1101.2	1389.6	1518.5
145°	857.6	924.5	1096.5	1331.9	1430.3
147.5°	894.5	952.7	1091.7	1283.4	1360.7
150°	919.1	969.6	1089.5	1252.9	1317.1
152.5°	941.4	985.4	1088.3	1228.1	1280.3
155°	973.5	1009.0	1086.7	1195.1	1233.3
157.5°	1001.8	1029.3	1087.0	1171.9	1197.6
160°	1019.6	1042.8	1088.1	1158.3	1177.5
162.5°	1035.3	1054.1	1089.2	1147.0	1160.7
165°	1055.9	1068.2	1090.9	1134.3	1139.8
167.5°	1072.7	1079.8	1092.3	1124.4	1126.6
170°	1083.9	1086.6	1092.3	1118.8	1118.8
172.5°	1090.6	1091.1	1093.4	1113.2	1113.2
175°	1097.8	1096.5	1092.3	1107.6	1104.8
177.5°	1100.9	1098.7	1093.1	1102.0	1099.8
180°	1096.5	1096.5	1096.5	1096.5	1096.5

(END OF REPORT)